








NOTES:

1. MATERIAL:

HOUSING : PPS

TERMINAL: PHOSPHOR BRONZE

2.FINISH 0 - GOLD FLASH IN CONTACT AREA, 152um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER 0.76um/30uin MIN. NICKEL OVERALL.

1 - 0.25um/10uin MIN. GOLD IN CONTACT AREA, 152um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER 0.76um/30uin MIN. NICKEL OVERALL.

2 - 0.38um/15uin MIN. GOLD IN CONTACT AREA, 152um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER 0.76um/30uin MIN. NICKEL OVERALL.

3 - 0.76um/30uin MIN. GOLD IN CONTACT AREA, 152um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER 0.76um/30uin MIN. NICKEL OVERALL.

4 - 0.50um/20uin MIN. GOLD IN CONTACT AREA, 152um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER 0.76um/30uin MIN. NICKEL OVERALL.

3. PRODUCT SPECIFICATION REFER TO PS-48200-001.

4. PRODUCT SPECIFICATION : PER PS-48200-001

5. TEST SUMMARY : PER TS-48200-001

6. PACKAGE SPECIFICATION : PK-48200-001

7. LEAD FREE AND ROHS COMPLIANT PRODUCT

PART NO. LEGEND : 48200 - 92**


0:STANDARD , BROWN , 5V, PLASTIC PEG

1:STANDARD , WHITE , 5V, PLASTIC PEG

5:STANDARD , WHITE , 5V, METAL PEG

PLATING VERSION (REFER TO NOTES 2)

DRAWING ERROR				QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
						MM ONLY		2:1	METRIC		
EC NO: 2007/03/05 DRW:ALLIN CHKD: 2007/03/09 APPR:WWSCHANG 2007/03/13	DESCRIPTION	REV	▽=0 ▽=0	mm INCH		DRAWN BY DATE		TITLE			
				4 PLACES ± --- ± ---		TOM 2005/02/04		ASS'Y 1.27MM EDGE CARD			
				3 PLACES ± --- ± ---		CHECKED BY DATE		CONN 184 CKT (3.3V & 5V)			
				2 PLACES ± 0.25 ± ---		ALL IN 2005/02/04					
				1 PLACE ± 0.25 ± ---		APPROVED BY DATE					
				ANGULAR ± 3 °		WWSCHANG 2005/02/04		MOLEX MOLEX INCORPORATED			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
						SEE TABLE		SD-48200-001		1 OF 4	
						SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			



SLOT TO INDICATE
CKT# 1

MARK

NOTES:

1. MATERIAL:

HOUSING : PPS

TERMINAL: PHOSPHOR BRONZE



0 - GOLD FLASH IN CONTACT AREA, 1.52um/60uin
MIN. TIN IN SOLDER TAIL, BOTH OVER 0.76um/
30uin MIN. NICKEL OVERALL.

1 - 0.25um/10uin MIN. GOLD IN CONTACT AREA,
1.52um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER
0.76um/30uin MIN. NICKEL OVERALL.

2 - 0.38um/15uin MIN. GOLD IN CONTACT AREA,
1.52um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER
0.76um/30uin MIN. NICKEL OVERALL.

3 - 0.76um/30uin MIN. GOLD IN CONTACT AREA,
1.52um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER
0.76um/30uin MIN. NICKEL OVERALL.

4 - 0.50um/20uin MIN. GOLD IN CONTACT AREA,
1.52um/60uin MIN. TIN IN SOLDER TAIL, BOTH OVER
0.76um/30uin MIN. NICKEL OVERALL.

3. PROCUDT SPECIFICATION REFER TO PS-48200-001.

4. PRODUCT SPECIFICATION : PER PS-48200-001

5. TEST SUMMARY : PER TS-48200-001

6. PACKAGE SPECIFICATION : PK-48200-001

7. LEAD FREE AND ROHS COMPLIANT PRODUCT

PART NO. LEGEND : 48200 - 92**

PEG VERSION, COLOR PLATING VERSION
(SEE NOTES 2)

2 : STANDARD , BROWN , 3.3V, PLASTIC PEG


3 : STANDARD , WHITE , 3.3V, PLASTIC PEG

4 : STANDARD , RED , 3.3V, PLASTIC PEG

6 : STANDARD , WHITE, 3.3V, METAL PEG

7 : STANDARD , GREEN , 3.3V, PLASTIC PEG
(PANTON COLOR 365C)

8 : STANDARD , BLACK , 3.3V, PLASTIC PEG



SEE SHEET 1 EC NO: SH2007-0620 2007/03/05 DRWN:ALLIN 2007/03/09 CHKD: APPR:WWSCHANG 2007/03/13	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE ASS'Y 1.27MM EDGE CARD CONN 184 CKT (3.3V & 5V)				
			4 PLACES	± ---	± ---	TOM	2005/02/04					
			3 PLACES	± ---	± ---	CHECKED BY	DATE					
			2 PLACES	± 0.25	± ---	ALL IN	2005/02/04	MOLEX INCORPORATED				
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE					
			ANGULAR ± 3 °		WWSCHANG	2005/02/04						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
SEE TABLE		SD-48200-001			3 OF 4							
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

10 9 8 7 6 5 4 3 2 1

F


E

D


C

B

A



RECOMMENDED P.C. BOARD PATTERN



RECOMMENDED MATING P.C. BOARD EDGE CONFIGURATION

SEE SHEET 1 EC NO: SH2007-0620 DRWN:ALLIN CHKD: APPR:WWSCHANG	2007/03/05 2007/03/09 2007/03/13	QUALITY SYMBOLS ▽=0 ▽C=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY TOM	DATE 2005/02/04	TITLE ASS'Y 1.27MM EDGE CARD CONN 184 CKT (3.3V & 5V)			
				4 PLACES	± ---	± ---	CHECKED BY	DATE				
				3 PLACES	± ---	± ---	ALL IN	2005/02/04				
				2 PLACES	± 0.25	± ---	APPROVED BY	DATE	MOLEX MOLEX INCORPORATED			
				1 PLACE	± 0.25	± ---	WWSCHANG	2005/02/04				
ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-48200-001		4 OF 4					
REV				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

9 8 7 6 5 4 3 2 1