








DRILLING PLAN



CIRCUIT DIAGRAM



KTT 217



Specifications:

Contact rating:	20mA, 24V DC; max. 0.5W
Contact resistance:	100mOhm max.
Insulation resistance:	1 000MOhm min. at 100V DC
Dielectric strength:	250V, 50Hz for the duration of 1 minute
Operating temperature:	-40°C to +85°C
Mechanical life:	min. 1 000 000 cycles
Operating force:	4.5 +/-1.0N
Travel:	0.75 +/-0.25mm
Soldering conditions:	auto-soldering: max.: 270°C, 5sec.
Mounting:	on pc-board
Material:	Base: thermoplastic UL94V-0, blue Button: silicone, ivory Contact disc: stainless steel, 0.025µm gold plated over nickel barrier Terminal contact: brass, 0.025µm gold plated Terminal: brass, tin plated
IP rating:	IP67



Tolerances: 0.1-1.0: ±0.05mm 1.0-5.0: ±0.1mm 5.0-10.0: ±0.2mm			Date	Name	TMP 1	
			09/08	dr		
Tolerances	01/13	dr			30 15 93	
Material	07/12	dr				
IP rating	04/12	dr				
Operating temperature	06/09	dr				
Operating force	05/09	dr			Page 1/1	
Modifications	Date	Name				

knitter-switch

TMP 1

30 15 93

Page

1/1