


High Precision Foil Wraparound Surface Mount Chip Resistor with TCR of $\pm 2 \text{ ppm/}^\circ\text{C}$ and Load Life Stability of $\pm 0.01 \%$ (100 ppm)



Top View

Any value at any tolerance within resistance range

INTRODUCTION

Bulk Metal® Foil (BMF) Technology out-performs all other resistor technologies available today for applications that require high precision and high stability, and allows production of customer oriented products designed to satisfy challenging and specific technical requirements.

The BMF provides an inherently low and predictable Temperature Coefficient of Resistance (TCR) and excellent load life stability for high precision analog applications.

Model VSM offers low TCR, excellent load life stability, tight tolerance, excellent shelf life stability, low current noise and low voltage coefficient, all in the same resistor.

The VSM has a full wraparound termination which ensures safe handling during the manufacturing process, as well as providing stability during multiple thermal cyclings.

Our Application Engineering Department is available to advise and make recommendations. For non-standard technical requirements and special applications, please contact us using the e-mail address in the footer below.

TABLE 1 - TOLERANCE AND TCR VS. RESISTANCE VALUE¹⁾
(- 55 °C to + 125 °C, + 25 °C Ref.)

RESISTANCE VALUE (Ω)	TOLERANCE (%)	TYPICAL TCR AND MAX. SPREAD (ppm/°C)
250 to 150K	± 0.01	$\pm 2 \pm 2$
100 to < 250	± 0.02	$\pm 2 \pm 3$
50 to < 100	± 0.05	$\pm 2 \pm 3$
25 to < 50	± 0.1	$\pm 2 \pm 4$
10 to < 25	± 0.25	$\pm 2 \pm 6$

Note

- For tighter performances, please contact Vishay Application Engineering using the e-mail addresses in the footer below.

FEATURES

- Temperature coefficient of resistance (TCR): $\pm 2.0 \text{ ppm/}^\circ\text{C}$ typical (- 55 °C to + 125 °C, + 25 °C ref.) (see table 1)
- Tolerance: to $\pm 0.01 \%$
- Power rating: to 400 mW at + 70 °C
- Load life stability: to $\pm 0.01 \%$ at 70 °C, 2000 h at rated power
- Resistance range: 10 Ω to 150 k Ω (for higher and lower values, please contact us)
- Fast thermal stabilization < 1 s
- Electrostatic discharge (ESD) above 25 000 V**
- Short time overload: $\leq 0.01 \%$
- Non inductive, non capacitive design
- Rise time: 1 ns without ringing
- Current noise: - 42 dB
- Voltage coefficient < 0.1 ppm/V
- Non inductive: < 0.08 μH
- Non hot spot design
- Terminal finishes available: lead (Pb)-free tin/lead alloy
- Matched sets are available per request
- Any value available within resistance range (e.g. 1K2345)
- Screening per EEE-INST-002 is available for military and space
- Prototype samples available from 48 h. For more information, please contact foil@vishay.com
- For better performances please review **VSMP** and **VFCP** Series datasheets




RoHS*
COMPLIANT

APPLICATIONS

- Automatic test equipment (ATE)
- High precision instrumentation
- Laboratory, industrial and medical
- Audio
- EB applications (electron beam scanning and recording equipment, electron microscopes)
- Military and space
- Satellite
- Commercial aviation
- Airborne
- Down hole instrumentation
- Communication

FIGURE 1 - POWER DERATING CURVE



* Pb containing terminations are not RoHS compliant, exemptions may apply



VSM Series (0805, 1206, 1506, 2010, 2512)

High Precision Foil Wraparound Surface Mount Chip Resistor with TCR of $\pm 2 \text{ ppm}/^\circ\text{C}$ and Load Life Stability of $\pm 0.01 \%$ (100 ppm) Vishay Foil Resistors

FIGURE 2 - TRIMMING TO VALUES

(Conceptual Illustration)





FIGURE 3 - TYPICAL TCR CURVE

(For more details, see Table 1)



Note

- The TCR values for $< 100 \Omega$ are influenced by the termination composition and result in deviation from this curve.

TABLE 2 - DIMENSIONS AND LAND PATTERN in inches (millimeters)

Top View				Recommended Land Pattern			
CHIP SIZE	L ± 0.005 (0.13)	W ± 0.005 (0.13)	THICKNESS MAXIMUM	D ± 0.005 (0.13)	Z ¹⁾ MAXIMUM	G ¹⁾ MINIMUM	X ¹⁾ MAXIMUM
0805	0.080 (2.03)	0.050 (1.27)	0.025 (0.64)	0.015 (0.38)	0.122 (3.10)	0.028 (0.71)	0.050 (1.27)
1206	0.126 (3.20)	0.062 (1.57)	0.025 (0.64)	0.020 (0.51)	0.175 (4.45)	0.059 (1.50)	0.071 (1.80)
1506	0.150 (3.81)	0.062 (1.57)	0.025 (0.64)	0.020 (0.51)	0.199 (5.05)	0.083 (2.11)	0.071 (1.80)
2010	0.198 (5.03)	0.097 (2.46)	0.025 (0.64)	0.025 (0.64)	0.247 (6.27)	0.115 (2.92)	0.103 (2.62)
2512	0.249 (6.32)	0.127 (3.23)	0.025 (0.64)	0.032 (0.81)	0.291 (7.39)	0.150 (3.81)	0.127 (3.23)

Note

- Land Pattern Dimensions are per IPC-7351A

TABLE 3 - SPECIFICATIONS

CHIP SIZE	RATED POWER (mW) at $+70^\circ\text{C}$	MAX VOLTAGE RATING ($\leq \sqrt{P \times R}$)	RESISTANCE RANGE (Ω)	MAXIMUM WEIGHT (mg)
0805	100	34 V	10 to 12K	6
1206	150	67 V	10 to 30K	11
1506	200	89 V	10 to 40K	12
2010	300	173 V	10 to 100K	27
2512	400	220 V	10 to 150K	40

TABLE 4 - PERFORMANCES

TEST OR CONDITIONS	MIL-PRF-55342 CHARACTERISTIC E ΔR LIMITS	TYPICAL ΔR LIMITS	MAXIMUM ΔR LIMITS ¹⁾
Thermal Shock	$\pm 0.1 \%$	$\pm 0.005 \%$ (50 ppm)	$\pm 0.02 \%$ (200 ppm)
Low Temperature Operation	$\pm 0.1 \%$	$\pm 0.01 \%$ (100 ppm)	$\pm 0.02 \%$ (200 ppm)
Short Time Overload	$\pm 0.1 \%$	$\pm 0.01 \%$ (100 ppm)	$\pm 0.02 \%$ (200 ppm)
High Temperature Exposure	$\pm 0.1 \%$	$\pm 0.01 \%$ (100 ppm)	$\pm 0.03 \%$ (300 ppm)
Resistance to Soldering Heat	$\pm 0.2 \%$	$\pm 0.005 \%$ (50 ppm)	$\pm 0.01 \%$ (100 ppm)
Moisture Resistance	$\pm 0.2 \%$	$\pm 0.005 \%$ (50 ppm)	$\pm 0.03 \%$ (300 ppm)
Load Life Stability $+70^\circ\text{C}$ for 2000 h at Rated Power	$\pm 0.5 \%$	$\pm 0.005 \%$ (50 ppm)	$\pm 0.01 \%$ (100 ppm)

Note


- As shown $+0.01 \Omega$ to allow for measurement errors at low values.

VSM Series (0805, 1206, 1506, 2010, 2512)



Vishay Foil Resistors High Precision Foil Wraparound Surface
Mount Chip Resistor with TCR of $\pm 2 \text{ ppm}/^\circ\text{C}$
and Load Life Stability of $\pm 0.01 \%$ (100 ppm)

FIGURE 4 - RECOMMENDED MOUNTING¹⁾²⁾³⁾



Notes


1. Avoid the use of cleaning agents which could attack epoxy resins, which form part of the resistor construction
2. Vacuum pick up is recommended for handling
3. Soldering iron may damage the resistor

TABLE 5 - SPACE AND MILITARY SPECIFICATIONS

MODEL	EEE-INST-002	DSCC	MIL-PRF
VSM0805	✓	07024	55342
VSM1206	✓	07025	
VSM1506	✓	03010	
VSM2010	✓	06001	
VSM2512	✓	06002	

TABLE 6 - GLOBAL PART NUMBER INFORMATION

NEW GLOBAL PART NUMBER: Y145512K7560T9R (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y1455 12K7565 T 9 R:

TYPE: VSM1506
VALUES: 12.7560 $k\Omega$
ABSOLUTE TOLERANCE: 0.01 %
TERMINATION: lead (Pb)-free
PACKAGING: tape and reel

HISTORICAL PART NUMBER: VSM1506 12K756 TCR2 T S T (will continue to be used)

VSM1506	12K756	TCR2	T	S	T
MODEL	RESISTANCE VALUE	TCR CHARACTERISTICS	TOLERANCE	TERMINATION	PACKAGING
VSM0805 VSM1206 VSM1506 VSM2010 VSM2512	12.756 $k\Omega$		T = $\pm 0.01 \%$ Q = $\pm 0.02 \%$ A = $\pm 0.05 \%$ B = $\pm 0.10 \%$ C = $\pm 0.25 \%$ D = $\pm 0.5 \%$ F = $\pm 1.0 \%$	S = lead (Pb)-free B = tin/lead	T = tape and reel W = waffle pack

Note

* For non-standard requests, please contact application engineering.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[VSMD1505-10K/10K-0.01-0.005](#)