




PRODUCT NUMBER
SEE TABLE



SEE SHEET 3 FOR
LOCATOR/HOLDDOWN
VARIATIONS

.014 [0.36]
AT TIPS



mat'l. code				surface		tolerance		projection	product family			
-				ISO 1302 ✓		ISO 406 ISO 1101			RIBCAGE			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title			
L	J10329	CRG	6/6/01	angles	linear	.XX±.01/0.3			RIBCAGE III T/M			
M	M05-0123	MHT	6/6/05			.XXX±.005/0.13		VERT. HEADER ASS'Y				
N	M06-0225	ERE	06/12/06	0±2°		.XXXX±.0020/0.051		scale 4:1				
P	M06-0370	MHT	9/26/06	dr	M. CORNMAN	6/6/95			dwg no		sheet 1 of 6	size
R	M09-0058	MHT	4/04/09	enrg	D. WHITING	6/6/95			95776		A3	
S	N10-0122	YO	5/10/10	chr	D. WHITING	6/6/95						
T	ELX-N-009749	YO	1/31/12	appd	D. WHITING	6/6/95						
sheet	revision	T	T	T	T	T	T		type Product Customer Drawing			
index	sheet	1	2	3	4	5	6					




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW



SECTION Y-Y

mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		scale 4:1	title		
T					angles	linear		RIBCAGE III T/M VERT. HEADER ASS'Y		
					0.002	.XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051				
					dr	M. CORNMAN 6/6/95				
					enr	D. WHITING 6/6/95	FCI	dwg no		sheet 2 of 6
					chr	D. WHITING 6/6/95		95776		size A3
					appd	D. WHITING 6/6/95		type Product Customer Drawing		
sheet index	revision sheet									


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS


STYLE
1





STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title				
T					angles	linear	.XX±.01/0.3			RIBCAGE III T/M VERT. HEADER ASS'Y				
					0.002		.XXX±.005/0.13							
					0.002		.XXXX±.0020/0.051		scale 4:1					
					dr	M. CORNMAN	6/6/95			dwg no		sheet 3 of 6		size
					enrg	D. WHITING	6/6/95			95776				A3
					chr	D. WHITING	6/6/95			type Product Customer Drawing				
					appd	D. WHITING	6/6/95							
sheet index		revision sheet												


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ISO 406 ISO 1101	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		RIBCAGE III T/M VERT. HEADER ASS'Y	
T					angles	linear	INCH/MM		dwg no	
					0.001	0.001	scale 4:1		sheet 4 of 6	
					dr	M. CORNMAN	6/6/95	95776		size
					enrg	D. WHITING	6/6/95	A3		
					chr	D. WHITING	6/6/95	type		
					appd	D. WHITING	6/6/95	Product Customer Drawing		
sheet	revision									
index	sheet									


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE					
ltr		ecn no		dr		date		tolerances unless otherwise specified				title			
T										RIBCAGE III T/M VERT. HEADER ASS'Y					
										INCH/MM					
										scale 4:1					
															
										dwg no					
										sheet5 of 6					
										95776					
										A3					
										type Product Customer Drawing					
sheet index		revision sheet													

