




ICE Components, Inc.

Voice: 800.729.2099
Fax: 678.560.9304

cust.serv@icecomp.com
www.icecomponents.com

SMT High Current Inductors

LP08 Series



Features


- Low Cost Design
- High saturation current of 45A
- Designed for frequencies up to 1MHz
- Suitable for pick and place applications

Applications


- Voltage Regulator Modules (VRMs)
- High Frequency, High Current Switching Power Supplies
- Synchronous Buck DC/DC Converters

Packaging: Reel diameter: 13", Reel Width: 24 mm, Pieces/Reel: 600

Mechanical




Top View




Side View

Recommended PCB layout



Schematic



units: mm

Electrical Specifications

Part Number	Inductance ¹ (nH, $\pm 15\%$)	DCR (m Ω , $\pm 8\%$)	Idc ⁵ (A)	Isat ⁶ (A)
LP08-211	210	0.58	38	45
LP08-271	270	0.58	38	35
LP08-331	330	0.58	38	31

1. Tested at 1.0 MHz, 0.1 Vrms.
2. Electrical specifications at 25°C.
3. Operating range: -40°C to +130°C.
4. Meets UL 94V-0.
5. Idc is DC current required to produce a temperature rise of 40°C.
6. Isat is the DC current required to reduce the nominal inductance by 15%.

