


CORE DIMENSIONS:

A	13.00 [.512]	+	0.30 [.012]
B	7.00 [.275]	+	0.30 [.012]
C	23.00 [.905]	+	0.50 [.020]
D	6.27 [.247]	+	0.20 [.008]
E	5.00 [.197]	+	0.30 [.012]

Weight/1000 10.6 kgs 23.49 lbs.
(Per Pair)



CASE DIMENSIONS:


A	16.50 [.650]	+	0.40 [.016]
B	7.00 [.276]	+	0.40 [.016]
C	30.50 [1.201]	+	0.60 [.024]
D	15.25 [.600]	+	0.40 [.016]
E	2.79 [.110]	+	REF.

**UNCONTROLLED
DOCUMENT**

IMPEDANCE (Z)

Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	92 Ω	183 Ω	315 Ω
Minimum	- Ω	146 Ω	- Ω

Z vs. FREQUENCY



FREQUENCY (MHz)

AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture

NOTES:

- CASE FLAMMABILITY RATING: UL94 V-0
- CASE MATERIAL: HALOGEN FREE NYLON
- ASSEMBLED PART #: 28A2307-0A2
- CORE PART #: 28A2307-000
- CASE COLOR: BLACK -"0A2"

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		Laird TECHNOLOGIES®		
				PROJECT/PART NUMBER:		REV	PART TYPE:	DRAWN BY:
				28A2307-0A2		C	FERRITE SNAP-ON	TMB
C	UPDATE CASE SHAPE	06/14/11	Jcai	DATE:	09/26/08	SCALE:	NTS	MATERIAL: Ferrite
B	UPDATE DIMS. C AND D	3/10/09	JRK	CAD #	28A2307-0A2-C	TOOL #	—	
A	ORIGINAL DRAFT	09/26/08	TMB					
REV	DESCRIPTION	DATE	INT					