






THIS DRAWING IS UNPUBLISHED.  
RELEASED FOR PUBLICATION 20  
ALL RIGHTS RESERVED.  
© COPYRIGHT 20

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
A1		REVISED PER ECR-17-015449	25OCT2017	BDA KR



RECOMMENDED  
PANEL CUT-OUT  
SCALE 2:1

① LOCKNUT; METAL  
HOUSING; NYLON, FLAME RETARDANT,  
UL 94-VO  
O-RING; NEOPRENE

② LOCKNUT; PLATED

③ LOCKNUT, SIX(6) OR EIGHT(8) SYMETRICAL  
PLACED GRIP POINTS PERMISSIBLE.

4 DIMENSIONS SHOWN REPRESENT PRODUCT IN  
DRY, AS MOLDED, CONDITION. ADDITIONAL  
2% GROWTH DUE TO SUBSEQUENT MOISTURE  
ABSORPTION MAY OCCUR AND SHOULD BE  
ACCOUNTED FOR.

1604941-1

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W J RUDY 12JUN03	TE Connectivity
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK JHW 12JUN03	
0 PLC ± 1 PLC ±0.5 [ .02 ] 2 PLC ±0.13 [ .005 ] 3 PLC ± 4 PLC ± ANGLES ±	APVD JHW 12JUN03	PRODUCT SPEC -	
MATERIAL	FINISH	APPLICATION SPEC -	
①	②	WEIGHT -	RESTRICTED TO A 200779 C=1604941
CUSTOMER DRAWING		SCALE 2:1	1 OF 1 REV A1