

Display Solutions

Your Value-added Partner for Industrial Display Solutions



[Product Lines](#) > [Display Solutions](#) > [ES-1000 LCD Kits](#) > [ES-1106N-LVAE](#)

Model Information

ES-1106N-LVAE



RoHS

[Ordering Information](#)

[Datasheet \(PDF\)](#)

[Downloads](#)

[Add to My Products](#)

6.5" Color TFT-LCD Kit for LVDS Interface

Main Features

- LCD Panel: AUO G065VN01 V0
- Display: 640 x 480 VGA, 16.2M
- Viewing Angle (L/R/U/D): 70/70/60/60
- Brightness (nit): 500
- Response Time (ms): 25
- Backlight (hrs.): CCFL, 2-tubes, 50,000 hrs
- Operation Temp.: -10 ~ 70 °C
- ES-1106N-LVA-01E ~ 04E LCD Kit Cable Length (mm): 500 (optional)
- Outline Dimensions mm (W x H x D): 153 x 118 x 10.7

Introduction

6.5" Color TFT-LCD Kit for LVDS Interface

Ordering Information

Part Number		Description
ES-1106N-LVA-02E	RoHS	6.5" LCD kit, AUO 400 nites, LVDS-02, VGA
ES-1106N-LVA-01E	RoHS	6.5" LCD kit, AUO 400 nites, LVDS-01, VGA
ES-1106N-LVA-03E	RoHS	6.5" LCD kit, AUO 400 nites, LVDS-03, VGA
ES-1106N-LVA-04E	RoHS	6.5" LCD kit, AUO 400 nites, LVDS-04, VGA
ES-1106N-LVAE	RoHS	6.5" Color TFT-LCD Kit for LVDS Interface
New		

Contact Information

Office	Tel	Email
Advantech Headquarters	886-2-2792-7818	ECG.ACL@advantech.com

Main Menu

- [About Display Solutions](#)
- [CTOS for Display Solutions](#)
- [DTOS Industrial Display Solutions](#)
- [Product News](#)
- [Selection Wizard](#)
- [Virtual Tour](#)
- [Applications](#)
- [Contact Us](#)

Related Links

- [Embedded Computing - x86](#)
- [Embedded Computing - ARM/XScale](#)
- [Applied Panel Computers](#)
- [SMART Home Solution](#)

Feature Articles

- [Panel PC, Flat Panel Computer, Touch Screen, Human Machine Interface](#)
- [Industrial Computer](#)