

NTE39 Silicon PNP Transistor Line–Operated Series Pass/Switching Regulator (Compl to NTE157)

Description:

The NTE39 is a silicon PNP transistor in a TO126 type package designed for use in line–operated applications such as low power, line–operated series pass and switching regulators requiring PNP capability.

Features:

- High Collector–Emitter Sustaining Voltage: $V_{CEO(sus)} = 300V$ @ $I_C = 1.0mA$
- Excellent DC Current Gain: $h_{FE} = 30$ to 240 @ $I_C = 50mA$

Absolute Maximum Ratings:

Collector–Emitter Voltage, V_{CEO} 300V
 Emitter–Base Voltage, V_{EB} 3V
 Continuous Collector Current, I_C 500mA
 Total Power Dissipation ($T_C = +25^\circ C$), P_D 20W
 Derate Above $25^\circ C$ 0.16W/ $^\circ C$
 Operating Junction Temperature Range, T_J -65° to $+150^\circ C$
 Storage Temperature Range, T_{stg} -65° to $+150^\circ C$
 Thermal Resistance, Junction to case, $R_{\theta JC}$ 6.25 $^\circ C/W$

Electrical Characteristics: ($T_C = +25^\circ C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF Characteristics						
Collector–Emitter Sustaining Voltage	$V_{CEO(sus)}$	$I_C = 1.0mA, I_B = 0$	300	–	–	V
Collector Cutoff Current	I_{CEO}	$V_{CB} = 300V, I_E = 0$	–	–	100	μA
Emitter Cutoff Current	I_{EBO}	$V_{EB} = 3V, I_C = 0$	–	–	100	μA
ON Characteristics						
DC Current Gain	h_{FE}	$I_C = 50mA, V_{CE} = 10V$	30	–	240	

