

# SKY77155: System Smart™ PA Module for CDMA / PCS (1750–1780 MHz)

## Applications

- Personal Communications Services (PCS)
- Full Korean PCS coverage
- Wireless local loop (WLL)

## Features

- Low voltage positive bias supply
  - 3.2 V to 4.2 V
- Low  $V_{REF}$ 
  - 2.85 V, nominal
- Low  $I_{REF}$ 
  - less than 1 mA
- Good linearity
- High efficiency
- Large dynamic range
- 8-pin package
  - 3 x 3 x 1.2 mm
- Power down control
- Dynamic bias control
- InGaP
- IS95/CDMA2000/EVDO

## Description

The SKY77155 System Smart™ Power Amplifier Module (PAM) is a fully matched 8-pin surface mount module developed for Code Division Multiple Access (CDMA) / Personal Communications Service (PCS) and Wireless Local Loop (WLL) applications. This small and efficient module packs full 1750–1780 MHz bandwidth coverage into a single compact package. The SKY77155 meets the stringent spectral linearity requirements of Code Division Multiple Access (CDMA) PCS transmission, with high power added efficiency for power output of up to 28 dBm. A low current pin (V<sub>CONT</sub>) is provided to improve efficiency for the low RF power range of operation.

The single Gallium Arsenide (GaAs) Microwave Monolithic Integrated Circuit (MMIC) contains all active circuitry in the module. The MMIC contains on-board bias circuitry, as well as input and interstage matching circuits. The output match is realized off-chip within the module package to optimize efficiency and power performance into a 50-ohm load. This device is manufactured with Skyworks' GaAs Heterojunction Bipolar Transistor (HBT) process that provides for all positive voltage DC supply operation while maintaining high efficiency and good linearity. Primary bias to the SKY77155 is supplied directly from a three-cell Ni-Cd, a single-cell Li-Ion, or other suitable battery with an output in the 3.2 to 4.2 volt range. Power down is accomplished by setting the voltage on the low current reference pin to zero volts. No external supply side switch is needed as typical "off" leakage is a few microamperes with full primary voltage supplied from the battery.




Figure 1. SKY77155 Functional Block Diagram

103162\_001

## Preliminary Electrical Target Specifications

The following tables list the electrical characteristics of the SKY77155 Power Amplifier. [Table 1](#) lists the absolute maximum

ratings, while [Table 2](#) shows the recommended operating conditions to achieve the performance characteristics listed in [Table 4](#). [Table 3](#) presents a truth table for the power settings.

**Table 1. Absolute Maximum Ratings<sup>(1)</sup>**

Parameter	Symbol	Minimum	Nominal	Maximum	Unit
RF Input Power	P <sub>IN</sub>	—	1.0	6.0	dBm
Supply Voltage	V <sub>CC</sub>	—	3.4	6.0	Volts
Reference Voltage	V <sub>REF</sub>	—	2.85	3.0	Volts
Case Operating Temperature <sup>(2)</sup>	T <sub>C</sub>	-30	25	+110	°C
Case Storage Temperature	T <sub>STG</sub>	-55	—	+125	°C

<sup>(1)</sup> No damage assuming only one parameter is set at limit at a time with all other parameters set at nominal value.

<sup>(2)</sup> Case Operating Temperature refers to the temperature of the GROUND PAD on the underside of the package.

**Table 2. Recommended Operating Conditions**

Parameter	Symbol	Minimum	Nominal	Maximum	Unit
Power Output	P <sub>O</sub>			28.0	dBm
Supply Voltage	V <sub>CC</sub>	3.2	3.4	4.2	Volts
Reference Voltage	V <sub>REF</sub>	2.75	2.85	2.95	Volts
Operating Frequency	F <sub>O</sub>	1750.0	1765.0	1780.0	MHz
Control Voltage	V <sub>CONT</sub>	0.0	1.25		Volts
High Power	V <sub>CONT</sub>		2.0	2.5	
Case Operating Temperature <sup>(1)</sup>	T <sub>C</sub>	-30	+25	+85	°C

<sup>(1)</sup> Case Operating Temperature refers to the temperature of the GROUND PAD on the underside of the package.

**Table 3. Power Range Truth Table**

Power Mode	V <sub>REF</sub>	V <sub>CONT</sub>	Range <sup>(1)</sup>
High Power	2.85 V	2.0 V	28 dBm
Low Power	2.85 V	< 1.3 V	≤ 0 dBm
Shut Down	0.0 V	0.0 V	—

<sup>(1)</sup> In the output power range between -10 dBm and 28 dBm, V<sub>CONT</sub> can be continuously adjusted to minimize current consumption while meeting required linearity specification.

Table 4. Electrical Specifications for CDMA Nominal Operating Conditions<sup>(1)</sup>

Characteristics	Symbol	Condition	Minimum	Typical	Maximum	Unit
Gain conditions	GLOW	V <sub>CONT</sub> = 1.25 V P <sub>0</sub> ≤ 0 dBm	21.0	24.5	26.0	dB
	GMID	V <sub>CONT</sub> = 1.55 V 0 ≥ P <sub>0</sub> ≤ 16 dBm	26.0	28.5	30.0	
	GHIGH	V <sub>CONT</sub> = 2.0 V P <sub>0</sub> = 28 dBm	27.0	29.0	30.5	
Gain Sensitivity	GSEN	All conditions fixed except V <sub>CONT</sub>	5	10	15	dB/Volt
Power Added Efficiency	PAE <sub>MID</sub>	V <sub>CONT</sub> = 1.55 V P <sub>0</sub> = 16 dBm	8	9	—	%
	PAE <sub>HIGH</sub>	V <sub>CONT</sub> ≥ 2.0 V P <sub>0</sub> = 28 dBm	37	40	—	
Total Supply Current	I <sub>CC_LOW</sub>	P <sub>0</sub> = 0 dBm	—	40	65	mA
	I <sub>CC_HIGH</sub>	P <sub>0</sub> = 28 dBm	—	455	500	
Quiescent Current	I <sub>Q_LOW</sub>	V <sub>CONT</sub> = 1.25 V	25	30	45	mA
	I <sub>Q_HIGH</sub>	V <sub>CONT</sub> = 2.0 V	65	85	110	
Reference Current	I <sub>REF</sub>		—	1.0	2.0	mA
Control Current	I <sub>CTRL</sub>	V <sub>CONT</sub> = 2.0 V	—	100	250	μA
Total Supply Current in Power-down Mode	I <sub>PD</sub>	V <sub>CC</sub> = 3.4 V V <sub>CONT</sub> = 0.0 V V <sub>REF</sub> = 0.0 V	—	3.0	5.0	μA
Adjacent Channel Power <sup>(2)(3)</sup>	1.25 MHz offset	ACP1 <sub>LOW</sub>	V <sub>CONT</sub> = 1.25 V P <sub>0</sub> ≤ 0 dBm	—	-56.0	-48.0
		ACP1 <sub>HIGH</sub>	V <sub>CONT</sub> ≥ 2.0 V P <sub>0</sub> ≤ 28 dBm	—	-50.0	-47.5
	2.25 MHz offset	ACP3 <sub>LOW</sub>	V <sub>CONT</sub> = 1.25 V P <sub>0</sub> ≤ 0 dBm	—	-80.0	-58.0
		ACP3 <sub>HIGH</sub>	V <sub>CONT</sub> ≥ 2.0 V P <sub>0</sub> ≤ 28 dBm	—	-59.0	-57.5
Harmonic Suppression	Second	F <sub>02</sub>	P <sub>0</sub> ≤ 28 dBm	—	-62	-35
	Third	F <sub>03</sub>	P <sub>0</sub> ≤ 28 dBm	—	-43	-40
Noise Power in RX Band 1840–1870 MHz	RxBN	P <sub>0</sub> ≤ 28 dBm	—	-138.0		dBm/Hz
Noise Figure	NF	—	—	4.0		dB
Input Voltage Standing Wave Ratio (VSWR)	VSWR	—	—	—	2.0:1	—
Stability (Spurious output)	S	5:1 VSWR All phases	—	—	-70.0	dBc
Ruggedness <sup>(4)</sup>	Ru	P <sub>0</sub> ≤ 28 dBm	10:1	—		VSWR
Turn On Time <sup>(5)</sup>	DC	T <sub>ONDC</sub>	—	40		μs
	RF	T <sub>ONRF</sub>	—	5		
Turn Off Time <sup>(5)</sup>	DC	T <sub>OFFDC</sub>	—	40		μs
	RF	T <sub>OFFRF</sub>	—	5		

<sup>(1)</sup> Per Table 2 over dynamic range up to 28 dBm output power, unless otherwise specified.

<sup>(2)</sup> ACP is specified per IS95 as the ratio of the total in-band power (1.23 MHz BW) to adjacent power in a 30 kHz BW.

<sup>(3)</sup> For CDMA2000 test configured as [PCH @ -3.75 dB, DCCH-9600 bps @ 0 dB; SCH-9600 bps @ 0 dB] and other test configurations that yield a peak-to-average up to 4.5 dB for CCDF = 1%, up to 1. dB power back off from the maximum listed for IS95 may be required to meet specified maximum ACP performance under worst-case conditions.

<sup>(4)</sup> All phases, time = 10 seconds.

<sup>(5)</sup> T<sub>ONDC</sub> is time required to reach stable quiescent bias (±10%) after V<sub>REF</sub> is switched high.


T<sub>OFFDC</sub> is time required for battery to decrease to < 100 μA after V<sub>REF</sub> is switched low.

After I<sub>Q0</sub> is stable, the T<sub>ONRF</sub> is time to reach final output power (±1 dB) once RF input is applied.

T<sub>OFFRF</sub> is time required for P<sub>0</sub> to drop 30 dB once RF input is removed.

## Evaluation Board Description

The evaluation board is a platform for testing and interfacing design circuitry. To accommodate the interface testing of the SKY77155, the evaluation board schematic and diagrams are



103062\_002

Figure 2. SKY77155 Evaluation Board Schematic





Figure 3. SKY77155 Evaluation Board Assembly Diagram

103162\_003

## Package Dimensions and Pin Descriptions

The SKY77155 is a multi-layer laminate base, overmold encapsulated modular package designed for surface mount solder attachment to a printed circuit board. Figure 4 is a mechanical drawing of the pad layout for this package.

Figure 5 shows the pin functions and the pin numbering convention, which starts with pin 1 in the upper left and increments counter-clockwise around the package. Figure 6 illustrates typical case markings.




### NOTES: Unless otherwise specified

1. DIMENSIONING AND TOLERANCES IN ACCORDANCE WITH ASME Y14.5M-1994.
2. SEE APPLICABLE BONDING DIAGRAM AND DEVICE ASSEMBLY DRAWING FOR DIE AND COMPONENT PLACEMENT.
3. PADS ARE SOLDER MASK DEFINED ON ALL INSIDE EDGES.
4. ALL DIMENSIONS ARE IN MILLIMETERS.

103162\_004

**Figure 4. SKY77155 Package Drawing**



Pad layout as seen from top view looking through package.

<sup>(1)</sup> All supply pins may be connected together at the supply.

<sup>(2)</sup> Package underside is GND.

103162\_007

Figure 5. SKY77155 Pin Configuration and Pin Names (Top View)




Figure 6. Typical 3x3 Case Markings

## Package and Handling Information

Because of its sensitivity to moisture absorption, this device package is baked and vacuum-packed prior to shipment. Instructions on the shipping container label must be followed regarding exposure to moisture after the container seal is broken, otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY77155 is capable of withstanding an MSL3/250 °C solder reflow. Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. If the part is attached in a reflow oven, the temperature ramp rate should not exceed 5 °C per second; maximum temperature should not exceed 250 °C. If the part is manually attached, precaution should be taken to insure that the part is not subjected to temperatures exceeding 250 °C for more than 10 seconds. For

details on attachment techniques, precautions, and handling procedures recommended by Skyworks, please refer to *Skyworks' Application Note: PCB Design and SMT Assembly/Rework, Document Number 101752*. Additional information on standard SMT reflow profiles can also be found in the *JEDEC Standard J-STD-020B*.

Production quantities of this product are shipped in the standard tape-and-reel format. For packaging details, refer to *Skyworks' Application Note: Tape and Reel, Document Number 101568*.

## Electrostatic Discharge Sensitivity

The SKY77155 is a Class 2 device. Figure 7 lists the Electrostatic Discharge (ESD) immunity level for each pin of the SKY77155 product. The numbers in Figure 7 specify the ESD threshold level for each pin where the I-V curve between the pin and ground starts to show degradation.

The ESD testing was performed in compliance with MIL-STD-883E Method 3015.7 using the Human Body Model. If ESD damage threshold magnitude is found to consistently exceed 2000 volts on a given pin, this so is indicated. If ESD damage threshold below 2000 volts is measured for either polarity, numbers are indicated that represent worst case values observed in product characterization.

Various failure criteria can be utilized when performing ESD testing. Many vendors employ relaxed ESD failure standards, which fail devices only after “the pin fails the electrical specification limits” or “the pin becomes completely non-functional”. Skyworks employs most stringent criteria and fails devices as soon as the pin begins to show any degradation on a curve tracer.

To avoid ESD damage, both latent and visible, it is very important that the product assembly and test areas follow the Class-1 ESD handling precautions listed in Table 5.




Figure 7. ESD Sensitivity Areas

**Table 5. Precautions for Handling GaAs IC-based Products to Avoid Induced Damage**

<b>Personnel Grounding</b>	Wrist Straps Conductive Smocks, Gloves and Finger Cots Antistatic ID Badges
<b>Facility</b>	Relative Humidity Control and Air Ionizers Dissipative Floors (less than $10^9 \Omega$ to GND)
<b>Protective Packaging &amp; Transportation</b>	Bags and Pouches (Faraday Shield) Protective Tote Boxes (Conductive Static Shielding) Protective Trays Grounded Carts Protective Work Order Holders
<b>Protective Workstation</b>	Dissipative Table Tops Protective Test Equipment (Properly Grounded) Grounded Tip Soldering Irons Conductive Solder Suckers Static Sensors

## Ordering Information

Model Number	Manufacturing Part Number	Product Revision	Package	Operating Temperature
SKY77155	SKY77155	-13	3x3LM-10	-30 °C to +85 °C

## Revision History

Revision	Level	Date	Description
P1		August 4, 2003	Advance Information
P2		March 18, 2004	Revise: Op. Freq., Tables 2, 4, Figure 6
P3		May 17, 2004	Revise: Tables 2, 4, Figure 7

## References

Application Note: PCB Design and SMT Assembly/Rework, Document Number 101752

Application Note: Tape and Reel, Document Number 101568

Standard SMT Reflow Profiles: JEDEC Standard J-STD-020

© 2003–2004, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products. These materials are provided by Skyworks as a service to its customers and may be used for informational purposes only. Skyworks assumes no responsibility for errors or omissions in these materials. Skyworks may make changes to its products, specifications and product descriptions at any time, without notice. Skyworks makes no commitment to update the information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from future changes to its products and product descriptions.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as may be provided in Skyworks' Terms and Conditions of Sale for such products, Skyworks assumes no liability whatsoever.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF SKYWORKSTM PRODUCTS INCLUDING WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. SKYWORKS FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THESE MATERIALS.

Skyworks™ products are not intended for use in medical, lifesaving or life-sustaining applications. Skyworks' customers using or selling Skyworks™ products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

The following are trademarks of Skyworks Solutions, Inc.: Skyworks™, the Skyworks symbol, and "Breakthrough Simplicity"™. Product names or services listed in this publication are for identification purposes only, and may be trademarks of third parties. Third-party brands and names are the property of their respective owners.

Additional information, posted at [www.skyworksinc.com](http://www.skyworksinc.com), is incorporated by reference.