



Switches > Tactile Switches



Actuator Style: **Top Actuator**
Operating Function: **Off (On)**
Contact Base Material: **Stainless Steel**
Switch Contact Plating Material: **Silver**
Low Profile: **Yes**

Features

Product Type Features

Leg Style	Gull Wing
Actuator Style	Top Actuator

Configuration Features

Switch Feedback Type	Non-Tactile
ESD Grounding Terminal	Without
Ganged	Without
Operating Function	Off (On)
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Body Features

Actuator Material	Thermoplastic
Actuator Force	40 g[1.41 oz]
Product Orientation	Vertical
Actuator Color	Black



Contact Features

Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver
Contact Current Rating	1 mA

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	Yes
Process Sealed	No

Usage Conditions

Operating Temperature Range	-10 – 60 °C[14 – 140 °F]
-----------------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2331398-1
DET SW6.5X3.9X6.0 GW VERT. NO AG TB



TE Part # 2331370-1
DET SW4.7X3.8X2.3 GW VERT. NO AG RL



TE Part # 2331393-1
DET SW5.7X4.0X2.0 GW HORZ. NO AG RL



TE Part # 2331394-1
DET SW4.7X3.5X2.25 GW VERT. NOH AG RL



TE Part # 2331365-1
DET SW4.7X3.8X2.3 GW VERT. NO AG RL

Also in the Series | [ALCOSWITCH JJ](#)



Tactile Switches(52)

Customers Also Bought



TE Part #650470-5
096 EURO TYPE R PIN ST ASSY



TE Part #2-1879132-1
RN 0402 15K 0.1% 10PPM 5K RL



TE Part #7-1879133-8
RN 0603 5K62 0.1% 10PPM 1K RL




TE Part #8-1879213-9
CPF 0402 249R 0.1% 25PPM 1K RL







TE Part #3-1879233-4
[SMW5 2R4 5%](#)



TE Part #2176304-1
[RP 1E 0.1W 10R 0.1% 25PPM 5K RL](#)




TE Part #3-2176304-0
[RP 1E 0.1W 20R 0.1% 25PPM 5K RL](#)



TE Part #5-2176364-6
[RQ 0402 17K4 0.1% 10PPM 5K RL](#)



TE Part #3-2176369-9
[RQ 0603 100R 0.1% 10PPM 5K RL](#)



TE Part #3-2176370-6
[RQ 0603 1K0 0.1% 10PPM 5K RL](#)

Documents

Product Drawings

[DET SW4.7X3.8X2.3 GW VERT. NO AG RL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2331364-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2331364-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2331364-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[JJ Series Detector Switches Data Sheet](#)

English