



#### **DUAL SURFACE MOUNT SCHOTTKY BARRIER DIODE**

### **Features**

- Very Low Forward Voltage Drop
- Guard Ring Construction for Transient Protection
- High Conductance
- Lead, Halogen and Antimony Free, RoHS Compliant "Green" Device (Notes 4, 5 and 6)


## **Mechanical Data**

- Case: SOT-23
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0

SDM40E20LA

2

- Moisture Sensitivity: Level 1 per J-STD-020D
- Polarity: See Diagram
- Leads: Solderable per MIL-STD-202, Method 208
- Terminals: SDM40E20L/S/A Finish Matte Tin Finish annealed over Alloy 42 leadframe. SDM40E20LC Finish — Matte Tin Finish annealed over CDA194 leadframe.
- Marking Information: See Page 2
- Ordering Information: See Page 2
- Weight: 0.008 grams (approximate)



# **Maximum Ratings** @T<sub>A</sub> = 25°C unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load. For capacitance load, derate current by 20%

8.3ms single half sine-wave superimposed on rated load

Characteristic Value Unit **Symbol** Peak Repetitive Reverse Voltage  $V_{RRM}$ Working Peak Reverse Voltage 20  $V_{RWM}$ DC Blocking Voltage  $V_{\mathsf{R}}$ RMS Reverse Voltage 14 V<sub>R(RMS)</sub> Forward Continuous Current (Note 1) 0.4 Α  $I_{FM}$ Non-Repetitive Peak Forward Surge Current

 $I_{FSM}$ 

### Thermal Characteristics

Characteristic		Symbol	Value	Unit
Power Dissipation	(Note 1)	<b>D</b>	225	mW
	(Note 2)	$P_{D}$	300	IIIVV
Typical Thermal Resistance Junction to Ambient	(Note 1)	6	444	°C/W
	(Note 2)	$R_{ heta JA}$	333	-C/VV
Operating and Storage Temperature Range		T <sub>J</sub> , T <sub>STG</sub>	-65 to +125	°C

# **Electrical Characteristics** @T<sub>A</sub> = 25°C unless otherwise specified


Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
Reverse Breakdown Voltage (Note 3)	$V_{(BR)R}$	20	_	_	V	$I_R = 0.5 \text{mA}$
Forward Voltage Drop	VF	_	_	0.310	· · · · · · · · · · · · · · · · · · ·	$I_F = 0.1A$
Polward Voltage Drop		_	_	0.430		$I_F = 0.5A$
Leakage Current (Note 3)	1-	_	_	100		$V_R = 10V$
Leakage Current (Note 3)	IR	_	_	250		$V_R = 20V$
Total Capacitance	C <sub>T</sub>	_	120	_	pF	$f = 1MHz, V_R = 0VDC$

#### Notes:

- 1. Device mounted on FR-5 1.0 x 0.75 x 0.062 inch PCB pad layout.
- Device mounted on Alumina PCB, 0.4 inch x 0.3 inch x 0.024 inch pad layout.
- Short duration pulse test used to minimize self-heating effect.
- No purposefully added lead. Halogen and Antimony Free.
- 5. Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead\_free/index.php.
- 6. Product manufactured with Green Molding Compound and does not contain Halogens or Sb<sub>2</sub>O<sub>3</sub> Fire Retardants.

Α








Fig. 3 Total Capacitance vs. Reverse Voltage, Per Element




Fig. 2 Typical Reverse Characteristics, Per Element





Fig. 4 Forward Current Derating Curve, Per Element

# Ordering Information (Note 7)

Part Number	Case	Packaging
SDM40E20LS-7-F	SOT-23	3000/Tape & Reel
SDM40E20LC-7	SOT-23	3000/Tape & Reel
SDM40E20LA-7	SOT-23	3000/Tape & Reel


Notes: 7. For packaging details, go to our website at http://www.diodes.com/datasheets/ap02007.pdf.

### **Marking Information**






# **Package Outline Dimensions**



SOT-23				
Dim	Min	Max		
Α	0.37	0.51		
В	1.20	1.40		
С	2.30	2.50		
D	0.89	1.03		
F	0.45	0.60		
G	1.78	2.05		
Н	2.80	3.00		
J	0.013	0.10		
K	0.903	1.10		
L	0.45	0.61		
M	0.085	0.180		
α	0°	8°		
All Dimensions in mm				

# **Suggested Pad Layout**



Dimensions	Value (in mm)
Z	2.9
Х	0.8
Y	0.9
С	2.0
E	1.35

### IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

### LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.