



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

45U 2-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: **SR2POST**



Highlights

- 45U 2-post open frame rack
- Black aluminum with round threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR2POST
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty information
- Owner's Manual

Description

Tripp Lite's SR2POST 2-Post SmartRack Open Frame Rack is an economical way to accommodate 45U of rack space for 19-inch rack mount applications where space is at a premium. Its heavy-duty, aluminum construction can safely support 800 lbs. of rackmount equipment. The black, textured power coat finish makes it resistant to scratching while giving it a classic, attractive appearance. The SR2POST is easy to install due to a self-squaring design combined with numbered mounting holes and bolt down provisions. Only standard hand tools are required for installation (9/16" wrench and 9/16" socket/ratchet). Multiple units can be bolted together side by side for easy expansion or customization when required. The SR2POST 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, DIN 41494 and RoHS, and is backed by a 5-year warranty.

Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

SELECTOR	
Selector Type	RACK EQUIPMENT
General Info	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Group	RACKS
TAA Compliant	No
OVERVIEW	
Style	2-Post
Rack Type	Open-Frame
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	4.8
Installed Whole System Maximum Rack Depth (cm)	12.19
Rack Height (U Spaces)	45
Shipping Dimensions (hwd / in.)	7 x 3 x 85
Shipping Dimensions (hwd / cm)	17.78 x 7.62 x 215.9
Shipping Weight (lbs.)	29
Shipping Weight (kg)	13.15
Unit Dimensions (hwd / in.)	84 x 20.3 x 4.75
Unit Weight (lbs.)	29
Unit Weight (kg)	13.15
Unit Dimensions (cm)	213.36 x 51.56 x 12.07
Color	Black
Weight Capacity - Stationary (lbs.)	800
Weight Capacity - Stationary (kg)	362.9
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.