




10 9 8 7 6 5 4 3 2 1

F


E

D

C




B

A



SPECIFICATIONS:

- Material:
 - Body: PA66
 - Terminal: Brass
- Wire range: N/A
- Electrical rating: 300V, 8A.
- Max Torque: N/A.
- Wire strip length: N/A.
- Operating temperature: -40C to +105C.
- $A = (N \times P) + 1.39\text{MM}$
- $B = (N - 1) \times P$
- $P \text{ (PITCH)} = 3.81\text{MM} (.150")$.
- N = Number of positions available 2 through 20.



MOVED MARKING PER AS MFG EC NO: IPG2014-0700 DRAWN BY: DRUMRSTONE CHKD BY: RUPERT APPR: JF MURPHY B	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY LROTHAUS	DATE 12/6/05	TITLE 3.81MM, EURO HEADER VERTICAL, CLOSED END		
				4 PLACES	± ---	± ---	CHECKED BY C. YORK	DATE 01/06/06			
				3 PLACES	± ---	± .005	APPROVED BY DATE		MOLEX MOLEX INCORPORATED		
				2 PLACES	± 0.13	± .01					
				1 PLACE	± 0.3	± ---	MATERIAL NO. DOCUMENT NO.		SD-39511-001		
				ANGULAR ± 2 °							
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE SHEET 2		SHEET NO. 1 OF 2		
							SIZE B				
							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

9 8 7 6 5 4 3 2 1

		Material Numbers												Dimensional Information			
		Black						Green									
		100% Tin			30 u" Gold			100% Tin			30 u" Gold						
		Circuit Size	Printing Options			Printing Options			Printing Options			Printing Options			Dim. A		Dim. B
None	10/W		11/W	None	10/W	11/W	None	10/W	11/W	None	10/W	11/W	mm	inch	mm	inch	
Description																	
3.81mm, Euro Header, Vertical	2	395111002	395111302	395111402	395111502	395111602	395111902	395116002	395116302	395116402	395116502	395116602	395116902	9.01	0.355	3.91	0.150
3.81mm, Euro Header, Vertical	3	395111003	395111303	395111403	395111503	395111603	395111903	395116003	395116303	395116403	395116503	395116603	395116903	12.82	0.505	7.62	0.300
3.81mm, Euro Header, Vertical	4	395111004	395111304	395111404	395111504	395111604	395111904	395116004	395116304	395116404	395116504	395116604	395116904	16.63	0.653	11.43	0.450
3.81mm, Euro Header, Vertical	5	395111005	395111305	395111405	395111505	395111605	395111905	395116005	395116305	395116405	395116505	395116605	395116905	20.44	0.805	15.24	0.600
3.81mm, Euro Header, Vertical	6	395111006	395111306	395111406	395111506	395111606	395111906	395116006	395116306	395116406	395116506	395116606	395116906	24.25	0.955	19.05	0.750
3.81mm, Euro Header, Vertical	7	395111007	395111307	395111407	395111507	395111607	395111907	395116007	395116307	395116407	395116507	395116607	395116907	28.06	1.105	22.96	0.900
3.81mm, Euro Header, Vertical	8	395111008	395111308	395111408	395111508	395111608	395111908	395116008	395116308	395116408	395116508	395116608	395116908	31.87	1.255	26.67	1.050
3.81mm, Euro Header, Vertical	9	395111009	395111309	395111409	395111509	395111609	395111909	395116009	395116309	395116409	395116509	395116609	395116909	35.68	1.405	30.48	1.200
3.81mm, Euro Header, Vertical	10	395111010	395111310	395111410	395111510	395111610	395111910	395116010	395116310	395116410	395116510	395116610	395116910	39.49	1.555	34.29	1.350
3.81mm, Euro Header, Vertical	11	395111011	395111311	395111411	395111511	395111611	395111911	395116011	395116311	395116411	395116511	395116611	395116911	43.30	1.705	38.10	1.500
3.81mm, Euro Header, Vertical	12	395111012	395111312	395111412	395111512	395111612	395111912	395116012	395116312	395116412	395116512	395116612	395116912	47.11	1.855	41.91	1.650
3.81mm, Euro Header, Vertical	13	395111013	395111313	395111413	395111513	395111613	395111913	395116013	395116313	395116413	395116513	395116613	395116913	50.92	2.005	45.72	1.800
3.81mm, Euro Header, Vertical	14	395111014	395111314	395111414	395111514	395111614	395111914	395116014	395116314	395116414	395116514	395116614	395116914	54.73	2.155	49.53	1.950
3.81mm, Euro Header, Vertical	15	395111015	395111315	395111415	395111515	395111615	395111915	395116015	395116315	395116415	395116515	395116615	395116915	58.54	2.305	53.34	2.100
3.81mm, Euro Header, Vertical	16	395111016	395111316	395111416	395111516	395111616	395111916	395116016	395116316	395116416	395116516	395116616	395116916	62.35	2.455	57.15	2.250
3.81mm, Euro Header, Vertical	17	395111017	395111317	395111417	395111517	395111617	395111917	395116017	395116317	395116417	395116517	395116617	395116917	66.16	2.605	60.96	2.400
3.81mm, Euro Header, Vertical	18	395111018	395111318	395111418	395111518	395111618	395111918	395116018	395116318	395116418	395116518	395116618	395116918	69.97	2.755	64.77	2.550
3.81mm, Euro Header, Vertical	19	395111019	395111319	395111419	395111519	395111619	395111919	395116019	395116319	395116419	395116519	395116619	395116919	73.78	2.905	68.58	2.700
3.81mm, Euro Header, Vertical	20	395111020	395111320	395111420	395111520	395111620	395111920	395116020	395116320	395116420	395116520	395116620	395116920	77.59	3.055	72.39	2.850

SEE SHEET 1

EC NO: IPG2014-0700

DRWNR:STONE

CHKD:RUPERT

APPR:JFURPHY

2013/10/17

2013/10/21

2013/11/22

QUALITY SYMBOLS

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.3	± ---
0 PLACE	±	±

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM/IN

DRAWN BY	DATE
LROTHAUS	12/6/05
CHECKED BY	DATE
C. YORK	01/06/06
APPROVED BY	DATE

SCALE

1:1

DESIGN UNITS

INCH

THIRD ANGLE PROJECTION

TITLE

3.81MM, EURO HEADER VERTICAL, CLOSED END

molex

MATERIAL NO.

SEE CHART

DOCUMENT NO.

SD-39511-001

SHEET NO.

2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION