


E-8051201S

DWG. NO.

SYM	DCN NO.	DESCRIPTION	DATE	DRAWN	CHECKED	APP' D	APP' D



DESCRIPTION	APPLICABLE WIRE		AWG# MARK
	WIRE SIZE	OUTER DIA. OF INSUL.	
D02-22-22S-10000	AWG#22~24	1.3 DIA. MAX.	22
D02-22-26S-10000	AWG#26~28	1.1 DIA. MAX.	26


NOTE 1. CONTACT TO BE SUPPLIED IN REELED FORM.

(10,000 CONTACT/REEL)

2. NUMBER OF CONTACTS TO BE SHOWN ON THIS PORTION.

3. LABEL SHOWING PART NUMBER & Q'TY TO BE PUT ON THIS PORTION.

DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON: (INCHES)	
DIMENSION	ANGLES
. ± 0.3	$X^\circ \pm$
.X ± 0.3	$X^\circ X' \pm$
.XX $\pm$	CONCENTRICITY
.XXX $\pm$	WITHIN T. I. R.



3	SOCKET CONTACT	10000	COPPER ALLOY	GOLD OVER NICKEL	
2	PAPER TAPE	1	PAPER		
1	MAGAZINE	1	PAPER		
ITEM	DESCRIPTION	Q' TY	MATERIAL	FINISH	REMARKS
REFERENCE DOCUMENT		DATE	SCALE	JAE-CONNECTOR.COM	
JACS-3050-2		30. OCT. ' 90	10:1	JAE AVIATION ELECTRONICS INDUSTRY, LTD.	
MATERIAL		DRAWN	TITLE		
		H. KATO	D02-22-22S-10000		
		CHECKED	D02-22-26S-10000		
		O. OTSUKA			
TREATMENT		APP' D	SERIES		
		Y. NISHINO	D02		
FINISH		APP' D	DWG. NO.		
			SJ021508-E		

MUSASHINO, AKISHIMA-SHI
TOKYO, JAPAN

DWG. NO.

SJ021508-E

CDS-1201

SIZE A3

DOF-116A

0 10 20 30 40 50 60 70 80 90 100