
samtec



SO SERIES


PRECISION BOARD STACKING STANDOFF

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SO

Material:
Aluminum
Locking Compound:
Nylon


APPLICATIONS



See QMS/QFS Series SUMIT™ & PCI/104-Express™ connectors

Requires Standoff SO-1524-03-01-02-L 15,24mm board spacing. Connectors designed to not fully seat when mated.

APPLICATIONS





RUGGEDIZED by SAMTEC
- Precision machined
- Locking compound

ALSO AVAILABLE (MOQ Required)

- Other heights
- Stainless Steel
- Locking compound removed
- Other materials and threading
- No Hardware

Contact Samtec.

SO	–	BOARD STACKER	–	LEAD STYLE	–	THREAD STYLE	–	01	–	L

Specify BOARD STACKER from chart


LEAD STYLE
–01 = Female Thread/Press-In (–0515 thru –0865 only)
–02 = Male/Male Thread (–0515 and –1115 thru –2515 only)
–03 = Male/Female Thread (-0815 thru –2515 only)
–05 = Female/Female Thread (–1524 thru –2515 only)

THREAD STYLE
–01 = #4-40 Thread
–02 = M3 x 0.5 Thread

01

–L = –02 & –03 Lead Style thread locking compound (Leave blank for –01 Lead Style)

BOARD STACKER	A	BOARD STACK HEIGHT
–0515	(5,15) .203	5 mm
–0715	(7,15) .282	7 mm
–0815	(8,15) .321	8 mm
–0865	(8,65) .341	8,5 mm
–1115	(11,15) .439	11 mm
–1215	(12,15) .478	12 mm
–1524	(15,24) .600	15,24 mm
–1615	(16,15) .636	16 mm
–1890	(18,90) .744	18,75 mm
–1915	(19,15) .754	19 mm
–2515	(25,15) .990	25 mm



Components are to be packaged in separate bags unassembled.

Notes:
Standoffs are designed, 0,15 mm longer than connector stack heights to allow for processing variables.

Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.