

## CD4023BC

### Buffered Triple 3-Input NAND Gate

#### General Description

These triple gates are monolithic complementary MOS (CMOS) integrated circuits constructed with N- and P-channel enhancement mode transistors. They have equal source and sink current capabilities and conform to standard B series output drive. The devices also have buffered outputs which improve transfer characteristics by providing very high gain. All inputs are protected against static discharge with diodes to  $V_{DD}$  and  $V_{SS}$ .

#### Features


- Wide supply voltage range: 3.0V to 15V
- High noise immunity:  $0.45 V_{DD}$  (typ)
- Low power TTL compatibility:  
fan out of 2 driving 74L or 1 driving 74LS
- 5V–10V–15V parametric ratings
- Symmetrical output characteristics
- Maximum input leakage 1  $\mu A$  at 15V over full temperature range

#### Ordering Code:


| Order Number | Package Number | Package Description                                                       |
|--------------|----------------|---------------------------------------------------------------------------|
| CD4023BCM    | M14B           | 14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300 Wide |
| CD4023BCS    | M14D           | 14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide             |
| CD4023BCN    | N14A           | 14-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300 Wide     |

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### Connection Diagram



#### Block Diagram



$1/3$  Device Shown

\*All Inputs Protected by Standard CMOS Input Protection Circuit.

**Absolute Maximum Ratings**(Note 1)

(Note 2)

|                                |                                                 |
|--------------------------------|-------------------------------------------------|
| DC Supply Voltage ( $V_{DD}$ ) | $-0.5 V_{DC}$ to $+18 V_{DC}$                   |
| Input Voltage ( $V_{IN}$ )     | $-0.5 V_{DC}$ to $V_{DD}+0.5 V_{DC}$            |
| Storage Temp. Range ( $T_S$ )  | $-65^{\circ}\text{C}$ to $+150^{\circ}\text{C}$ |
| Power Dissipation ( $P_D$ )    |                                                 |
| Dual-In-Line                   | 700 mW                                          |
| Small Outline                  | 500 mW                                          |
| Lead Temperature ( $T_L$ )     |                                                 |
| (Soldering, 10 seconds)        | $260^{\circ}\text{C}$                           |

**Recommended Operating Conditions**

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| DC Supply Voltage ( $V_{DD}$ )        | $5 V_{DC}$ to $15 V_{DC}$                      |
| Input Voltage ( $V_{IN}$ )            | $0 V_{DC}$ to $V_{DD} V_{DC}$                  |
| Operating Temperature Range ( $T_A$ ) | $-40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ |

**Note 1:** "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed; they are not meant to imply that the devices should be operated at these limits. The table of "Recommended Operating Conditions" and "Electrical Characteristics" provides conditions for actual device operation.

**Note 2:**  $V_{SS} = 0V$  unless otherwise specified.

**DC Electrical Characteristics** (Note 3)

| Symbol   | Parameter                             | Conditions               | $-40^{\circ}\text{C}$ |      | $+25^{\circ}\text{C}$ |            |      | $+85^{\circ}\text{C}$ |      | Units         |
|----------|---------------------------------------|--------------------------|-----------------------|------|-----------------------|------------|------|-----------------------|------|---------------|
|          |                                       |                          | Min                   | Typ  | Min                   | Typ        | Max  | Min                   | Max  |               |
| $I_{DD}$ | Quiescent Device Current              | $V_{DD} = 5V$            |                       | 1.0  |                       | 0.004      | 1.0  |                       | 7.5  | $\mu\text{A}$ |
|          |                                       | $V_{DD} = 10V$           |                       | 2.0  |                       | 0.005      | 2.0  |                       | 15   |               |
|          |                                       | $V_{DD} = 15V$           |                       | 4.0  |                       | 0.006      | 4.0  |                       | 30   |               |
| $V_{OL}$ | LOW Level Output Voltage              | $V_{DD} = 5V$            |                       | 0.05 |                       | 0          | 0.05 |                       | 0.05 | V             |
|          |                                       | $V_{DD} = 10V$           |                       | 0.05 |                       | 0          | 0.05 |                       | 0.05 |               |
|          |                                       | $V_{DD} = 15V$           |                       | 0.05 |                       | 0          | 0.05 |                       | 0.05 |               |
| $V_{OH}$ | HIGH Level Output Voltage             | $V_{DD} = 5V$            | 4.95                  |      | 4.95                  | 5          |      | 4.95                  |      | V             |
|          |                                       | $V_{DD} = 10V$           | 9.95                  |      | 9.95                  | 10         |      | 9.95                  |      |               |
|          |                                       | $V_{DD} = 15V$           | 14.95                 |      | 14.95                 | 15         |      | 14.95                 |      |               |
| $V_{IL}$ | LOW Level Input Voltage               | $V_{DD}=5V, V_O=4.5V$    |                       | 1.5  |                       | 2          | 1.5  |                       | 1.5  | V             |
|          |                                       | $V_{DD}=10V, V_O=9.0V$   |                       | 3.0  |                       | 4          | 3.0  |                       | 3.0  |               |
|          |                                       | $V_{DD}=15V, V_O=13.5V$  |                       | 4.0  |                       | 6          | 4.0  |                       | 4.0  |               |
| $V_{IH}$ | HIGH Level Input Voltage              | $V_{DD}=5V, V_O=0.5V$    | 3.5                   |      | 3.5                   | 3          |      | 3.5                   |      | V             |
|          |                                       | $V_{DD}=10V, V_O=1.0V$   | 7.0                   |      | 7.0                   | 6          |      | 7.0                   |      |               |
|          |                                       | $V_{DD}=15V, V_O=1.5V$   | 11.0                  |      | 11.0                  | 9          |      | 11.0                  |      |               |
| $I_{OL}$ | LOW Level Output Current<br>(Note 4)  | $V_{DD}=5V, V_O=0.4V$    | 0.52                  |      | 0.44                  | 0.88       |      | 0.36                  |      | mA            |
|          |                                       | $V_{DD}=10V, V_O=0.5V$   | 1.3                   |      | 1.1                   | 2.2        |      | 0.90                  |      |               |
|          |                                       | $V_{DD}=15V, V_O=1.5V$   | 3.6                   |      | 3.0                   | 8          |      | 2.4                   |      |               |
| $I_{OH}$ | HIGH Level Output Current<br>(Note 4) | $V_{DD}=5V, V_O=4.6V$    | -0.52                 |      | -0.44                 | -0.88      |      | -0.36                 |      | mA            |
|          |                                       | $V_{DD}=10V, V_O=9.5V$   | -1.3                  |      | -1.1                  | -2.2       |      | -0.90                 |      |               |
|          |                                       | $V_{DD}=15V, V_O=13.5V$  | -3.6                  |      | -3.0                  | -8         |      | -2.4                  |      |               |
| $I_{IN}$ | Input Current                         | $V_{DD}=15V, V_{IN}=0V$  |                       | -0.3 |                       | $-10^{-5}$ | -0.3 |                       | -1.0 | $\mu\text{A}$ |
|          |                                       | $V_{DD}=15V, V_{IN}=15V$ |                       | 0.3  |                       | $10^{-5}$  | 0.3  |                       | 1.0  |               |

**Note 3:**  $V_{SS} = 0V$  unless otherwise specified.

**Note 4:**  $I_{OH}$  and  $I_{OL}$  are tested one output at a time.


**AC Electrical Characteristics** (Note 5) $T_A = 25^\circ\text{C}$ ,  $C_L = 50\text{ pF}$ ,  $R_L = 200\text{ k}\Omega$ , unless otherwise specified

| Symbol                   | Parameter                            | Conditions                                                             | Min | Typ             | Max              | Units |
|--------------------------|--------------------------------------|------------------------------------------------------------------------|-----|-----------------|------------------|-------|
| $t_{PHL}$                | Propagation Delay, HIGH-to-LOW Level | $V_{DD} = 5\text{V}$<br>$V_{DD} = 10\text{V}$<br>$V_{DD} = 15\text{V}$ |     | 130<br>60<br>40 | 250<br>100<br>70 | ns    |
| $t_{PLH}$                | Propagation Delay, LOW-to-HIGH Level | $V_{DD} = 5\text{V}$<br>$V_{DD} = 10\text{V}$<br>$V_{DD} = 15\text{V}$ |     | 110<br>50<br>35 | 250<br>100<br>70 | ns    |
| $t_{THL}$ ,<br>$t_{TLH}$ | Transition Time                      | $V_{DD} = 5\text{V}$<br>$V_{DD} = 10\text{V}$<br>$V_{DD} = 15\text{V}$ |     | 90<br>50<br>40  | 200<br>100<br>80 | ns    |
| $C_{IN}$                 | Average Input Capacitance            | Any Input                                                              |     | 5               | 7.5              | pF    |
| $C_{PD}$                 | Power Dissipation Capacity (Note 6)  | Any Gate                                                               |     | 17              |                  | pF    |


**Note 5:** AC Parameters are guaranteed by DC correlated testing.**Note 6:**  $C_{PD}$  determines the no load AC power consumption of any CMOS device.

For complete explanation, see Family Characteristics Application Note AN-90.

# Physical Dimensions inches (millimeters) unless otherwise noted




**14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300 Wide Package Number M14B**



**14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide Package Number M14D**

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



14-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300 Wide  
Package Number N14A

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)