







RECOMMENDED PCB LAYOUT

- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: 0.0 ± 0.4
 0.00 ± 0.25
 3. TERM. NOS. FOR REF. ONLY
 4. RATING: 50mA, @12V DC
 5. TRAVEL: 0.25 ± 0.1 mm
 6. OPERATING FORCE: 250 ± 50 gf
 7. CONTACT RESISTANCE: 100m ohms max.
 8. ELECTRICAL LIFE: 100,000 CYCLES MIN.
 9. INSULATION RESISTANCE: 100M ohms min.
 10. DIELECTRIC STRENGTH: 250V RMS MIN.
 11. OPERATING TEMP.: -30°C to $+85^{\circ}\text{C}$
 12. ▲ DESIGNATE MAJOR DIMENSIONS



CIRCUIT: SPST
CONTACT CONFIGURATION

E-SWITCH®			
TITLE			
TL 1105A F250 Q			
SCALE			
4:1			
DATE			
8/14/96			
DR			
MM			
DWG			
P010012			
REV			
C			
REV.			
ECN NO.			
DESCRIPTION			
DATE			
CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT			
IS PROPRIETARY TO E-SWITCH AND IS			
NOT TO BE COPIED OR TRANSMERRED			