



SBS817

Schottky Barrier Diode 15V, 2A, Low VF, Non-Monolithic Dual EMH8 Common Cathode

ON Semiconductor®

http://onsemi.com

Applications

- High frequency rectification (switching regulators, converters, choppers)

Features

- Low switching noise
- Low forward voltage (IF=2.0A, VF max=0.46V)
- Ultrasmall package permitting applied sets to be small and slim (Mounting height 0.75mm)

Specifications

Absolute Maximum Ratings at Ta=25°C (Value per element)


Parameter	Symbol	Conditions	Ratings	Unit
Repetitive Peak Reverse Voltage	V _{RRM}		15	V
Nonrepetitive Peak Reverse Surge Voltage	V _{RSM}		15	V
Average Output Current	I _O		2.0	A
Surge Forward Current	I _{FSM}	50Hz sine wave, 1 cycle	20	A
Junction Temperature	T _j		-55 to +125	°C
Storage Temperature	T _{stg}		-55 to +125	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions

unit : mm (typ)


7045-004




Product & Package Information

- Package : EMH8
- JEITA, JEDEC : -
- Minimum Packing Quantity : 3,000 pcs./reel


Packing Type : TL



Marking




Electrical Connection



Electrical Characteristics at $T_a=25^\circ\text{C}$ (Value per element)



Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Reverse Voltage	V_R	$I_R=1\text{mA}$	15			V
Forward Voltage	V_F1	$I_F=1.0\text{A}$		0.33	0.39	V
	V_F2	$I_F=2.0\text{A}$		0.39	0.46	V
Reverse Current	I_R	$V_R=7.5\text{V}$			300	μA
Interterminal Capacitance	C	$V_R=10\text{V}, f=1\text{MHz}$		35		pF
Reverse Recovery Time	t_{rr}	$I_F=I_R=100\text{mA}$, See specified Test Circuit.			10	ns
Thermal Resistance	$R_{th(j-a)}$	When mounted on ceramic substrate (900mm ² x 0.8mm)		65		$^\circ\text{C} / \text{W}$






*: The absolute maximum ratings and electrical characteristics refer to those between Terminal 1 and Terminal 7 (or 8), and between Terminal 3 and Terminal 5 (or 6).

 t_{rr} Test Circuit

Ordering Information

Device	Package	Shipping	memo
SBS817-TL-E	EMH8	3,000pcs./reel	Pb Free






Embossed Taping Specification

SBS817-TL-E

1. Packing Format

Package Name	Carrier Tape Type	Maximum Number of devices contained (pcs)			Packing format	
		Reel	Inner box	Outer box	Inner BOX (C-1)	Outer BOX (A-7)
EMH8	MCP4	3,000	15,000	90,000	5 reels contained Dimensions:mm (external) 183×72×185	6 inner boxes contained Dimensions:mm (external) 440×195×210

Packing method

Type No.
LOT No.
Quantity
Origin

Reel label, Inner box label

(unit:mm)

6.9
4.3
8.0
2.0
1.0

Outer box label

It is a label at the time of factory shipments.
The form of a label may change in physical distribution process.

TYPE CODE	XXXXXXXXXXXX
TYPE	○○○○○○○○
QTY	0.000 PCS (1)
LOT	○○○○○○○○
PACKAGE	○○○○○○○○
SPECIAL	XXXXXXXXXXXX
ASSEMBLY	**20722005310C*
DIFFUSION	****(****)


NOTE (1)

The LEAD FREE * description shows that the surface treatment of the terminal is lead free.


Label	JEITA Phase
LEAD FREE 3	JEITA Phase 3A
LEAD FREE 4	JEITA Phase 3

2. Taping configuration

2-1. Carrier tape size (unit:mm)




2-2. Device placement direction




Those with pin 1 index on the feed hole side.....TL

Outline Drawing

SBS817-TL-E



Land Pattern Example



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ON Semiconductor](#):

[SBS817-TL-E](#)