

PRINT DIST



	180	39	49.53	49	62.23	—	115.57	51.53	64.23	117.57	120.66	128.19	125.54		▲	-8
E	160	29	36.83	49	62.23	—	102.07	38.83	64.23	104.07	107.96	115.49	112.84			7
	140	29	36.83	39	49.53	—	90.17	38.83	51.53	92.17	95.26	102.79	100.14			-6
	120	19	24.13	39	49.53	—	77.47	26.13	51.53	79.47	82.56	90.09	87.44			-5
	100	—	—	—	—	49	62.23	—	—	64.23	67.32	74.85	72.2			-4
	80	—	—	—	—	39	49.53	—	—	51.53	54.62	62.15	59.5			-3
	60	—	—	—	—	29	36.83	—	—	38.83	41.92	49.45	46.8			-2
	40	—	—	—	—	19	24.13	—	—	26.13	29.22	36.75	34.1			-1
Pos.	a	A	b	B	c	C	D	E	F	G	H	J				P/N

P1	REVISED PER ECR-12-013273	28MAR2013	K.M	E.T
P	ECO-11-005030	23MAR11	RK	HMI
LTR	DESCRIPTION	DATE	DWN	APV

		 TE Connectivity	
WIRE RANGE mm ² (AWG -)		INSULATION DIA - mmφ	
MATERIAL ①		FINISH ②	
		NAME AMP FH CONNECTOR RECEPTACLE WITH RETENTION LEG (HORIZONTAL)	
		GENERAL TOLERANCE 0<W<10 : ±0.2 10<W<30 : ±0.25 30<W<100 : ±0.3 ANGLES : ±3°	
		SIZE B	LOC J
		NUMBER C- 5176379	
DE. T. KAWAMAE 09JUN04		SCALE NTS	REV. P1
CHK. TENOMOTO 09JUN04 APP. TENOMOTO 09JUN04		SHEET 1 OF 1	

CUSTOMER DRAWING

② 表面仕上げ;
 コントクト: 全面ニッケル下地めっき
 接触部金めっき、脚部すずめっき
 リテンションレグ: ニッケル下地めっきにすずめっき

鉛フリー
LEAD FREE