




Preliminary Datasheet


Dimensions mm[inch]

 tolerances acc. to DIN ISO 2768-m
 Toleranzen gem. DIN ISO 2768-m


Layout

 Top view
 Draufsicht


Isometric

 Scale 2:1
 Maßstab 2:1


Marking

 according to EN60062/factory code
 gem. EN60062/Fertigungsstätte

MEDER electronic
SIL12-1B90-71D YW/P

Coil Data at 20 °C	Conditions	Min	Typ	Max	Unit
Coil resistance		900	1.000	1.100	Ohm
Coil voltage			12		VDC
Rated power			144		mW
Coil current			12		mA
Thermal resistance	max. Relay temperature = operating temperature + self heating		92		K/W
Pull-In voltage				8,4	VDC
Drop-Out voltage		1,8			VDC

Contact Data 94	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			100	V
Switching current	DC or Peak AC			0,2	A
Carry current	DC or Peak AC			0,5	A
Contact resistance static	Measured with 40% overdrive Start Value			150	mOhm
Contact resistance dynamic	Maximum value 1,5 ms after excitation Start Value			200	mOhm
Insulation resistance	RH <45 %, 100 V test voltage	1			GOhm
Breakdown voltage (<21 AT)	according to EN 60255-5	150			VDC
Operate time incl. bounce	measured with 40% overdrive			2	ms
Release time	measured with no coil excitation			2	ms
Capacity	@ 10 kHz across open switch		1,5		pF

Special Product Data	Conditions	Min	Typ	Max	Unit
Dielectric Strength Coil/Contact	according to EN 60255-5	1,5			kV DC
Insulation resistance Coil/Contact	RH <45%, 200 VDC measuring voltage	100			GOhm
Housing material		epoxy resin			
Connection pins		FeNi42, tin plated			
Approval		UL-File Nr. NRNT2.E156887 / NRNT8.E156887			
Reach / RoHS conformity		yes			



*Products for
Homomax...*

Europe: +49 / 7731 8399 0 | Email: info@meder.com
USA: +1 / 508 295 0771 | Email: salesusa@meder.com
Asia: +852 / 2955 1682 | Email: salesasia@meder.com

Item No.:
3312190171
Item:
SIL12-1B90-71D

Preliminary Datasheet

Environmental data	Conditions	Min	Typ	Max	Unit
Shock	1/2 sine, duration 11ms, in 3 axis			50	g
Vibration	from 10 - 2000 Hz			20	g
Operating temperature		-20		70	°C
Storage temperature		-35		95	°C
Soldering temperature	wave soldering max. 5 sec.			260	°C
Washability		fully sealed			

General data	Conditions	Min	Typ	Max	Unit
Packaging		tube per 25 pcs.			

Modifications in the sense of technical progress are reserved

Designed at: 08.08.06 Designed by: KMUELLER
Last Change at: 14.11.12 Last Change by: THAUKE

Approval at: 31.10.08 Approval by: KOLBRICH
Approval at: Approval by:

Version: 5