









NOTES:

- MATERIALS:
HOUSING: POLYETHERIMIDE PER ASTM-D5205
GROMMET: SILICONE RUBBER PER A-A-59588
THREADED INSERT: STAINLESS STEEL
- OPERATING RANGE:
TEMPERATURE: -65 °C TO 125 °C
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS AT
SEA LEVEL AND 500 VRMS AT 80,000 FT. ALTITUDE
VIBRATION: MIL-STD-202, METHOD 204, TEST CONDITION G
SHOCK: MIL-STD-202, METHOD 213, TEST CONDITION C
- PART ACCEPTS M39029/92-533 AND M39029/92-535
SOCKET CONTACTS, SIZE 16/16 AND SIZE 12/12.



PART NUMBER TABLE

APCD P/N	HARDWARE PACKAGE	CONTACTS SUPPLIED
JRS310100	NONE	NONE
JRS310101	NONE	YES
JRS310110	YES	NONE
JRS310111	YES	YES



DIMENSIONS		TOLERANCES		PROJECTION		TITLE					
ANSI Y14.5M UNITS: INCHES Pro/E FILE		.XX ±0.01 .XXX ±0.005 ANGLES ±1.0°				Amphenol Pcd SPECIFICATION DRAWING					
ORIGINAL		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA		ENGR		SNAP-IN RELAY SOCKET 3 POLE					
				Frank.Li 07-Apr-08		SIZE B					
				CHKD 5/29/09							
				APPD 5-29-09		DWG NO.		JRS310100		REV -	
						CODE: 58982		SCALE: 2:1		SHEET 1 OF 1	