

GaAs IC High Isolation Positive Control SPDT Switch DC–3.0 GHz



AS177-86


Features

- Positive Voltage Control (0/+3, +5 V)
- High Isolation (50 dB @ 0.9, 1.9 GHz)
- Low DC Power Consumption
- Ideal for GSM, PCS, 3G and ISM 2.4 GHz Applications
- Miniature Low Cost MSOP-10 Plastic Package

Description

The AS177-86 is a GaAs FET IC SPDT switch packaged in a MSOP-10 plastic package for low cost, high isolation commercial applications. Ideal building block for base station dual-band applications where synthesizer isolation is critical. Use in conjunction with the AS165-59 SPST switch to meet GSM synthesizer isolation requirements.

MSOP-10



Electrical Specifications at 25°C (0, +3 V), (0, +5 V)

Parameter ¹	Condition	Frequency ²	Min.	Typ.	Max.	Unit
Insertion Loss ³		DC–1.0 GHz		0.7	0.85	dB
		1.0–2.0 GHz		0.8	1.00	dB
		2.0–3.0 GHz		0.9	1.20	dB
Isolation	J ₁ –J ₂ /J ₁ –J ₃ J ₁ –J ₂ /J ₁ –J ₃	DC–2.0 GHz	44/50	48/55		dB
		2.0–2.5 GHz	41/44	46/50		dB
		2.5–3.0 GHz	34	40		dB
VSWR ⁴		DC–3.0 GHz		1.3:1	1.5:1	

Operating Characteristics at 25°C (0, +5 V)

Parameter	Condition	Frequency	Min.	Typ.	Max.	Unit
Switching Characteristics ⁵	Rise, Fall (10/90% or 90/10% RF)			50		ns
	On, Off (50% CTL to 90/10% RF)			100		ns
	Video Feedthru			25		mV
Input Power for 1 dB Compression	+3 V	0.5–3.0 GHz		+21		dB
	+5 V	0.5–3.0 GHz		+27		dB
Intermodulation Intercept Point (IP3)	Two-tone Input Power +5 dBm					
	+3 V	0.5–3.0 GHz		+41		dBm
	+5 V	0.5–3.0 GHz		+45		dBm
Control Voltages	V _{Low} = 0 to 0.2 V @ 20 μA Max. V _{High} = +3 V @ 100 μA Max. to +5 V @ 200 μA Max. V _S = V _{High} ± 0.2 V					

1. All measurements made in a 50 Ω system, unless otherwise specified.




2. DC = 300 kHz.

3. Insertion loss changes by 0.003 dB/°C.

4. Insertion loss state.

5. Video feedthru measured with 1 ns risetime pulse and 500 MHz bandwidth.


Typical Performance Data (0, +5 V)



Absolute Maximum Ratings

Characteristic	Value
RF Input Power	1 W Max. > 500 MHz 0/+8 V Control
Supply Voltage	+8 V
Control Voltage	-0.2 V, +8 V
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C
Θ _{JC}	25°C/W

Pin Out



Truth Table

V_1	V_2	J_1-J_2	J_1-J_3
0	V_{High}	Isolation	Insertion Loss
V_{High}	0	Insertion Loss	Isolation

$V_{High} = +3\text{ V to }+5\text{ V.}$