



PRODUCT NUMBER	SERIES NAME	PITCH
20020010-CXXXXXXLF	02-350	3.50 mm





N = Number of poles
 Dim A = $N \times 3.5$ [.138]
 Dim B = $(N-1) \times 3.5$ [.138]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]





mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title
F				TERMINAL BLOCK PLUGGABLE PLUG, BACK SIDE HOOK
				dwg no
				20020010
				sheet 2 of 5
				size
				A4
				type
				CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-DXXXXXXLF	02-381	3.81 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)






N = Number of poles
Dim A = $N \times 3.81$ [.150]
Dim B = $(N-1) \times 3.81$ [.150]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.20 [.008]
13-18p	± 0.25 [.010]
19-24p	± 0.30 [.012]



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5 X.X±0.3		TERMINAL BLOCK
				X*±1°	X.XX±0.1	scale	PLUGGABLE PLUG, BACK SIDE HOOK
		dr	JASON HSU	120909		FCI	dwg no
		enr	JASON HSU	120909			sheet 3 of 5 size
		chr	GARY HSIEH	120909			20020010
		appd	JOSEPH HSIA	120909			A4
sheet index	revision sheet						type
							CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-GXXXXXXLF	02-500	5.00 mm



N = Number of poles
Dim A = $N \times 5.0$ [.197]
Dim B = $(N-1) \times 5.0$ [.197]




POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



SECTION P-P


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM [INCH]	title
F				angles	X.±0.5		TERMINAL BLOCK
				linear	X.X±0.3		PLUGGABLE PLUG, BACK SIDE HOOK
				X*±1°	X.XX±0.1	scale	dwg no
		dr	JASON HSU	120909		FCI	sheet 4 of 5
		enr	JASON HSU	120909			20020010
		chr	GARY HSIEH	120909			A4
		appd	JOSEPH HSIA	120909			type
sheet index	revision sheet						CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020010-HXXXXXXLF	02-508	5.08 mm




N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

POLES	TOLERANCE
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



SECTION P-P



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK	
ltr	ecn	no	dr	date				title
F								TERMINAL BLOCK
				angles	$X \pm 0.5$			PLUGGABLE PLUG, BACK SIDE HOOK
				linear	$X.X \pm 0.3$			
				$X' \pm 1'$	$X.XX \pm 0.1$	scale		
			dr	JASON HSU	120909	FCI		
			enr	JASON HSU	120909			
			chr	GARY HSIEH	120909			
			appd	JOSEPH HSIA	120909			
sheet	revision						dwg no	sheet 5 of 5 size
index	sheet						20020010	A4
							type	CUSTOMER Drawing