






FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE

68685 - XXX - LF
LEAD FREE OPTION
PACKAGING OPTIONS OMIT IF NOT REQUIRED.
NO. OF POSITIONS PER ROW
PLATING CODE
BASE PART NUMBER



mat'l. code				surface		tolerance		projection		product family			
				ISO 1302 ✓		ISO 406 ISO 1101				DUBOX			
ltr ecn nodr date				tolerances unless otherwise specified						title			
W	N-005262	SH	2011-8-22	angles	linea	.XX ±.01/.3			DUBOX SING. ROW VERT.				
P	V03-0309	HTB	04/30/03			.XXX ±.005/.13			CARD CONN. ASSEMBLY				
R	V04-0002	HTB	01/06/04	0'±2'	.XXXX ±.0020/.051		scale 4:1						
S	V05-0463	DPU	06/27/05	dr	S. RAMP		02/25/91		dwg no		sheet 1 of 3		size
T	M06-0237	MN	06/19/06	engr	M. HAHN		02/25/91				68685		A3
U	M06-0433	AGS	10/31/06	chr	M. HAHN		02/25/91						
V	M07-0203	MHT	5/01/07	appd	M. HAHN		02/25/91				type		Product
sheet		revision		W	W	W							
Index		sheet		1	2	3							

PRODUCT NO NOTE 8	PLATING CONTACT AREA MIN	PLATING SOLDER TAIL
68685-2XX	15u"/.38u Au OR GXT, OVER 50u"/1.27uNI	100u"/160u" SN 2.54u/4.06u
68685-3XX	30u"/.76u Au OR GXT, OVER 50u"/1.27u NI	100u"/160u" SN 2.54u/4.06u
68685-4XX	100u"/160u" SN 2.54u/4.06u	100u"/160u" SN 2.54u/4.06u
68685-5XX	50u"/1.27u Au OVER 50u"/1.27u NI	100u"/160u" SN 2.54u/4.06u
68685-6XX	30u"/.76u Au OR GXT, OVER 50u"/1.27u NI	100u"/160u" SN 2.54u/4.06u
68685-8XX	30u"/.76u Au OVER 50u"/1.27u NI	100u"/160u" SN 2.54u/4.06u

OBSOLETE

OBSOLETE




FIGURE A

NOTES:

- MATERIAL HOUSING: PPS, COLOR - BLACK, FLAME RETARDANT PER UL-94V-0.
THIS PART WILL WITHSTAND EXPOSURES TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- MATERIAL TERMINAL: PHOSPHOR BRONZE.
- RECOMMENDED APPLICATION DATA:
 - RECOMMENDED HOLE PATTERN IS SHOWN IN FIGURE A.
 - ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA
 - SUGGESTED MATING PIN LENGTH .210±.020/5.33±.51
 - RECOMMENDED PC BOARD THICKNESS: .062/1.58
- FCI, FCI FINAL PART NUMBER AND DATE CODE TO BE MARKED ON TUBE LABEL.
- PREPLATED STAMPED TERMINALS.
- STANDARD TUBE PACKAGE PER BUS-14-097/3.
- PART NUMBER WITH SUFFIX "U" FOR SAWING ONLY.
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENT.

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ISO 1101		product family DUBOX	
ltr ecn nodr date		tolerances unless otherwise specified		title		INCH/MM		DUBOX SING. ROW VERT. CARD CONN. ASSEMBLY	
W		angles	line	.XX ±.01/3		scale 4:1		dwg no	
		0°±2'		.XXX ±.005/.13				sheet 2 of 3	
				.XXXX ±.0020/.051				size	
		dr	S. RAMP	02/25/91				68685	
		enr	M. HAHN	02/25/91				A3	
		chr	M. HAHN	02/25/91					
		appd	M. HAHN	02/25/91					
sheet index		revision sheet						type Product Customer Drawing	

