



Benefits:

- Saving up to 70% air consumption
- Maintenance free – no moving parts
- Simple and easy to operate

**Air Amplifier
Series ZH-X185**

Air Amplifier


■ What is an Air Amplifier?

It is a simple, light, cost effective tool that takes energy from a small volume of compressed air to produce high velocity, high volume, low pressure output airflow.


■ How does it work?

In simple terms: it multiplies the flow. For one unit of air you feed into the device, it creates output flow 4 times greater.

Blowing is possible at a flow rate quadruple that of the supplied air.



Suctioning is possible at a flow rate triple the supplied air.



The Air Amplifier uses the Coanda effect, the phenomena in which a jet flow attaches itself to a nearby surface and remains attached when the surfaces curves away from the initial jet direction. Using a small amount of compressed air as their power source, Air Amplifiers pull in large volumes of surrounding air to produce high volume, high velocity outlet flow.

x4



■ Features


- Energy efficiency – 1:4
- Instant on-off control
- Air driven – no electrical supply required
- It is a flow amplifier not a pressure booster
- It can replace a fan/s

■ Benefits


- Air consumption saving – reduces air consumption for air blows by 70%
- Maintenance free – no moving parts
- Simple and easy to operate
- Quiet
- Safe

Application examples


Blow



Vacuum



Transportation



Air Amplifier – technical details at a glance

RoHS

ZH 20 - B - X185

Passage diameter

10	13 mm
20	21.6 mm
30	30 mm
40	42 mm

Bracket

—	No bracket
B	With bracket

Warning

- Objects that have been sucked in may be discharged with the exhaust air, so make sure the exhaust port is not facing towards people or equipment.
 - Do not use in an environment containing corrosive gases, chemicals, organic solvents, sea water or steam, or where it will come into contact with these fluids.
- ⚠ For safety precautions and common precautions for vacuum equipment, refer to "SMC Product Handling Precautions" (M-E03-3B).


Specifications

Model	ZH10-X185	ZH20-X185	ZH30-X185	ZH40-X185
Body material	Aluminium alloy ^{Note)}			
Seal material	NBR			
Passage diameter	ø13	ø21.6	ø30	ø42
Fluid used	Air			
Supply pressure range	0 ~ 0.7MPa			
Weight [g]	110	430	970	2000
Bracket assembly	ZH-BK1-10-A	ZH-BK1-20-A	ZH-BK1-30-A	ZH-BK1-40-A


Note) Body material in SUS 304 with FKM seals available as special product.

Flow rate characteristics


ZH10-X185




ZH20-X185



ZH30-X185



ZH40-X185




Note 1) Suction flow rate is a theoretical value.

Note 2) The characteristics above show the values when the discharge pressure is atmospheric pressure.


Note 3) If the filter is installed to collect dust in the outlet side piping, make sure it does not cause back pressure.

External Dimensions Drawing

ZH10~20-□-X185



ZH30~40-□-X185



Note) threaded model available as special product.

We love energy-saving products that save money and help the environment!



SMC CORPORATION (Europe)

Austria ☎ +43 (0)22622800
Belgium ☎ +32 (0)33551464
Bulgaria ☎ +359 (0)2807670
Croatia ☎ +385 (0)13707288
Czech Republic ☎ +420 541424611
Denmark ☎ +45 70252900
Estonia ☎ +372 6510370
Finland ☎ +358 207513513
France ☎ +33 (0)164761000
Germany ☎ +49 (0)61034020
Greece ☎ +30 210 2717265
Hungary ☎ +36 23511390
Ireland ☎ +353 (0)14039000
Italy ☎ +39 0292711
Latvia ☎ +371 67817700

www.smc.at
www.smc-pneumatics.be
www.smc.bg
www.smc.hr
www.smc.cz
www.smc.dk.com
www.smc-pneumatics.ee
www.smc.fi
www.smc-france.fr
www.smc-pneumatik.de
www.smc-hellas.gr
www.smc.hu
www.smc-pneumatics.ie
www.smc-italia.it
www.smc-lv

office@smc.at
info@smc-pneumatics.be
office@smc.bg
office@smc.hr
office@smc.cz
smc@smc.dk.com
smc@smc-pneumatics.ee
smc@smc.fi
promotion@smc-france.fr
info@smc-pneumatik.de
sales@smc-hellas.gr
office@smc.hu
sales@smc-pneumatics.ie
mailbox@smc-italia.it
info@smc-lv

Lithuania ☎ +370 5 2308118
Netherlands ☎ +31 (0)205318888
Norway ☎ +47 67129020
Poland ☎ +48 (0)222119616
Portugal ☎ +351 226166570
Romania ☎ +40 213205111
Russia ☎ +7 8127185445
Slovakia ☎ +421 (0)413213212
Slovenia ☎ +386 (0)73885412
Spain ☎ +34 902184100
Sweden ☎ +46 (0)86031200
Switzerland ☎ +41 (0)523963131
Turkey ☎ +90 212 489 0 440
UK ☎ +44 (0)845 121 5122

www.smc.lt
www.smc-pneumatics.nl
www.smc-norge.no
www.smc.pl
www.smc.eu
www.smc-romania.ro
www.smc-pneumatik.ru
www.smc.sk
www.smc.si
www.smc.eu
www.smc.nu
www.smc.ch
www.smc-pneumatik.com.tr
www.smc-pneumatics.co.uk

info@smc.lt
info@smc-pneumatics.nl
post@smc-norge.no
office@smc.pl
post@smc-pneumatics.es
smcromania@smcromania.ro
info@smc-pneumatik.ru
office@smc.sk
office@smc.si
post@smc-smc.es
post@smc.nu
info@smc.ch
info@smc-pneumatik.com.tr
sales@smc-pneumatics.co.uk