

## Diode block - EMG 45-DIO 8E - 2950103

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Diode module, with 8 diodes, individually wired, diode type 1N 4007

### Product Features

- ✓ Spark-suppression diodes for limiting surge voltages of inductive loads
- ✓ Electrical decoupling of messages in fault reporting systems



### Key commercial data

|                      |                                                                                                         |
|----------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit         | 1 PCE                                                                                                   |
| GTIN                 | <br>4 017918 083953 |
| Custom tariff number | 85411000                                                                                                |
| Country of origin    | GERMANY                                                                                                 |

### Technical data

#### Dimensions

|        |       |
|--------|-------|
| Width  | 45 mm |
| Height | 75 mm |
| Depth  | 55 mm |

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |

#### General

|                        |          |
|------------------------|----------|
| Diode type             | 1 N 4007 |
| Max. operating voltage | 250 V AC |

## Diode block - EMG 45-DIO 8E - 2950103

### Technical data

#### General

|                                    |                                         |
|------------------------------------|-----------------------------------------|
| Peak reverse voltage per diode     | 1300 V                                  |
| Reverse current per diode          | 5 µA                                    |
| Conducting state voltage per diode | approx. 0.8 V                           |
| Conducting state current per diode | 0.7 A (with single load)                |
|                                    | 0.5 A (with simultaneous loads)         |
| Surge voltage category             | III, basic insulation (as per EN 50178) |
| Mounting position                  | Any                                     |
| Assembly instructions              | In rows with zero spacing               |

#### Connection data

|                                        |                     |
|----------------------------------------|---------------------|
| Conductor cross section solid min.     | 0.2 mm <sup>2</sup> |
| Conductor cross section solid max.     | 4 mm <sup>2</sup>   |
| Conductor cross section stranded min.  | 0.2 mm <sup>2</sup> |
| Conductor cross section stranded max.  | 2.5 mm <sup>2</sup> |
| Conductor cross section AWG/kcmil min. | 24                  |
| Conductor cross section AWG/kcmil max  | 12                  |
| Stripping length                       | 8 mm                |
| Screw thread                           | M3                  |
| Connection method                      | Screw connection    |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27250312 |
| eCl@ss 4.1 | 27260801 |
| eCl@ss 5.0 | 27260801 |
| eCl@ss 5.1 | 27260801 |
| eCl@ss 6.0 | 27242602 |
| eCl@ss 7.0 | 27242602 |
| eCl@ss 8.0 | 27242602 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001432 |
| ETIM 3.0 | EC001597 |
| ETIM 4.0 | EC001597 |
| ETIM 5.0 | EC001596 |

## Diode block - EMG 45-DIO 8E - 2950103

### Classifications

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211506 |
| UNSPSC 7.0901 | 39121008 |
| UNSPSC 11     | 39121008 |
| UNSPSC 12.01  | 39121008 |
| UNSPSC 13.2   | 39121008 |

### Approvals

#### Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

#### Approval details



### Accessories

Accessories

Marking

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

### Drawings

## Diode block - EMG 45-DIO 8E - 2950103

Circuit diagram

