**Description:**

18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® IV quad shield (60% and 40% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BCCS - Bare Copper Covered Steel	.040

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	.180

Outer Shield**Outer Shield Material:**

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 0.294 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +80°C
Bulk Cable Weight:	32 lbs/1000 ft.
Max. Recommended Pulling Tension:	162 lbs.
Min. Bend Radius (Install)/Minor Axis:	3 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CATV, CM
CEC/C(UL) Specification:	CM
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

1189A Coax - Broadband CATV Coax Cable

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Series Type: Series 6

Flame Test

UL Flame Test: UL1685 UL Loading

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 1189AP

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/ft)

.097

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.2

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/ft)

1.2

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

28.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.8

Max. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

5	.67
55	1.60
211	2.87
270	3.24
300	3.43
350	3.72
400	4.00
450	4.26
550	4.71
750	5.59
870	6.00
1000	6.54

Max. Operating Voltage - UL:

Voltage

350 V RMS

Minimum Structural Return Loss:

Description Freq. (MHz) Start Freq. (MHz) Stop Freq. (MHz) Min. SRL (dB)

		5	1000	20
--	--	---	------	----

1189A Coax - Broadband CATV Coax Cable

Sweep Test

Sweep Testing: 5 MHz - 1 GHz

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1189A 009U1000	1,000 FT	32.000 LB	WHITE		#18 GIFHDLDPPE DBL SH PVC
1189A 009U500	500 FT	16.500 LB	WHITE		#18 GIFHDLDPPE DBL SH PVC
1189A 0091000	1,000 FT	31.000 LB	WHITE	C	#18 GIFHDLDPPE DBL SH PVC
1189A 010U1000	1,000 FT	32.000 LB	BLACK		#18 GIFHDLDPPE DBL SH PVC .
1189A 010U500	500 FT	16.500 LB	BLACK		#18 GIFHDLDPPE DBL SH PVC
1189A 0101000	1,000 FT	31.000 LB	BLACK		#18 GIFHDLDPPE DBL SH PVC .
1189A 2901000	1,000 FT	31.000 LB	BEIGE, LIGHT		#18 GIFHDLDPPE DBL SH PVC

Notes:

C = CRATE REEL PUT-UP.

Broadband Coax

CATV Cables


Series 6

Description	Part No.	UL NEC/ C(UL) CEC Type	Standard Lengths		Standard Unit Weight		Conductor (stranding) Diameter Nom. DCR	Nominal Core OD		Shielding Materials Nom. DCR	Nominal OD		Nom. Imp. (Ω)	Nom. Vel. of Prop.	Nominal Capacitance		Nominal Attenuation		
			Ft.	m	Lbs.	kg		Inch	mm		Inch	mm			pF/Ft.	pF/m	MHz	dB/ 100 Ft.	dB/ 100m

Series 6 • 18 AWG Solid .040" Bare Copper-covered Steel Conductor • Duobond® IV Quad Shield (60% and 40% Coverage)

Gas-injected Foam Polyethylene Insulation • Black PVC Jacket

80°C	1191AM	—	1000	304.8	46.0	20.9	18 AWG (solid) .040" BCCS 28.0Ω/M' 91.9Ω/km	.180	4.57	Duobond IV* 60% & 40% Aluminum Braids 4.8Ω/M' 15.7Ω/km	.298 x .433	7.57 x 11.00	75	83%	16.2	53.1	See Chart on page 6.92
																	
Sweep tested 5 MHz to 1 GHz.																	



.051" (1.3mm) galvanized steel messenger.

80°C	1322R NEW	NEC: CATVR, CMR CEC: CMG FT4	U-1000 1000	U-304.8 304.8	41.0 35.0	18.6 15.9	18 AWG (solid) .040" BCCS 28.0Ω/M' 91.9Ω/km	.180	4.57	Duobond IV* 60% & 40% Aluminum Braids 4.8Ω/M' 15.7Ω/km	.298	7.57	75	83%	16.2	53.1	5 55 500 750 1000 1450 1800 3000	.5 1.4 4.1 5.1 6.0 7.4 8.3 10.5	1.6 4.6 13.5 16.7 19.7 24.3 27.2 34.5
			Sweep tested 5 MHz to 3 GHz.																



Gas-injected Foam Polyethylene Insulation • PVC Jacket (Available in Black or White)


80°C	1189A	NEC:	U-500	U-152.4	18.0	8.2	18 AWG	.180	4.57	Duobond IV*	.298	7.57	75	83%	16.2	53.1	See Chart on page 6.92
	CATV	U-1000	U-304.8	35.0	15.9	(solid)	BCCS	28.0Ω/M'	91.9Ω/km	60% & 40% Aluminum Braids	4.8Ω/M'	15.7Ω/km					
	CM	1000	304.8	35.0	15.9												
	CEC:																
CM																	



*1000 ft. put-up also available in Beige or White Neutral.

Plenum • Foam FEP Insulation • Natural Flamarrest® Jacket

75°C	1189AP	NEC: CATVP CMP CEC: CMP FT6	1000	304.8	32.0	14.5	18 AWG (solid) .040" BCCS 28.0Ω/M' 91.9Ω/km	.170	4.32	Duobond IV* 60% & 40% Aluminum Braids 4.8Ω/M' 15.7Ω/km	.248	6.30	75	83%	16.3	53.5	1 10 50 100 200 400 700 900 1000	.3 .7 1.6 2.2 3.0 4.6 6.6 7.7 8.2	1.0 2.2 5.3 7.2 9.8 15.1 21.7 25.3 26.9
			Sweep tested 5 MHz to 1 GHz.																



BCCS = Bare Copper-covered Steel • DCR = DC Resistance • FEP = Fluorinated Ethylene Propylene

*Duobond IV = Bonded Duofoil® (100% coverage) + aluminum braid (67% coverage) + Duofoil (100% coverage) + aluminum braid (46% coverage).

Technical Information

Attenuation vs. Frequency for Belden® Broadband Coaxial Products

Frequency Point (MHz)	Series 59				Series 6				Series 11			
	Nominal dB/100 Ft.	Nominal dB/100m	Maximum dB/100 Ft.	Maximum dB/100m	Nominal dB/100 Ft.	Nominal dB/100m	Maximum dB/100 Ft.	Maximum dB/100m	Nominal dB/100 Ft.	Nominal dB/100m	Maximum dB/100 Ft.	Maximum dB/100m
5	.75	2.46	.89	2.92	.54	1.77	.67	2.20	.34	1.12	.38	1.25
55	1.84	6.04	1.95	6.40	1.45	4.76	1.60	5.25	.91	2.99	.97	3.18
211	3.36	11.02	3.59	11.78	2.64	8.66	2.87	9.42	1.68	5.51	1.81	5.94
216	3.41	11.19	3.69	12.11	2.67	8.76	2.95	9.68	1.70	5.58	1.84	6.04
240	3.57	11.71	3.87	12.70	2.80	9.19	3.09	10.14	1.78	5.84	1.94	6.36
270	3.79	12.43	4.05	13.29	2.97	9.74	3.24	10.63	1.89	6.20	2.05	6.73
300	3.99	13.09	4.27	14.01	3.13	10.27	3.43	11.25	1.99	6.53	2.15	7.05
325	4.16	13.65	4.50	14.76	3.26	10.70	3.59	11.78	2.07	6.79	2.24	7.35
350	4.33	14.21	4.64	15.22	3.39	11.12	3.72	12.20	2.15	7.05	2.32	7.61
375	4.49	14.73	4.84	15.88	3.52	11.55	3.87	12.70	2.22	7.28	2.40	7.87
400	4.66	15.29	4.88	16.01	3.65	11.97	4.00	13.12	2.30	7.55	2.47	8.10
450	4.96	16.27	5.30	17.39	3.88	12.73	4.26	13.98	2.45	8.04	2.65	8.69
500	5.22	17.13	5.50	18.04	4.09	13.42	4.48	14.70	2.59	8.50	2.85	9.35
550	5.48	17.98	5.90	19.36	4.30	14.11	4.71	15.45	2.73	8.96	2.94	9.65
600	5.75	18.86	6.18	20.28	4.51	14.80	4.94	16.21	2.85	9.35	3.08	10.10
650	6.03	19.78	6.52	21.39	4.72	15.49	5.18	16.99	2.98	9.78	3.22	10.56
700	6.28	20.60	6.83	22.41	4.92	16.14	5.45	17.88	3.10	10.17	3.37	11.06
750	6.51	21.36	6.96	22.83	5.11	16.76	5.59	18.34	3.21	10.53	3.50	11.48
800	6.71	22.01	7.30	23.95	5.27	17.29	5.75	18.86	3.32	10.89	3.65	11.97
862	6.97	22.87	7.50	24.61	5.47	17.95	5.98	19.62	3.46	11.35	3.82	12.53
870	7.00	22.97	7.54	24.74	5.49	18.01	6.00	19.68	3.48	11.42	3.84	12.60
900	7.14	23.42	7.79	25.56	5.60	18.37	6.11	20.05	3.55	11.65	3.96	12.99
950	7.39	24.25	7.90	25.92	5.79	19.00	6.35	20.83	3.66	12.01	4.10	13.45
1000	7.68	25.20	8.09	26.54	5.99	19.65	6.54	21.46	3.77	12.37	4.23	13.88
1450	—	—	—	—	7.80	25.60	8.00	26.20	5.00	16.41	5.50	18.10
1800	—	—	—	—	8.60	28.20	8.80	28.90	5.70	18.70	6.27	20.60
2250	—	—	—	—	9.80	32.20	10.00	32.80	6.50	21.33	7.15	23.50
3000	—	—	—	—	11.30	37.10	11.90	39.00	8.00	26.25	8.80	28.90