

# Boca Semiconductor Corp.

BSC

<http://www.bocasemi.com>

## MAXIMUM RATINGS

| Rating                                                                                 | Symbol         | 2N3250<br>2N3251 | 2N3251A | Unit                          |
|----------------------------------------------------------------------------------------|----------------|------------------|---------|-------------------------------|
| Collector-Emitter Voltage                                                              | $V_{CEO}$      | -40              | -60     | Vdc                           |
| Collector-Base Voltage                                                                 | $V_{CBO}$      | -50              | -60     | Vdc                           |
| Emitter-Base Voltage                                                                   | $V_{EBO}$      | -5.0             |         | Vdc                           |
| Collector Current                                                                      | $I_C$          | -200             |         | mAdc                          |
| Total Device Dissipation @ $T_A = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$          | 0.36<br>2.06     |         | Watt<br>mW/ $^\circ\text{C}$  |
| Total Device Dissipation @ $T_C = 25^\circ\text{C}$<br>Derate above $25^\circ\text{C}$ | $P_D$          | 1.2<br>6.9       |         | Watts<br>mW/ $^\circ\text{C}$ |
| Operating and Storage Temperature<br>Temperature Range                                 | $T_J, T_{stg}$ | -65 to +200      |         | $^\circ\text{C}$              |

## THERMAL CHARACTERISTICS

| Characteristic                          | Symbol          | Max | Unit               |
|-----------------------------------------|-----------------|-----|--------------------|
| Thermal Resistance, Junction to Ambient | $R_{\theta JA}$ | 486 | $^\circ\text{C/W}$ |
| Thermal Resistance, Junction to Case    | $R_{\theta JC}$ | 146 | $^\circ\text{C/W}$ |

## ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted.)

| Characteristic                                                         | Symbol        | Min        | Max | Unit |
|------------------------------------------------------------------------|---------------|------------|-----|------|
| <b>OFF CHARACTERISTICS</b>                                             |               |            |     |      |
| Collector-Emitter Breakdown Voltage(1)<br>( $I_C = -10$ mAdc)          | $V_{(BR)CEO}$ | -40<br>-60 | —   | Vdc  |
| Collector-Base Breakdown Voltage<br>( $I_C = -10$ $\mu\text{Adc}$ )    | $V_{(BR)CBO}$ | -50<br>-60 | —   | Vdc  |
| Emitter-Base Breakdown Voltage<br>( $I_E = -10$ $\mu\text{Adc}$ )      | $V_{(BR)EBO}$ | -5.0       | —   | Vdc  |
| Collector Cutoff Current<br>( $V_{CE} = -40$ Vdc, $V_{EB} = -3.0$ Vdc) | $I_{CEX}$     | —          | -20 | nA   |
| Base Cutoff Current<br>( $V_{CE} = -40$ Vdc, $V_{EB} = -3.0$ Vdc)      | $I_{BL}$      | —          | -50 | nAdc |

## ON CHARACTERISTICS


|                                                                                                                              |                           |               |           |               |     |
|------------------------------------------------------------------------------------------------------------------------------|---------------------------|---------------|-----------|---------------|-----|
| DC Forward Current Transfer Ratio<br>( $I_C = -0.1$ mAdc, $V_{CE} = -10$ Vdc)                                                | 2N3250<br>2N3251, 2N3251A | $h_{FE}$      | 40<br>80  | —<br>—        | —   |
| ( $I_C = -1.0$ mAdc, $V_{CE} = -1.0$ Vdc)                                                                                    | 2N3250<br>2N3251, 2N3251A |               | 45<br>90  | —<br>—        |     |
| ( $I_C = -10$ mAdc, $V_{CE} = -1.0$ Vdc)(1)                                                                                  | 2N3250<br>2N3251, 2N3251A |               | 50<br>100 | 150<br>300    |     |
| ( $I_C = -50$ mAdc, $V_{CE} = -1.0$ Vdc)(1)                                                                                  | 2N3250<br>2N3251, 2N3251A |               | 15<br>30  | —<br>—        |     |
| Collector-Emitter Saturation Voltage (1)<br>( $I_C = -10$ mAdc, $I_B = -1.0$ mAdc)<br>( $I_C = -50$ mAdc, $I_B = -5.0$ mAdc) |                           | $V_{CE(sat)}$ | —<br>—    | -0.25<br>-0.5 | Vdc |
| Base-Emitter Saturation Voltage (1)<br>( $I_C = -10$ mAdc, $I_B = -1.0$ mAdc)<br>( $I_C = -50$ mAdc, $I_B = -5.0$ mAdc)      |                           | $V_{BE(sat)}$ | -0.6<br>— | -0.9<br>-1.2  | Vdc |

## SMALL-SIGNAL CHARACTERISTICS

|                                                                                            |                           |           |            |        |     |
|--------------------------------------------------------------------------------------------|---------------------------|-----------|------------|--------|-----|
| Current-Gain — Bandwidth Product<br>( $I_C = -10$ mAdc, $V_{CE} = -20$ Vdc, $f = 100$ MHz) | 2N3250<br>2N3251, 2N3251A | $f_T$     | 250<br>300 | —<br>— | MHz |
| Output Capacitance<br>( $V_{CB} = -10$ Vdc, $I_E = 0$ , $f = 1.0$ MHz)                     |                           | $C_{obo}$ | —          | 6.0    | pF  |
| Input Capacitance<br>( $V_{EB} = -1.0$ Vdc, $I_C = 0$ , $f = 1.0$ MHz)                     |                           | $C_{ibo}$ | —          | 8.0    | pF  |

## 2N3250 2N3251,A★

CASE 22-03, STYLE 1  
TO-18 (TO-206AA)



## GENERAL PURPOSE TRANSISTORS

PNP SILICON

★2N3251A is a Motorola  
designated preferred device.

2N3250 2N3251,A

ELECTRICAL CHARACTERISTICS (continued) (T<sub>A</sub> = 25°C unless otherwise noted.)

| Characteristic                                                                                            |                           | Symbol            | Min        | Max        | Unit               |
|-----------------------------------------------------------------------------------------------------------|---------------------------|-------------------|------------|------------|--------------------|
| Input Impedance<br>(I <sub>C</sub> = -1.0 mA, V <sub>CE</sub> = -10 V, f = 1.0 kHz)                       | 2N3250<br>2N3251, 2N3251A | h <sub>ie</sub>   | 1.0<br>2.0 | 6.0<br>12  | kohms              |
| Voltage Feedback Ratio<br>(I <sub>C</sub> = -1.0 mA, V <sub>CE</sub> = -10 V, f = 1.0 kHz)                | 2N3250<br>2N3251, 2N3251A | h <sub>re</sub>   | —<br>—     | 10<br>20   | X 10 <sup>-4</sup> |
| Small-Signal Current Gain<br>(I <sub>C</sub> = -1.0 mA, V <sub>CE</sub> = -10 V, f = 1.0 kHz)             | 2N3250<br>2N3251, 2N3251A | h <sub>fe</sub>   | 50<br>100  | 200<br>400 | —                  |
| Output Admittance<br>(I <sub>C</sub> = -1.0 mA, V <sub>CE</sub> = -5.0 V, f = 1.0 kHz)                    | 2N3250<br>2N3251, 2N3251A | h <sub>oe</sub>   | 4.0<br>10  | 40<br>60   | μmhos              |
| Collector Base Time Constant<br>(I <sub>C</sub> = -10 mA, V <sub>CE</sub> = -20 V, f = 31.8 MHz)          |                           | rb'C <sub>C</sub> | —          | 250        | ps                 |
| Noise Figure<br>(I <sub>C</sub> = -100 μA, V <sub>CE</sub> = -5.0 V, R <sub>S</sub> = 1.0 kΩ, f = 100 Hz) |                           | NF                | —          | 6.0        | dB                 |

SWITCHING CHARACTERISTICS

| Characteristic |                                                                                                                  | Symbol                                      | Max        | Unit |
|----------------|------------------------------------------------------------------------------------------------------------------|---------------------------------------------|------------|------|
| Delay Time     | (V <sub>CC</sub> = -3.0 Vdc, V <sub>BE</sub> = +0.5 Vdc<br>I <sub>C</sub> = -10 mAdc, I <sub>B1</sub> = -1.0 mA) | t <sub>d</sub>                              | 35         | ns   |
| Rise Time      |                                                                                                                  | t <sub>r</sub>                              | 35         | ns   |
| Storage Time   | I <sub>C</sub> = -10 mAdc, I <sub>B1</sub> = I <sub>B1</sub> = -1.0 mAdc<br>(V <sub>CC</sub> = -3.0 V)           | 2N3250<br>2N3251, 2N3251A<br>t <sub>s</sub> | 175<br>200 | ns   |
| Fall Time      |                                                                                                                  | t <sub>f</sub>                              | 50         | ns   |

(1) Pulse Test: PW = 300 μs, Duty Cycle = 2.0%.

<http://www.bocasemi.com>

SWITCHING TIME CHARACTERISTICS

FIGURE 1 — DELAY AND RISE TIME






FIGURE 2 — STORAGE AND FALL TIME




**AUDIO SMALL-SIGNAL CHARACTERISTICS**  
**NOISE FIGURE VARIATIONS**  
 $(V_{CE} = 6.0 \text{ V}, T_A = 25^\circ\text{C})$

**FIGURE 3 — FREQUENCY**




**FIGURE 4 — SOURCE RESISTANCE**




**h PARAMETERS**  
 $V_{CE} = 10 \text{ V}, f = 1.0 \text{ kc}, T_A = 25^\circ\text{C}$


**FIGURE 5 — CURRENT GAIN**




**FIGURE 6 — OUTPUT ADMITTANCE**



**FIGURE 7 — VOLTAGE FEEDBACK RATIO**




**FIGURE 8 — INPUT IMPEDANCE**




**2N3250 2N3251,A**

**FIGURE 9 — NORMALIZED CURRENT GAIN CHARACTERISTICS**



**FIGURE 10 — COLLECTOR SATURATION REGION**




<http://www.bocasemi.com>


This graph shows the effect of base current on collector current  $\beta_O$  is the current gain of the transistor at 1 volt, and  $\beta_F$  (forced gain) is the ratio of  $I_C/I_{BF}$  in a circuit. EXAMPLE: For type 2N3251, estimate a base current ( $I_{BF}$ ) to insure saturation at a temperature of 25°C and a collector current of 10 mA. Observe that at  $I_C = 10$  mA an overdrive factor of at least 2.5 is required to drive the transistor well into the saturation region. From Figure 1, it is seen that  $h_{FE} @ 1$  volt is typically 167 (guaranteed limits from the Table of Characteristics can be used for "worst case" design).

$$\frac{\beta_O}{\beta_F} = \frac{h_{FE} @ 1 \text{ Volt}}{I_C/I_{BF}} \quad 2.5 = \frac{167}{10 \text{ mA}/I_{BF}} \quad I_{BF} \approx -6.68 \text{ mA}$$


**FIGURE 11 — SATURATION VOLTAGES**




**FIGURE 12 — TEMPERATURE COEFFICIENTS**



**FIGURE 13 —  $f_T$  AND  $r_b'C_c$  versus  $I_C$**




**FIGURE 14 — 30 MC EQUIVALENT CIRCUIT**



<http://www.bocasemi.com>

**FIGURE 15 — JUNCTION CAPACITANCE**



**FIGURE 16 — CHARGE DATA**

