


SN75130 QUADRUPLER LINE DRIVER

SLLS077A - D3408, FEBRUARY 1990 - REVISED FEBRUARY 1993

- Meets IBM 360/370 I/O Interface Specification GA22-6974-3 (Also See SN75ALS130)
- Minimum Output Voltage of 3.11 V at $I_{OH} = -59.3$ mA
- Fault-Flag Circuit Output Signals Driver Output Fault
- Fault-Detection Current-Limit Circuit Minimizes Power Dissipation During a Fault Condition
- Common Enable and Common Fault Flag
- Designed to Be an Improved Replacement for the MC3485

D OR N PACKAGE
(TOP VIEW)



FUNCTION TABLE

INPUTS		OUTPUTS		
G†	A	Y	F	W
L	X	L	H	H
X	L	L	H	H
H	H	H	H	L
H	H	S	L	H

H = high level, L = low level, X = irrelevant,
S = shorted to ground

† G and F are common to the four drivers. If any of the four Y outputs is shorted, the fault flag will respond.

description

The SN75130 quadruple line driver is designed to meet the IBM 360/370 I/O specification GA22-6974-3. The output voltage is 3.11 V minimum (at $I_{OH} = -59.3$ mA) over the recommended ranges of supply voltage (4.5 V to 5.5 V) and temperature (0°C to 70°C). Driver outputs use a fault-detection current-limit circuit to allow high drive current but still minimize power dissipation when the output is shorted to ground. The SN75130 is compatible with standard TTL logic and supply voltages.

Fault-flag circuitry is designed to sense and signal a line short on any Y line. Upon detecting an output fault condition, the fault-flag circuit forces the driver output into the off (low) state and signals a fault condition by causing the fault-flag output to go low.

The SN75130 can drive a 50-Ω load as required in the IBM GA22-6974-3 specification or a 90-Ω load as used in many I/O systems. Optimum performance can be achieved when the device is used with either the SN75125, SN75127, SN75128, or SN75129 line receivers.

The SN75130 is characterized for operation from 0°C to 70°C.

PRODUCTION DATA information is current as of publication date.
Products conform to specifications per the terms of Texas Instruments
standard warranty. Production processing does not necessarily include
testing of all parameters.

Copyright © 1993, Texas Instruments Incorporated

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


2-297

8961724 0090521 199

SN75130 QUADRUPLE LINE DRIVER


SLLS077A - D3406, FEBRUARY 1990 - REVISED FEBRUARY 1993

logic symbol†



† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagram (positive logic)




8961724 0090522 025

2-298

**TEXAS
INSTRUMENTS**
POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

schematics of inputs and outputs



absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, VCC	7 V
Input voltage	7 V
Continuous total dissipation	See Dissipation Rating Table
Operating free-air temperature range, TA	0°C to 70°C
Storage temperature range	-65°C to 150°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C

DISSIPATION RATING TABLE

PACKAGE	TA ≤ 25°C POWER RATING	OPERATING FACTOR ABOVE TA = 25°C	TA = 70°C POWER RATING
D	950 mW	7.6 mW/°C	608 mW
N	1150 mW	9.2 mW/°C	736 mW

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-299

8961724 0090523 T61

SN75130 QUADRUPLE LINE DRIVER

SLLS077A – D3406, FEBRUARY 1990 – REVISED FEBRUARY 1993

recommended operating conditions

	MIN	NOM	MAX	UNIT
Supply voltage, V_{CC}	4.5	5	5.95	V
High-level input voltage, V_{IH}	2			V
Low-level input voltage, V_{IL}			0.8	V
High-level output current, I_{OH}			-59.3	mA
Operating free-air temperature, T_A	0		70	°C


electrical characteristics over recommended operating free-air temperature range

PARAMETER		TEST CONDITIONS	MIN	MAX	UNIT
V_{IK}	Input clamp voltage	A, G $I_I = -18$ mA		-1.5	V
V_{OH}	High-level output voltage	Y $V_{CC} = 4.5$ V, $I_{OH} = -59.3$ mA, $V_{IH} = 2$ V	3.11		V
		Y $V_{CC} = 5.25$ V, $I_{OH} = -41$ mA, $V_{IH} = 2$ V	3.9		
		W $V_{CC} = 4.5$ V, $I_{OH} = -400$ μ A, $V_{IH} = 2$ V	2.5		
V_{OL}	Low-level output voltage	Y $V_{CC} = 5.5$ V, $I_{OL} = -240$ μ A, $V_{IL} = 0.8$ V		0.15	V
		Y $V_{CC} = 5.95$ V, $I_{OL} = -1$ mA, $V_{IL} = 0.8$ V		0.15	
		F $V_{CC} = 4.5$ V, $I_{OL} = 8$ mA, Y at 0 V		0.5	
		W $V_{CC} = 4.5$ V, $I_{OL} = 8$ mA		0.5	
$I_{O(off)}$	Off-state output current	Y $V_{CC} = 4.5$ V, $V_{IL} = 0$, $V_O = 3.11$ V		100	μ A
		Y $V_{CC} = 0$, $V_{IL} = 0$, $V_O = 3.11$ V		200	
I_{OH}	High-level output current	F $V_{CC} = 5.95$ V, $V_{OH} = 5.95$ V		100	μ A
I_I	Input current	A $V_{CC} = 4.5$ V, $V_{IH} = 5.5$ V		100	μ A
		G $V_{CC} = 4.5$ V, $V_{IH} = 5.5$ V		400	
I_{IH}	High-level input current	A $V_{CC} = 4.5$ V, $V_{IH} = 2.7$ V		20	μ A
		G $V_{CC} = 4.5$ V, $V_{IH} = 2.7$ V		80	
I_{IL}	Low-level input current	A $V_{CC} = 5.95$ V, $V_{IL} = 0.4$ V		250	μ A
		G $V_{CC} = 5.95$ V, $V_{IL} = 0.4$ V		-1000	
I_{OS}	Short-circuit output	Y $V_{CC} = 5.5$ V, $V_O = 0$		-5	mA
		W $V_{CC} = 5.5$ V, $V_O = 0$	-15	-100	
		Y $V_{CC} = 5.95$ V, $V_O = 0$		-5	
		W $V_{CC} = 5.95$ V, $V_O = 0$	-15	-110	
I_{CCH}	Supply current, all outputs high	$V_{CC} = 5.5$ V, $V_I = 2$ V		75	mA
		$V_{CC} = 5.95$ V, $V_I = 2$ V		85	
I_{CCL}	Supply current, Y outputs low	$V_{CC} = 5.5$ V, $V_I = 0.8$ V		55	mA
		$V_{CC} = 5.95$ V, $V_I = 0.8$ V		70	

switching characteristics over recommended operating free-air temperature range

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	MAX	UNIT
t_{PLH} Propagation delay time, low-to-high-level output	A	Y	$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V},$ $C_L = 50 \text{ pF},$ Input $f = 1 \text{ MHz},$ $V_{H(ref)} = 3.11 \text{ V},$ $R_L = 50 \Omega,$ See Figures 1 and 2	40	ns	
t_{PHL} Propagation delay time, high-to-low-level output				37	ns	
t_{PLH} Ratio of propagation delay times t_{PHL}				0.3	3	
t_{PLH} Propagation delay time, low-to-high-level output	A	Y	$V_{CC} = 5.25 \text{ V to } 5.59 \text{ V},$ $C_L = 50 \text{ pF},$ Input $f = 5 \text{ MHz},$ $V_{H(ref)} = 3.9 \text{ V},$ $R_L = 90 \Omega,$ See Figures 1 and 2	45	ns	
t_{PHL} Propagation delay time, high-to-low-level output				45	ns	
t_{PLH} Propagation delay time, low-to-high-level output	A	W	$V_{CC} = 5 \text{ V},$ $C_L = 15 \text{ pF},$ $R_L = 2 \text{ k}\Omega,$ See Figures 1 and 2	45	ns	
t_{PHL} Propagation delay time, high-to-low-level output				28	ns	
t_{PLH} Propagation delay time, low-to-high-level output	A	$\bar{F}$	$V_{CC} = 5 \text{ V},$ $C_L = 15 \text{ pF},$ $R_L = 2 \text{ k}\Omega,$ See Figures 1 and 2	60	ns	
t_{PHL} Propagation delay time, high-to-low-level output				100	ns	

PARAMETER MEASUREMENT INFORMATION



NOTE A: The input pulse is supplied by a generator having the following characteristics: PRR = 1 MHz, duty cycle = 50%, $t_r \leq 6 \text{ ns}$, $t_f \leq 6 \text{ ns}$, $Z_0 = 50 \Omega$.

Figure 1. Input and Output Voltage Waveforms



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


2-301

8961724 0090525 834

SN75130 QUADRUPLE LINE DRIVER

SLLS077A - D3406, FEBRUARY 1990 - REVISED FEBRUARY 1993

PARAMETER MEASUREMENT INFORMATION



NOTE A: C_L includes probe and stray capacitance.

Figure 2. Switching Characteristics Load Circuits