

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC
GP

DIST
00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	ECR-11-025464	16DEC11	RK	BVH

NOTES:

1

PITCH TOLERANCE TO BE ±.18[.007] FOR 1.27[.050] PITCH JUMPERS & ±.25[.010] FOR ALL REMAINING PITCHES. TOLERANCE TO BE NON CUMULATIVE OVER GAUGE LENGTH.

2

11.92-152.40[.500-6.000] ARE STANDARD LENGTHS. JUMPERS ARE AVAILABLE IN INCREMENTS OF 2.50[.10] PLUS 6.35[.25] AND 19.05[.75].

3

DELETED

4

FOR CONDUCTOR PITCH 7 (2mm), ON PAGE 2 & 3, DIMENSION "B" IS 2.00[.079]

5

SPECIAL PIN LENGTHS ARE AVAILABLE FOR JUMPERS WITH A PIN CONFIGURATION OF "A" OR "B" ON LENGTHS OF UP TO 609.6[24.0] IN 2.54[.100] & 5.08[.200] PITCH VARIANTS ONLY BY ADDING THE FOLLOWING SUFFIXES:

SUFFIX	PEN LENGTH	TOLERANCE
V1	2.85 (.112)	±.305 [±.012]
V2	3.40 (.134)	
V3	4.10 (.161)	
V4	6.50 (.256)	
V5	3.10 (.122)	
V6	2.81 (.150)	
V7	4.50 (.177)	
V8	2.00 (.079)	
V9	TBD	
V10	.76 (.030)	
V11	2.41 (.095)	

"C"

DIMENSION FROM THE EDGE OF INSULATION MATERIAL TO EDGE OF THE FIRST COND. EXCEPT "M" STYLE.

6. RECOMMENDED PCB HOLE DRILLING DETAILS ARE AS FOLLOWS:-

PITCH A	ØG
1.27 (.050)	.70 (.028)
1.90 (.075)	.80 (.031)
2.54 (.100)	.95 (.037)
3.18 (.125)	.95 (.037)
3.81 (.150)	.95 (.037)
5.08 (.200)	.95 (.037)

PITCH A
Φ.13(.005)

ØG ±.03(.001)

7

BEND RADIUS TO APPLY ONLY IN THE FLAT SECTION OF JUMPER BETWEEN THE CONDUCTOR TRANSITION AREAS.

8

PER 108-2135.

9.

TOOL MARKS PERMISSIBLE ON BENDS. NO EXPOSED COPPER.

10

PIN DIAMETER SPECIFIED NOT APPLICABLE IN BENDING AREA OF PIN, DUE TO NORMAL DEFORMATION OF BENDING PROCESS.

11

REFER TO RELEVANT MATERIAL SPECIFICATIONS.

F - MID POINT THICKNESS BETWEEN PT 1 & PT 2

	MINIMUM	MAXIMUM
NOMEX®	.152 [.006]	.305 [.012]
POLYESTER	.152 [.006]	.305 [.012]
KAPTON®	.102 [.004]	.254 [.010]
TEFLON®	.305 [.012]	.533 [.021]

12. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY STANDARD 230-702.

Nomex®, Teflon® and Kapton® are trademarks of E. I. DuPont de Nemours.

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

25

26

27

28

29

30

31

32

33

34

35

36

37

38

39

40

41

42

43

44

45

46

47

48

49

50

51

52

53

54

55

56

57

58

59

60

61

62

63

64

65

66

67

68

69

70

71

72

73

74

75

76

77

78

79

80

81

82

83

84

85

86

87

88

89

90

91

92

93

94

95

96

97

98

99

100

101

102

103

104

105

106

107

108

109

110

111

112

113

114

115

116

117

118

119

120

121

122

123

124

125

126

127

128

129

130

131

132

133

134

135

136

137

138

139

140

141

142

143

144

145

146

147

148

149

150

151

152

153

154

155

156

157

158

159

160

161

162

163

164

165

166

167

168

169

170

171

172

173

174

175

176

177

178

179

180

181

182

183

184

185

186

187

188

189

190

191

192

193

194

195

196

197

198

199

200

201

202

203

204

205

206

207

208

209

210

211

212

213

214

215

216

217

218

219

220

221

222

223

224

225

226

227

228

229

230

231

232

233

234

235

236

237

238

239

240

241

242

243

244

245

246

247

248

249

250

251

252

253

254

255

256

257

258

259

260

261

262

263

264

265

266

267

268

269

270

271

272

273

274

275

276

277

278

279

280

281

282

283

284

285

286

287

288

289

290

291

292

293

294

295

296

297

298

299

300

301

302

303

304

305

306

307

308

309

310

311

312

313

314

315

316

317

318

319

320

321

322

323

324

325

326

327

328

329

330

331

332

333

334

335

336

337

338

339

340

341

342

343

344

345

346

347

348

349

350

351

352

353

354

355

356

357

358

359

360

361

362

363

364

365

366

367

368

369

370

371

372

373

374

375

376

377

378

379

380

381

382

383

384

385

386

387

388

389

390

391

392

393

394

395

396

397

398

399

400

401

402

403

404

405

406

407

408

409

410

411

412

413

414

415

416

417

418

419

420

421

422

423

424

425

426

427

428

429

430

431

432

433

434

435

436

437

438

439

440

441

442

443

444

445

446

447

448

449

450

451

452

453

454

455

456

457

458

459

460

461

462

463

464

465

466

467

468

469

470

471

472

473

474

475

476

477

478

479

480

481

482

483

484

485

486

487

488

489

490

491

492

493

494

495

496

497

498

499

500

501

502

503

504

505

506

507

508

509

510

511

512

513

514

515

516

517

518

519

520

521

522

523

524

525

526

527

528

529

530

531

532

533

534

535

536

537

538

539

540

541

542

543

544

545

546

547

548

549

550

551

552

553

554

555

556

557

558

559

560

561

562

563

564

565

566

567

568

569

570

571

572

573

574

575

576

577

578

579

580

581

582

583

584

585

586

587

588

589

590

591

592

593

594

595

596

597

598

599

600

601

602

603

604

605

606

607

608

609

610

611

612

613

614

615

616

617

618

619

620

621

622

623

624

625

626

627

628

629

630

631

632

633

634

635

636

637

638

639

640

641

642

643

644

645

646

647

648

649

650

651

652

653

654

655

656

657

658

659

660

661

662

663

664

665

666

667

668

669

670

671

672

673

674

675

676

677

678

679

680

681

682

683

684

685

686

687

688

689

690

691

692

693

694

695

696

697

698

699

700

701

702

703

704

705

706

707

708

709

710

711

712

713

714

715

716

717

718

719

720

721

722

723

724

725

726

727

728

729

730

731

732

733

734

735

736

737

738

739

740

741

742

743

744

745

746

747

748

749

750

751

752

753

754

755

756

757

758

759

760

761

762

763

764

765

766

767

768

769

770

771

772

773

774

775

776

777

778

779

780

781

782

783

784

785

786

787

788

789

790

791

792

793

794

795

796

797

798

799

800

801

802

803

804

805

806

807

808

809

810

811

812

813

814

815

816

817

818

819

820

821

822

823

824

825

826

827

828

829

830

831

832

833

834

835

836

837

838

839

840

841

842

843

844

845

846

847

848

849

850

851

852

853

854

855

856

857

858

859

860

861

862

863

864

865

866

867

868

869

870

871

872

873

874

875

876

877

878

879

880

881

882

883

884

885

886

887

888

889

890

891

892

893

894

895

896

897

898

899

900

901

902

903

904

905

906

907

908

909

910

911

912

913

914

915

916

917

918

919

920

921

922

923

924

925

926

927

928

929

930

931

932

933

934

935

936

937

938

939

940

941

942

943

944

945

946

947

948

949

950

951

952

953

954

955

956

957

958

959

960

961

962

963

964

965

966

967

968

969

970

971

972

973

974

975

976

977

978

979

980

981

982

983

984

985

986

987

988

989

990

991

992

993

994

995

996

997

998

999

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

± -

± -

± -

± -

± -

± 1/2°

MATERIAL

FINISH

DWN
J. SCHWARTZ
28FEB01

CHK
E. FOX
28FEB01

APVD
E. FOX
28FEB01

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

FLEXSTRIP PIN CONFIGURATIONS, GENERIC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1474339

RESTRICTED TO

SCALE
N.T.S.

SHEET
1 OF 4

REV
H1

1470-19 (3/11)

4		3		2		1																									
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION																											
© COPYRIGHT — By — ALL RIGHTS RESERVED.				LOC GP		DIST 00																									
				P		LTR																									
				DESCRIPTION		DATE																									
				SEE SHEET 1		—																									
				DWN		APVD																									
A — STRAIGHT PINS		B — RIGHT ANGLE PINS (BENT DOWN)		C — RIGHT ANGLE STAGGERED PINS (PIN 1 SHORT, BENT DOWN)		D — STRAIGHT ANGLE STAGGERED PINS (PIN 1 STRAIGHT)																									
STANDARD JUMPERS SMART DESCRIPTION				STANDARD LINE JOBS																											
AUTOMOTIVE USE ONLY FLEXSTRIP PRODUCT CODE INSULATION MATERIAL: N — NOMEX® P — POLYESTER T — TEFLON® K — KAPTON® CONDUCTOR PITCH: 1 — 1.27(.050) 2 — 2.54(.100) 3 — 3.18(.125) 4 — 3.81(.150) 5 — 5.08(.200) 6 — 1.90(.075) 7 — 2.00(.078) 8 — 1.25(.049) 9 — 1.00(.039)				MANUFACTURING NOTE: MINIMUM GAP BETWEEN STRIPS <table><tr><td>SK/A/Z</td><td>.75 INCH</td></tr><tr><td>LP</td><td>1.1 INCH</td></tr></table> MINIMUM CONDUCTOR COUNT PER STRIP FOR LINE JOBS <table><tr><th>PITCH</th><th>CONDUCTOR</th></tr><tr><td>1 1.27 (.050)</td><td>60</td></tr><tr><td>2 2.54 (.100)</td><td>60</td></tr><tr><td>3 3.18 (.125)</td><td>60</td></tr><tr><td>4 3.81 (.150)</td><td>50</td></tr><tr><td>5 5.08 (.200)</td><td>40</td></tr><tr><td>6 1.91 (.075)</td><td>60</td></tr><tr><td>7 2.0 (.078)</td><td>60</td></tr><tr><td>8 1.24 (.049)</td><td>60</td></tr><tr><td>9 1.0 (.039)</td><td>80</td></tr></table>				SK/A/Z	.75 INCH	LP	1.1 INCH	PITCH	CONDUCTOR	1 1.27 (.050)	60	2 2.54 (.100)	60	3 3.18 (.125)	60	4 3.81 (.150)	50	5 5.08 (.200)	40	6 1.91 (.075)	60	7 2.0 (.078)	60	8 1.24 (.049)	60	9 1.0 (.039)	80
SK/A/Z	.75 INCH																														
LP	1.1 INCH																														
PITCH	CONDUCTOR																														
1 1.27 (.050)	60																														
2 2.54 (.100)	60																														
3 3.18 (.125)	60																														
4 3.81 (.150)	50																														
5 5.08 (.200)	40																														
6 1.91 (.075)	60																														
7 2.0 (.078)	60																														
8 1.24 (.049)	60																														
9 1.0 (.039)	80																														
FS N 1 — 2 SK (LP) INSULATION LENGTH IN INCHES .5 MIN. — 30.0 MAX. IN .100 INCREMENTS, PLUS .25 & .75				THE FOLLOWING ORDERING CODE IS A SPECIAL FOR TE CONNECTIVITY GERMANY DESCRIBING A STRIP OF ANY INSULATION MATERIAL, ANY PITCH AND ANY INSULATION LENGTH WITH A 11.00[.433] MIN PIN LENGTH UNLESS OTHERWISE SPECIFIED:— FS X—X X J—A A W																											
Nomex®, Teflon® and Kapton® are trademarks of E. I. DuPont de Nemours.				THIS DRAWING IS A CONTROLLED DOCUMENT.																											
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN J. SCHWARTZ 28FEB01		TE Connectivity																									
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± 1/2°		CHK E. FOX 28FEB01		NAME																									
MATERIAL		FINISH		APVD E. FOX 28FEB01		FLEXSTRIP PIN CONFIGURATIONS, GENERIC																									
—		—		PRODUCT SPEC		—																									
				APPLICATION SPEC		—																									
				WEIGHT		—																									
				CUSTOMER DRAWING		—																									
				SCALE		N.T.S.																									
				SHEET		2 OF 4																									
				REV		H1																									

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT — By —

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

GP

DIST

00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

NORMAL CONDUCTOR PITCH		1.00 (.039)	1.25 (.049)	1.27 (.050)	1.90 (.075)	2.00 (.078)	2.54 (.100)	3.18 (.125)	3.81 (.150)	5.08 (.200)
WIRE GAUGE		AWG 28	AWG 28	AWG 28	AWG 26	AWG 26	AWG 24	AWG 24	AWG 24	AWG 24
NOMINAL WIRE DIAMETER		.32(.0126)	.32(.0126)	.32(.0126)	.40(.0159)	.40(.0159)	.51(.0201)	.51(.0201)	.51(.0201)	.51(.0201)
CURRENT RATING		8	8	8	8	8	8	8	8	8
VOLTAGE RATING		8	8	8	8	8	8	8	8	8
MAX NUMBER OF CONDUCTORS PER JUMPER		8	8	8	8	8	8	8	8	8
MIN BREAKDOWN VOLTAGE @ 1 MIN		8	8	8	8	8	8	8	8	8
INSULATION RESISTANCE (GND. SIG. GND) 305 (12') SAMPLE @ 500VDC	P N T K	8	8	8	8	8	8	8	8	8
CAPACITANCE (pf / 50.8 (12') LENGTH) (GND, SIG, GND) (AVERAGE)	P N T K	8	8	8	8	8	8	8	8	8
CHARACTERISTIC IMPEDANCE (GND. SIG. GND) (AVERAGE)	P N T K	8	8	8	8	8	8	8	8	8
APPLICATION TEMP RANGE (C°) (FOR SOLDERING)	P N T K	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	200 / 4 sec 200 / 4 sec 240 / 4 sec 240 / 4 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec	250 / 4 sec 250 / 4 sec 260 / 5 sec 260 / 5 sec
OPERATING TEMPERATURE (C°) 11	P N T K	-40 to 105 (For all Conductor Pitches) -40 to 125 (For all Conductor Pitches) -40 to 150 (For all Conductor Pitches) -40 to 150 (For all Conductor Pitches)								
MINIMUM BEND RADIUS 7	P N T K	3.18mm (For all Conductor Pitches) 3.18mm (For all Conductor Pitches) 3.18mm (For all Conductor Pitches) 3.18mm (For all Conductor Pitches)								
UL STYLE NUMBER	P N T K	2639 (For all Conductor Pitches .100 and above) 5456 (For all Conductor Pitches .100 and above) 2928 (For all Conductor Pitches .100 and above) 2927 (For all Conductor Pitches .100 and above)								

ABR.	MATERIAL	SPECIFICATION
	COPPER WIRE	100-1577
P	POLYESTER	100-1575
N	NOMEX®	100-1758
T	TEFLON®	100-1574
K	KAPTON®	100-1576

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

MATERIAL

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ± 1/2°

FINISH —

DWN
J. SCHWARTZ
28FEB01

CHK
E. FOX
28FEB01

APVD
E. FOX
28FEB01

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

TE Connectivity

FLEXSTRIP PIN CONFIGURATIONS, GENERIC

—

—

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1474339

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
N.T.S.

SHEET
4 OF 4

REV
H1

Nomex®, Teflon® and Kapton® are trademarks of E. I. DuPont de Nemours.

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[FSN-22A-16](#) [FST-24A-5](#)