



1812 CHIP TRANSFORMER

TITLE

JH 3/97
DRAWN BY / DATE

APPROVED BY / DATE

DRAWING SCALE

Q4123-A


PART NUMBER

Q4123-AC.DWG


FILE NAME

GENERAL USE:
☒ YES ☐ NO


REVISIONS



COLOR
CODE



WINDING CONFIGURATION



ELECTRICAL SPECIFICATIONS

TEST FREQUENCY: 460 (MHZ)

TEST SPECIFICATIONS:

L₁₋₂ = 16NH±10% @ 460 (MHZ)

L₃₋₄ = 16NH±10% @ 460 (MHZ)

SRF₁₋₂= N/A MIN (MHZ)

DCR₁₋₂ = .100 MAX (OHMS)

$$DCR_{3-4} = \underline{\quad .100 \quad} \text{ MAX (OHMS)}$$

HI POT - 50VRMS PAD 1 TO PAD 4 FOR 60 SEC.

TOLERANCES (EXCEPT AS NOTED)

$$.x=\pm$$

±

 $\cdot xx = \pm$

FRACTIONAL	
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
25	25
26	26
27	27
28	28
29	29
30	30
31	31
32	32
33	33
34	34
35	35
36	36
37	37
38	38
39	39
40	40
41	41
42	42
43	43
44	44
45	45
46	46
47	47
48	48
49	49
50	50
51	51
52	52
53	53
54	54
55	55
56	56
57	57
58	58
59	59
60	60
61	61
62	62
63	63
64	64
65	65
66	66
67	67
68	68
69	69
70	70
71	71
72	72
73	73
74	74
75	75
76	76
77	77
78	78
79	79
80	80
81	81
82	82
83	83
84	84
85	85
86	86
87	87
88	88
89	89
90	90
91	91
92	92
93	93
94	94
95	95
96	96
97	97
98	98
99	99
100	100

$$.xxx = \pm$$

±

THIS DRAWING, AND ALL INFORMATION HEREIN, IS PROPRIETARY TO COILCRAFT INC. AND SHALL NOT BE USED IN WHOLE OR IN PART WITHOUT COILCRAFT'S CONSENT.