


SMD Power Inductor CDRR157



Description

- Ferrite drum core construction.
- Magnetically shielded.
- L × W × H: 18.5 × 15.0 × 7.0mm Max.
- Product weight: 2.8g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40°C~+100°C (including coil's self temperature rise)
- Storage temperature range: -40°C~+100°C
- Solder reflow temperature: 260 °C peak.


Packaging

- Carrier tape and reel packaging.
- 12.9" diameter reel
- 300pcs per reel


Applications

- Ideally used in Portable Computers, Video Recorder, DSC/DVC, etc as DC-DC Converter inductors.

Dimension - [mm]



Land pattern and Schematics - [mm]



SMD Power Inductor CDRR157



Electrical Characteristics

Part Name	Stamp	Inductance (μ H) [within] ※1	D.C.R. (m Ω) Max. (Typ.) (at 20°C)	Saturation Current (A) ※2	Temperature rise current (A) ※3
CDRR157NP-1R3MC	1R3M	1.3 μ H $\pm$ 20%	5.7(4.5)	17.0	9.2
CDRR157NP-2R0MC	2R0M	2.0 μ H $\pm$ 20%	7.0(5.6)	13.4	9.0
CDRR157NP-2R7MC	2R7M	2.7 μ H $\pm$ 20%	8.3(6.6)	12.0	8.0
CDRR157NP-3R3MC	3R3M	3.3 μ H $\pm$ 20%	9.6(7.7)	10.8	7.5
CDRR157NP-4R7MC	4R7M	4.7 μ H $\pm$ 20%	12.9(10.3)	9.2	6.5
CDRR157NP-6R8MC	6R8M	6.8 μ H $\pm$ 20%	16.5(13.2)	7.6	6.0
CDRR157NP-100MC	100M	10 μ H $\pm$ 20%	25.0(20.0)	6.4	5.0
CDRR157NP-150MC	150M	15 μ H $\pm$ 20%	37.5(30.0)	5.0	3.8
CDRR157NP-220MC	220M	22 μ H $\pm$ 20%	47.0(37.5)	4.2	3.5
CDRR157NP-330MC	330M	33 μ H $\pm$ 20%	69.0(55.0)	3.5	2.7
CDRR157NP-470MC	470M	47 μ H $\pm$ 20%	105.0(84.0)	2.9	2.0
CDRR157NP-680MC	680M	68 μ H $\pm$ 20%	166.0(133)	2.4	1.6
CDRR157NP-101MC	101M	100 μ H $\pm$ 20%	244.0(195)	2.0	1.3
CDRR157NP-151MC	151M	150 μ H $\pm$ 20%	330.0(264)	1.6	1.1
CDRR157NP-221MC	221M	220 μ H $\pm$ 20%	485.0(388)	1.3	0.9
CDRR157NP-271MC	271M	270 μ H $\pm$ 20%	595.0(475)	1.2	0.8
CDRR157NP-331MC	331M	330 μ H $\pm$ 20%	738.0(590)	1.1	0.7
CDRR157NP-471MC	471M	470 μ H $\pm$ 20%	1000.0(800)	0.9	0.6
CDRR157NP-681MC	681M	680 μ H $\pm$ 20%	1544(1227)	0.75	0.5
CDRR157NP-102MC	102M	1000 μ H $\pm$ 20%	2388(1910)	0.60	0.4

※1. Inductance measuring condition: at 100 kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 90% of it's nominal value.













※3. Temperature rise current: The value of D.C. current when the temperature rise is $\Delta t=40^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).

SMD Power Inductor CDRR157



Saturation Current & Temperature Rise Graph

— L (20°C) — ΔT











SMD Power Inductor CDRR157



Saturation Current & Temperature Rise Graph



— L (20°C) — ΔT



SMD Power Inductor CDRR157



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
info@comp@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com