



(4.00 mm) .1575"

IJ5-04-05.0-L-S-1-TR

IJ5-01-05.0-L-S-1-TR



IJ5-04-05.0-L-D-1-TR



IJ5-08-05.0-L-S-1-TR

IJ5 SERIES

50 Ω HIGH ISOLATION RF JACKS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/IJ5

Shell Material:

Copper Alloy

Insulator Material:

Black LCP

Contact Material:

Copper Alloy

Dielectric Material:

Black LCP

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Current Rating (Vertical):

Signals: 2.36 A per pin

(2 adjacent pins powered)

Grounds: 4.4 A per pin

(2 adjacent pins powered)

Operating Temp Range:

-55 °C to +125 °C

Dielectric

Withstanding Voltage:

600 VAC

Working Voltage:


200 VAC

RoHS Compliant:

Yes

Mates with:

IP5

Single or
Double Row1, 2, 4, 6 or 8
Positions

IP5/IJ5 10 mm Stack Height	Frequency
Insertion Loss = 3 dB	10.5 GHz / 21.0 Gbps
Return Loss = 15 dB	5.5 GHz / 11.0 Gbps
Isolation = 60 dB	8.8 GHz / 17.6 Gbps
Isolation = 70 dB	7.6 GHz / 15.2 Gbps
Isolation = 80 dB	1.3 GHz / 2.6 Gbps

Complete test data available at www.samtec.com/IJ5 or contact sig@samtec.com

PROCESSING

Lead-Free Solderable:

Yes


RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

APPLICATION



OTHER SOLUTIONS

- Cable assembly (see IJ5C Series)

IJ5 — **JACKS PER ROW** — **05.0** — **PLATING** — **ROW OPTION** — **TAIL** — **"X"R**

-01, -02, -04, -06, -08

-L

= 10 μ" (0.25 μm)
Gold on contact area,
Matte Tin on tail

-S

= Single Row

-D
= Double Row
(Not available with -01)

-1

= (1.60 mm) .062"
board thickness

-TR

= Tape & Reel

-FR
= Full Reel Tape & Reel (must order max. quantity per reel; Contact Samtec for quantity breaks)

NO. OF JACKS	A
-01	(5.55) .219
-02	(9.55) .376
-04	(17.55) .691
-06	(25.55) 1.006
-08	(33.55) 1.321

