



## VEC Series

## Features

- $4\phi \sim 6.3\phi$ ,  $85^\circ\text{C}$ , 2,000 hours assured
- Vertical chip type miniaturized for 5.5mm, high capacitors
- Low Leakage Current Lead free reflow soldering is available
- Designed for surface mounting on high density PC board
- RoHS Compliance




Marking color: Black

## Specifications

Items	Performance																											
Category Temperature Range	$-40^\circ\text{C} \sim +85^\circ\text{C}$																											
Capacitance Tolerance	$\pm 20\%$ (at $120\text{Hz}, 20^\circ\text{C}$ )																											
Leakage Current (at $20^\circ\text{C}$ )	$I = 0.002\text{CV}$ or $0.5 (\mu\text{A})$ whichever is greater (after 2 minutes) Where, $C$ = rated capacitance in $\mu\text{F}$ $V$ = rated DC working voltage in $\text{V}$																											
Tan $\delta$ (at $120\text{Hz}, 20^\circ\text{C}$ )	<table border="1"> <thead> <tr> <th>Rated Voltage</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th></tr> </thead> <tbody> <tr> <td>Tan<math>\delta</math> (max)</td><td>0.28</td><td>0.24</td><td>0.20</td><td>0.14</td><td>0.12</td><td>0.10</td></tr> </tbody> </table>							Rated Voltage	6.3	10	16	25	35	50	Tan $\delta$ (max)	0.28	0.24	0.20	0.14	0.12	0.10							
Rated Voltage	6.3	10	16	25	35	50																						
Tan $\delta$ (max)	0.28	0.24	0.20	0.14	0.12	0.10																						
Low Temperature Characteristics (at $120\text{Hz}$ )	<p>Impedance ratio shall not exceed the values given in the table below.</p> <table border="1"> <thead> <tr> <th>Rated Voltage</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th></tr> </thead> <tbody> <tr> <td>Impedance Ratio</td><td><math>Z(-25^\circ\text{C})/Z(+20^\circ\text{C})</math></td><td>3</td><td>3</td><td>2</td><td>2</td><td>2</td></tr> <tr> <td></td><td><math>Z(-40^\circ\text{C})/Z(+20^\circ\text{C})</math></td><td>8</td><td>5</td><td>4</td><td>3</td><td>3</td></tr> </tbody> </table>							Rated Voltage	6.3	10	16	25	35	50	Impedance Ratio	$Z(-25^\circ\text{C})/Z(+20^\circ\text{C})$	3	3	2	2	2		$Z(-40^\circ\text{C})/Z(+20^\circ\text{C})$	8	5	4	3	3
Rated Voltage	6.3	10	16	25	35	50																						
Impedance Ratio	$Z(-25^\circ\text{C})/Z(+20^\circ\text{C})$	3	3	2	2	2																						
	$Z(-40^\circ\text{C})/Z(+20^\circ\text{C})$	8	5	4	3	3																						
Endurance	<table border="1"> <thead> <tr> <th>Test Time</th><th>2,000 Hrs</th></tr> </thead> <tbody> <tr> <td>Capacitance Change</td><td>Within <math>\pm 20\%</math> of initial value</td></tr> <tr> <td>Tan<math>\delta</math></td><td>Less than 200% of specified value</td></tr> <tr> <td>Leakage Current</td><td>Within specified value</td></tr> </tbody> </table>							Test Time	2,000 Hrs	Capacitance Change	Within $\pm 20\%$ of initial value	Tan $\delta$	Less than 200% of specified value	Leakage Current	Within specified value													
Test Time	2,000 Hrs																											
Capacitance Change	Within $\pm 20\%$ of initial value																											
Tan $\delta$	Less than 200% of specified value																											
Leakage Current	Within specified value																											
	<p>* The above Specifications shall be satisfied when the capacitors are restored to <math>20^\circ\text{C}</math> after the rated voltage applied for 2,000 hours at <math>85^\circ\text{C}</math>.</p>																											
Shelf Life Test	<table border="1"> <thead> <tr> <th>Test Time</th><th>1,000 Hrs</th></tr> </thead> <tbody> <tr> <td>Capacitance Change</td><td>Within <math>\pm 20\%</math> of initial value</td></tr> <tr> <td>Tan<math>\delta</math></td><td>Less than 200% of specified value</td></tr> <tr> <td>Leakage Current</td><td>Within specified value</td></tr> </tbody> </table>							Test Time	1,000 Hrs	Capacitance Change	Within $\pm 20\%$ of initial value	Tan $\delta$	Less than 200% of specified value	Leakage Current	Within specified value													
Test Time	1,000 Hrs																											
Capacitance Change	Within $\pm 20\%$ of initial value																											
Tan $\delta$	Less than 200% of specified value																											
Leakage Current	Within specified value																											
	<p>* The above Specifications shall be satisfied when the capacitors are restored to <math>20^\circ\text{C}</math> after exposing them for 1,000 hours at <math>85^\circ\text{C}</math> without voltage applied.</p>																											
Ripple Current & Frequency Multipliers	<table border="1"> <thead> <tr> <th>Frequency (Hz)</th><th>50</th><th>120</th><th>1k</th><th>10k up</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>0.7</td><td>1.0</td><td>1.3</td><td>1.4</td></tr> </tbody> </table>							Frequency (Hz)	50	120	1k	10k up	Multiplier	0.7	1.0	1.3	1.4											
Frequency (Hz)	50	120	1k	10k up																								
Multiplier	0.7	1.0	1.3	1.4																								


## Diagram of Dimensions



Lead Spacing and Diameter							Unit: mm
$\phi D$	L	A	B	C	W	P	$\pm 0.2$
4	$5.3 \pm 0.2$	4.3	4.3	5.1	$0.5 \sim 0.8$	1.0	
5	$5.3 \pm 0.2$	5.3	5.3	5.9	$0.5 \sim 0.8$	1.5	
6.3	$5.3 \pm 0.2$	6.6	6.6	7.2	$0.5 \sim 0.8$	2.0	

Dimension:  $\phi D \times L(\text{mm})$ Ripple Current: mA/rms at  $120\text{ Hz}, 85^\circ\text{C}$ 

## Marking



## Dimension &amp; Permissible Ripple Current

V. DC $\mu\text{F}$ Contents	6.3V (0J)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		
	$\phi D \times L$	mA											
1 010												$4 \times 5.3$	10
2.2 2R2												$4 \times 5.3$	15
3.3 3R3												$4 \times 5.3$	19
4.7 4R7							$4 \times 5.3$	19	$4 \times 5.3$	20	$5 \times 5.3$	26	
10 100			$4 \times 5.3$	23	$4 \times 5.3$	26	$5 \times 5.3$	32	$5 \times 5.3$	34	$6.3 \times 5.3$	44	
22 220	$4 \times 5.3$	31	$5 \times 5.3$	39	$5 \times 5.3$	44	$6.3 \times 5.3$	55	$6.3 \times 5.3$	59			
33 330	$5 \times 5.3$	44	$5 \times 5.3$	48	$6.3 \times 5.3$	63	$6.3 \times 5.3$	67					
47 470	$5 \times 5.3$	52	$6.3 \times 5.3$	67	$6.3 \times 5.3$	75							
100 101	$6.3 \times 5.3$	89	$6.3 \times 5.3$	98									

## Part Numbering System

VEC series	10 $\mu\text{F}$	$\pm 20\%$	16V	Carrier Tape	$4\phi \times 5.3\text{L}$	Pb-free and PET coating case
<b>VEC</b>	<b>100</b>	<b>M</b>	<b>1C</b>	<b>TR</b>	<b>0405</b>	Lead Wire and Coating Type
Series name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case size

Note: For more details, please refer to "Part Numbering System (SMD Type)" on page 12.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anderson Power Products:](#)

[5804B](#) [5810B](#)