




LEAD FREE PRODUCT NO.
72862-X01LF



See Sofix Shielded I/O



PRODUCT SPECIFICATION: GS-12-308
PACKAGING SPECIFICATION: GS-14-796
APPLICATION SPECIFICATION: GS-20-019.

MATERIAL:

1	WAFER	30 % GLASS FILLED LCP
2	SHROUD	30 % GLASS FILLED POLYAMIDE FLAME RETARDANT ACC. TO UL-94
3	COVER	ZINC ALLOY
4	TERMINAL	TINBRONZE
5	FERRULE	TINBRONZE
6	SCREW	STEEL
7	CLIP	INOX
8	FERRULE HOLDER	ZINC ALLOY


9-ROHS INFORMATIONS:

- This "LF" product meets European Union Directives and other country regulations as described in GS-22-008.
- This product is not intended to be exposed to a manufacturing solder process
- Packaging spec: See GS-14-920

rev	ecn no	dr	date
A	B30048	SVH	2003/02/26
B	LS4129	JTA	2004/12/15
C	LS05-0102	JTA	2005/08/11
D	LS06-0107	LGO	2006/08/30
E	LS06-0143	LGO	2006/09/25
F	LS07-0285	JTA	2007/11/09
-	-	-	-

72862-X01LF	
72862-101LF	Standard Product
72862-201LF	Customer Special



www.fciconnect.com			surface 0.8 / ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	S.Van Humbeeck	2003/02/25	ANGULAR	LINEAR	0.X	±0.3	size A4	Scale 1:1		
Eng	J.Taron	2004/11/20			0.XX	±0.1				
Chr	P.Legare	2004/11/20			0° ±2°	0.XXX				
Appr	P.Legare	2004/11/20	Product family				SOFIX	Spec ref		RELEASED
		title SHIELDED CABLE CONNECTOR 8 POS - SOLDER				dwg no 72862_C		Rev. F		
		catalog no				CUSTOMER COPY		sheet 1 of 3		

REV F - 2006-04-17



PDM: Rev:F


STATUS:Released

Printed: Aug 01, 2010



Copyright FCI.



www.fciconnect.com			surface 0.8 ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	S. Van Humbee	2003/02/25	ANGULAR	LINEAR	0.X	±0.3	size A4	Scale 1:1		
Eng	J. Taron	2004/11/20			0.XX	±0.1				
Chr	P. Legare	2004/11/20			0° ±°	0.XXX	±0.05	ECN		LS07-285
Appr	P. Legare	2004/11/20	Product family			SOFIX		Spec ref		RELEASED
		title	SHIELDED CABLE CONNECTOR				dwg no 72862_C		Rev. F	
		8 POS - SOLDER								
		catalog no				CUSTOMER COPY			sheet 2 of 3	

LEAD-FREE PRODUCTS:(see note 9)

Kit: 72862-X01LF	
COMPONENTS	QTY
COVER UPPER	1
COVER LOWER	1
FERRULE OUTER	2
FERRULE INNER	1
SCREW	2
SHROUD	1
FERRULE HOLDER	1
WAFER	2
CLIP	1




Dimension with oval around are critical dimensions including any attached geometrical tolerance. Other features or stand-alone geometrical tolerances being critical have a note "CRITICAL FEATURE" below the item

A symbol  (x: drawing current revision) will be next to any dimension, view or note which has been modified with the current drawing revision



Copyright FCI.

www.fciconnect.com			surface 0.8 ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	S. Van Humbee	2003/02/25	ANGULAR	LINEAR	0.X	±0.3	size A4	Scale 1:1		
Eng	J. Taron	2004/11/20			0.XX	±0.1				
Chr	P. Legare	2004/11/20			0.XXX	±0.05				
Appr	P. Legare	2004/11/20	Product family			SOFIX		Spec ref		RELEASED
		title	SHIELDED CABLE CONNECTOR				dwg no	72862_C		Rev. F
			8 POS - SOLDER							
			catalog no							
			CUSTOMER COPY				sheet 3 of 3			

REV F - 2006-04-17

PDM: Rev:F

STATUS:Released

Printed: Aug 01, 2010