


Plug-in units with IEL inserter/extractor handle for CompactPCI/VME64x applications



Dimension 3 / 6 U



Product illustrations are exemplary illustrations and can deviate from supplied products.

Part no.: 20848-592

Features:

- In accordance with IEEE 1101.10 and IEC 60297-3-102
- Codable to IEC 60297-3-103/ IEEE 1101.10
- Front panel shielded
- Suitable for insertion and extraction forces up to 700 N (per pair)
- Suitable for fitting microswitches



Technical Information:

Description	Height	Width
Front assembly	6 U	4 HP

Downloads:

3D PDF (STEP/PDF) (Log in required) 
User Manual (Log in required)
User Manual (Log in required)

To gain access to the additional information you must log in.
If you do not yet have a user name, you may register here.

Delivery comprises: kit

Item	Qty	Description
1	1	U front panel, Al, front anodised, rear conductive
2	1	EMC textile gasketing, core: foam, sleeve: textile cladding, CuNi coating
3	2	Handle with integrated alignment pin for perforated strip and guide rails, lever: plastic, PC, black, RAL 9005, key: plastic, PC, light grey, RAL 7035
7	2	Pozidrive collar screw M2.5 × 12.3, St, nickel-plated
8	2	Panhead screw with Torx, M2.5 × 6, St, zinc-plated, self-locking
9	2	Washer A2.7, DIN 125, St, nickel-plated
10	2	Panhead screw with Torx, M2.5 × 6, St, nickel-plated

Accessories:

Part no.	Description	
20817-606	Microswitch for handles, CompactPCI/VME64x application PU 10 pieces	Add to basket