


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
948	A	RELEASED	HYO	5/10/01	JWM	8/23/01	DJC	8/24/01



SPC Type No.	Replaces Incandescent Types	Volts (AC/DC)	Current	Emitted Color & Material	Wave Length peak (nm)	Luminous Intensity Typical: (mcd) See Note 1	Viewing Angle (deg)
SPC10554	24MB, 28MB 1818, 1843, 1819 1829, 757, 1820 1864, 313, 1873	24-28 AC/DC	13-15mA	White	mixed	1560	50°
SPC10555			13-15mA	Red	660	4500	30°
SPC10556			13-15mA	Green	520	2400	45°
SPC10557			13-15mA	Yellow	595	2500	30°
SPC10558	120MB	110-130 AC/DC	3-5mA	White	mixed	1560	50°
SPC10559			3-5mA	Red	660	4500	30°
SPC10560			3-5mA	Green	520	2400	45°
SPC10561			3-5mA	Yellow	595	2500	30°

**NOTES:**

1. mcd ratings are prior to basing of product
2. Lens Color: Water clear
3. Typical Useful Life: 20000 ~ 40000 Hours

SPC-F004.DWG

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



**SPC TECHNOLOGY**

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
HISHAM ODISH	5/10/01
CHECKED BY:	DATE:
JEFF MCVICKER	8/23/01
APPROVED BY:	DATE:
DANIEL CAREY	8/24/01

DRAWING TITLE:  
**SINGLE CONTACT MINI BAYONET LED LAMP**

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-334	TA-334.DWG	A

SCALE: NTS      U.O.M.: MILLIMETERS      SHEET: 1 OF 1