





REV.	DATE	ECR NO.	DESCRIPTION
NC	04/02/11	XXXXXX	INITIAL RELEASE



RECOMMENDED PCB LAYOUT



- FREQUENCY RANGE: DC 0–26.5 GHz
- PCB THICKNESS=1.6 mm

3	CONTACT PIN	BRASS	GOLD	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	BERYLLIUM COPPER	GOLD	1
DESCRIPTION	MATERIAL	FINISH	QTY	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE
	DRAWN M.ZHANG	04/02/11
	CHECKED	
	ISSUED	
	SHEET 1 OF 1	
CAD FILE C:/CONNEX/302114.DWG		

Amphenol Connex			
PART DESCRIPTION SMP END LAUNCH RECEPT. JACK, LIMITED DETENT (FOR 1.6MM THICK PCB)			
PART NO. 302114			
DWG. NO. 302114.DWG	REV. NC	SIZE A	SCALE NA