







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HG	-		D	REV PER ECR-10-001039	20JAN2010	JZ	RZ
			E	REV PER ECR-11-015981	05SEP2011	LL	CT
			F	UPDATE OPERATING WAVELENGTH 1260-1625nm	21AUG2012	PL	RZ


PERFORMANCE REQUIREMENTS:
OPERATING WAVELENGTH: 1260-1625nm
REFLECTANCE: AVG. -55dB
OPERATING TEMPERATURE: -40°C TO +85°C
ATTENUATION TOLERANCE, AMBIENT:
FOR 0 dB ATTENUATORS: +0.5dB MAX
FOR ATTENUATORS < 5dB: ±0.5dB
FOR ATTENUATORS ≥ 5dB: ±10% OF NOMINAL ATTENUATION VALUE
MEASURED WITH REFERENCE QUALITY LAUNCH LEADS:
- REFLECTANCE: ≤ -60dB
- FIBER CORE ECCENTRICITY < 0.3um



20	2-1693560-0
19	1-1693560-9
18	1-1693560-8
17	1-1693560-7
16	1-1693560-6
15	1-1693560-5
14	1-1693560-4
13	1-1693560-3
12	1-1693560-2
11	1-1693560-1
10	1-1693560-0
9	1693560-9
8	1693560-8
7	1693560-7
6	1693560-6
5	1693560-5
4	1693560-4
3	1693560-3
2	1693560-2
1	1693560-1
0	0-1693560-0
NOMINAL ATTENUATION VALUE (dB)	
PART NUMBER	

⚠ OBSOLETE

NOTES:
⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. MCCORMICK CHK E. HOPKINS APVD S. BUCHTER		01NOV2006 01NOV2006 01NOV2006		 TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		ATTENUATOR, OPTICAL, BUILD OUT, SM, LC/UPC, BROADBAND, BANDPASS							
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		PRODUCT SPEC 108-2221 APPLICATION SPEC 114-1129		SIZE A2		CAGE CODE 00779		DRAWING NO C=1693560		RESTRICTED TO -	
MATERIAL -		-		WEIGHT -		CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 1		REV F	