


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.98 ohms max.
D.C. RESISTANCE	4-5 @20°C	1.20 ohms max.
D.C. RESISTANCE	6-9 @20°C	0.24 ohms max.
INDUCTANCE	1-2 10kHz, 200mVAC, Ls	1.08mH ±10%
INDUCTANCE	1-2 10kHz, 200mVAC, 1.6ADC, Ls	800uH min.
DIELECTRIC	1-9 tie(3+4),4000VAC, 1 second	-
DIELECTRIC	1-5 1800VAC, 1 second	-
TURNS RATIO	(1-2):(4-5)	2.023:1, ±2%
TURNS RATIO	(1-2):(6-9)	4.047:1, ±2%



REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64	Decimals: ±.005 [1.3] Footprint: ±.001 [0.3]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0029 www.we-online.com/midcom				TRANSFORMER	750340505
6B	7/11			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750340505	
6A	8/09	SEE REVISION SHEET FOR	REVISION LEVEL				SPECIFICATION SHEET 1 OF 1

