



LOC		DIST		ZONE		LIT		REVISED PER		DATE	APPD
6	14							A	0720-0230-93	2/28/94	AMP

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed
16-14 AWG STRANDED		16-14 AWG STRANDED
LR7189 Certified		MILITARY P/N AND CLASS
NOT CERTIFIED		NOT APPLICABLE

STAMP AMP 16-14* APPROX AS SHOWN
MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE USER SHOULD BE ADVISED BY THE LATEST VERSION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLG DEC ± .005 3 PLG DEC ± .010 ANGLES MATERIAL COPPER PER ASTM B-152 ANNEALED		DR 3-1-93 IA BRINKMAN CHK 3-1-93 DA PATTERSON APPD 3-1-93 DE MILLER APPD 3-1-93 JL HECKLEY PRODUCT SPEC	NAME AMP Incorporated Harrisburg, PA 17125-3508
FINISH TIN PLATE 0.00254 [0.00100] MIN THK PER MIL-T-10727	APPLICATION SPEC	SIZE CAGE CODE 00779	DRAWING NO 32464
WEIGHT	SCALE 10:1	SHEET	1 OF 1