

TMM

TMM Series  
1.27mm pitch



X	-X	-XX	-X
---	----	-----	----

- Type**  
 1=IDC Male  
 2=IDC Transition Plug  
 3=DIP Male Straight  
 4=DIP Female Straight  
 5=DIP Female R/A  
 6=SMT Female Straight




- Locking**  
 L= with Lock  
 0= w/o Lock

- No. of Positions**  
 04= 04 Positions  
 :  
 :  
 26= 26 Positions

- Packaging**  
 1= Tape&Reel+cap  
 2= Tube  
 3= Bag  
 4= Tape&Reel w/o cap

**TMM-1**  
(IDC Male)

Circuits	Dimension	
	A	B
4	8.45	2.54
6	10.99	5.08
8	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48



**General Specification**

**Materials and Finish :**

**Insulator:** Themoplastic, UL 94V-0, Color in Red  
**Contact :** Phosphor Bronze, Tin plated.

**Electrical :**

**Contact Resistance:** 20 mΩ max. at 1A DC  
**Insulation Resistance:** 1000 MΩ min, at 500 V/DC.  
**Dielectric Withstanding Voltage :** 500 V AC/RMS 60Hz for one minute.  
**Current Rating :** 1.5A max,  
**Voltage Rating :** 230V AC/RMS 60Hz, DC

**Environment:**

**Operating Temperature:** -40 degree C to +105 degree C

TMM

TMM Series  
1.27mm pitch



- **X** - **-X** - **-XX** - **-X**

Type

- 1=IDC Male
- 2=IDC Transition Plug
- 3=DIP Male Straight
- 4=DIP Female Straight
- 5=DIP Female R/A
- 6=SMT Female Straight

Locking

- L= with Lock
- 0= w/o Lock


No. of Positions

- 04= 04 Positions
- :
- :
- 26= 26Positions




Packaging

- 1= Tape&Reel+cap
- 2= Tube
- 3= Bag
- 4= Tape&Reel w/o cap

TMM-2  
(IDC Plug)



Circuits	Dimension	
	A	B
4	8.45	2.54
6	10.99	5.08
8	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48



PCB Layout

General Specification

Materials and Finish :

**Insulator:** Themoplastic, UL 94V-0, Color in Red  
**Contact :** Phosphor Bronze, Tin plated.

Electrical :


**Contact Resistance:** 20 mΩ max. at 1A DC  
**Insulation Resistance:** 1000 MΩ min, at 500 V/DC.  
**Dielectric Withstanding Voltage :** 500 V AC/RMS 60Hz for one minute.  
**Current Rating :** 1.5 A max,  
**Voltage Rating :** 230V AC/RMS 60Hz, DC

Environment :

**Operating Temperature:** -40 degree C to +105 degree C

TMM

TMM Series  
1.27mm pitch



- X -X -XX -X



**Type**  
 1=IDC Male  
 2=IDC Transition Plug  
 3=DIP Male Straight  
 4=DIP Female Straight  
 5=DIP Female R/A  
 6=SMT Female Straight

**Locking**  
 L= with Lock  
 0= w/o Lock




**No. of Positions**  
 04= 04 Positions  
 :  
 :  
 26= 26 Positions

**Packaging**  
 1= Tape&Reel+cap  
 2= Tube  
 3= Bag  
 4= Tape&Reel w/o cap

TMM-3  
(Dip Male ST)



Mating Height Draw.



Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
4	7.20	2.54	12	17.36	12.70	20	27.52	22.86
6	9.74	5.08	14	19.90	15.24	22	30.06	25.40
8	12.28	7.62	16	22.44	17.78	24	32.60	27.94
10	14.82	10.16	18	24.98	20.32	26	35.14	30.48

General Specification

Materials and Finish :

**Insulator:** Glass-reinforce thermoplastic, UL 94V-0, Nylon, Color in Red.  
**Contact :** Phosphor Bronze, Tin plated.

Electrical :


**Contact Resistance:** 20 mΩ max. at 1.5A DC  
**Insulation Resistance:** 1000 MΩ min, at 500 V/DC.  
**Dielectric Withstanding Voltage :** 500 V AC/RMS 60Hz for one minute.  
**Current Rating :** 1.5A max,  
**Voltage Rating :** 230V AC/RMS 60Hz, DC

Environment :

**Operating Temperature:**  
 -40 degree C to +105 degree C



TMM

TMM Series  
1.27mm pitch



X	-X	-XX	-X
<b>Type</b> 1=IDC Male 2=IDC Transition Plug 3=DIP Male Straight 4=DIP Female Straight 5=DIP Female R/A 6=SMT Female Straight	<b>Locking</b> L= with Lock 0= w/o Lock	<b>No. of Positions</b> 04= 04 Positions : : 26= 26 Positions	<b>Packaging</b> 1= Tape&Reel+cap 2= Tube 3= Bag 4= Tape&Reel w/o cap

**TMM-4-0**  
(Dip Female ST)




Pos	A	B	C	Pos	A	B	C
4	7.00	3.81	5.60	16	22.24	19.05	20.84
6	9.54	6.35	8.14	18	24.78	21.59	23.38
8	12.08	8.89	10.68	20	27.32	24.13	25.92
10	14.62	11.43	13.22	22	29.86	26.67	28.46
12	17.16	13.97	15.76	24	32.40	29.21	31.00
14	19.70	16.51	18.30	26	34.94	31.75	33.54

**General Specification**

<p><b>Materials and Finish :</b></p> <p><b>Insulator:</b> Glass-reinforce thermo plastic, UL 94V-0, Nylon, Color in Red.</p> <p><b>Contact :</b> Phosphor Bronze, Tin plated.</p>	<p><b>Electrical :</b></p> <p><b>Contact Resistance:</b> 20 mΩ max. at 1A DC</p> <p><b>Insulation Resistance:</b> 1000 MΩ min, at 500 V/DC.</p> <p><b>Dielectric Withstanding Voltage :</b> 500 V AC/RMS 60Hz for one minute.</p> <p><b>Current Rating :</b> 1.5A max.</p> <p><b>Voltage Rating :</b> 230V AC/RMS 60Hz, DC</p>	<p><b>Envirement :</b></p> <p><b>Operating Temperature:</b> -40 degree C to +105 degree C</p>
---	--	---

TMM

TMM Series  
1.27mm pitch



- **X**      **-X**      **-XX**      **-X**

Type

- 1=IDC Male
- 2=IDC Transition Plug
- 3=DIP Male Straight
- 4=DIP Female Straight
- 5=DIP Female R/A
- 6=SMT Female Straight

Locking

- L= with Lock
- 0= w/o Lock

No. of Positions



- 04= 04 Positions
- :
- :
- 26= 26 Positions

Packaging




- 1= Tape&Reel+cap
- 2= Tube
- 3= Bag
- 4= Tape&Reel w/o cap

TMM-5-0

(Dip Female R/A)



Mating Height Draw.



PCB Layout


Pos	A	B	C	Pos	A	B	C
4	7.00	3.81	5.60	16	22.24	19.05	20.84
6	9.54	6.35	8.14	18	24.78	21.59	23.38
8	12.08	8.89	10.68	20	27.32	24.13	25.92
10	14.62	11.43	13.22	22	29.86	26.67	28.46
12	17.16	13.97	15.76	24	32.40	29.21	31.00
14	19.70	16.51	18.30	26	34.94	31.75	33.54

General Specification

<p><b>Materials and Finish :</b></p> <p><b>Insulator:</b> Glass-reinforce thermo plastic, UL 94V-0, Nylon, Color in Red.</p> <p><b>Contact :</b> Phosphor Bronze, Tin plated.</p>	<p><b>Electrical :</b></p> <p><b>Contact Resistance:</b> 20 mΩ max. at 1A DC</p> <p><b>Insulation Resistance:</b> 1000 MΩ min, at 500 V/DC.</p> <p><b>Dielectric Withstanding Voltage :</b> 500 V AC/RMS 60Hz for one minute.</p> <p><b>Current Rating :</b> 1.5A max</p> <p><b>Voltage Rating :</b> 230V AC/RMS 60Hz, DC</p>	<p><b>Environment :</b></p> <p><b>Operating Temperature:</b> -40 degree C to +105 degree C</p>
---	---	--

TMM

TMM Series  
1.27mm pitch



Type

- 1=IDC Male
- 2=IDC Transition Plug
- 3=DIP Male Straight
- 4=DIP Female Straight
- 5=DIP Female R/A
- 6=SMT Female Straight

Locking

- L= with Lock
- 0= w/o Lock

No. of Positions





- 04= 04 Positions
- :
- :
- 26= 26 Positions

Packaging

- 1= Tape&Reel+cap
- 2= Tube
- 3= Bag
- 4= Tape&Reel w/o cap

TMM-5-L

(Dip Female R/A, w/ Lock)



PCB Layout

Pos	Dim.A	Dim.B	Dim.C	Pos	Dim.A	Dim.B	Dim.C
4	9.70	3.81	5.60	16	24.94	19.05	20.84
6	12.24	6.35	8.14	18	27.48	21.59	23.38
8	14.78	8.89	10.68	20	30.02	24.13	25.92
10	17.32	11.43	13.22	22	32.56	26.67	28.46
12	19.86	13.97	15.76	24	35.10	29.21	31.00
14	22.40	16.51	18.30	26	37.64	31.75	33.54

General Specification

Materials and Finish :

**Insulator:** Glass-reinforce thermo plastic, UL 94V-0, Nylon, Color in Red.  
**Contact :** Phosphor Bronze, Tin plated.

Electrical :


**Contact Resistance:** 20 mΩ max. at 1A DC  
**Insulation Resistance:** 1000 MΩ min, at 500 V/DC.  
**Dielectric Withstanding Voltage :** 500 V AC/RMS 60Hz for one minute.  
**Current Rating :** 1.5A max,  
**Voltage Rating :** 230V AC/RMS 60Hz, DC

Environment :

**Operating Temperature:**  
-40 degree C to +105 degree C

**TMM**






TMM Series  
1.27mm pitch



<b>X</b>	<b>-X</b>	<b>-XX</b>	<b>-X</b>
----------	-----------	------------	-----------

- |  |  |  |  |
|--|--|--|--|
| <p><b>Type</b><br/>1=IDC Male<br/>2=IDC Transition Plug<br/>3=DIP Male Straight<br/>4=DIP Female Straight<br/>5=DIP Female R/A<br/>6=SMT Female Straight</p> | <p><b>Locking</b><br/>L= with Lock<br/>0= w/o Lock</p> | <p><b>No. of Positions</b><br/>04= 04 Positions<br/>:<br/>:<br/>26= 26 Positions</p> | <p><b>Packaging</b><br/>1= Tape&amp;Reel+cap<br/>2= Tube<br/>3= Bag<br/>4= Tape&amp;Reel w/o cap</p> |
|--|--|--|--|

**TMM-6-0**  
(SMT Female ST)




Pos	A	B	C	Pos	A	B	C
4	7.00	3.81	5.60	16	22.24	19.05	20.84
6	9.54	6.35	8.14	18	24.78	21.59	23.38
8	12.08	8.89	10.68	20	27.32	24.13	25.92
10	14.62	11.43	13.22	22	29.86	26.67	28.46
12	17.16	13.97	15.76	24	32.40	29.21	31.00
14	19.70	16.51	18.30	26	34.94	31.75	33.54

**General Specification**

<p><b>Materials and Finish :</b></p> <p><b>Insulator:</b> Glass-reinforce thermo plastic, UL 94V-0, Nylon, Color in Red <b>Contact :</b> Phosphor Bronze, Tin plated.</p>	<p><b>Electrical :</b></p> <p><b>Contact Resistance:</b> 20 mΩ max. at 1A DC <b>Insulation Resistance:</b> 1000 MΩ min, at 500 V/DC. <b>Dielectric Withstanding Voltage :</b> 500 V AC/RMS 60Hz for one minute. <b>Current Rating :</b> 1.5 A max <b>Voltage Rating :</b> 230V AC/RMS 60Hz, DC</p>	<p><b>Environment :</b></p> <p><b>Operating Temperature:</b> -40 degree C to +105 degree C</p>
---	--	--

TMM



TMM Series  
1.27mm pitch



X	-X	-XX	-X
---	----	-----	----

Type	Locking	No. of Positions	Packaging
1=IDC Male	L= with Lock	04= 04 Positions	1= Tape&Reel+cap
2=IDC Transition Plug	0= w/o Lock	:	2= Tube
3=DIP Male Straight		:	3= Bag
4=DIP Female Straight		26= 26 Positions	4= Tape&Reel w/o cap
5=DIP Female R/A			
6=SMT Female Straight			

TMM-6-L  
(SMT Female ST w/lock)



PCB Layout

Pos	A	B	C	Pos	A	B	C
4	9.70	3.81	5.60	16	24.94	19.05	20.84
6	12.24	6.35	8.14	18	27.48	21.59	23.38
8	14.78	8.89	10.68	20	30.02	24.13	25.92
10	17.32	11.43	13.22	22	32.56	26.67	28.46
12	19.86	13.97	15.76	24	35.10	29.21	31.00
14	22.40	16.51	18.30	26	37.64	31.75	33.54

General Specification

<p><b>Materials and Finish :</b></p> <p><b>Insulator:</b> Glass-reinforce thermo plastic, UL 94V-0, Nylon, Color in Red.</p> <p><b>Contact :</b> Phosphor Bronze, Tin plated.</p>	<p><b>Electrical :</b></p> <p><b>Contact Resistance:</b> 20 mΩ max. at 1A DC</p> <p><b>Insulation Resistance:</b> 1000 MΩ min, at 500 V/DC.</p> <p><b>Dielectric Withstanding Voltage :</b> 500 V AC/RMS 60Hz for one minute.</p> <p><b>Current Rating :</b> 1.5A max,</p> <p><b>Voltage Rating :</b> 230V AC/RMS 60Hz, DC</p>	<p><b>Environment :</b></p> <p><b>Operating Temperature:</b> -40 degree C to +105 degree C</p>
---	--	--