


## Data Sheet 2500 Rev.—

## Features

- Diffused Junction
- Low Leakage
- Low Cost
- High Surge Current Capability
- Low Cost Construction Utilizing Void-Free Molded Plastic Technique



## Mechanical Data

- Case: Molded Plastic
- Terminals: Plated Terminals Solderable per MIL-STD-202, Method 208
- Polarity: Color Ring Denotes Cathode End
- Weight: 1.8 grams (approx.)
- Mounting Position: Any
- Marking: Color Band

Dim	AR		ARS	
	Min	Max	Min	Max
A	0.382(9.70)	0.409(10.4)	0.327(8.30)	0.350(8.90)
B	0.217(5.50)	0.224(5.70)	0.217(5.50)	0.224(5.70)
C	0.236(6.00)	0.252(6.40)	0.236(6.00)	0.252(6.40)
D	0.165(4.20)	0.185(4.70)	0.165(4.20)	0.185(4.70)

All Dimensions in inch(mm)

S Suffix Designates ARS Package

No Suffix Designates AR Package

Maximum Ratings and Electrical Characteristics @T<sub>A</sub>=25°C unless otherwise specified

Single Phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	AR/S 25A	AR/S 25B	AR/S 25D	AR/S 25G	AR/S 25J	AR/S 25K	AR/S 25M	Unit
Peak Repetitive Reverse Voltage	V <sub>RRM</sub>								
Working Peak Reverse Voltage	V <sub>RWM</sub>	50	100	200	400	600	800	1000	V
DC Blocking Voltage	V <sub>R</sub>								
RMS Reverse Voltage	V <sub>R(RMS)</sub>	35	70	140	280	420	560	700	V
Average Rectified Output Current @T <sub>c</sub> = 150°C	I <sub>o</sub>				25				A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method) at T <sub>j</sub> = 150°C	I <sub>FSM</sub>				400				A
Forward Voltage @I <sub>F</sub> = 25A	V <sub>FM</sub>				1.0				V
Peak Reverse Current @T <sub>A</sub> = 25°C At Rated DC Blocking Voltage @T <sub>A</sub> = 100°C	I <sub>RM</sub>				5.0				µA
Reverse Recovery Time (Note 1)	t <sub>rr</sub>				250				µS
Typical Junction Capacitance (Note 2)	C <sub>j</sub>				300				pF
Typical Thermal Resistance Junction to Case (Note 3)	R <sub>θJC</sub>				1.0				K/W
Operating and Storage Temperature Range	T <sub>j</sub> , T <sub>STG</sub>				-50 to +175				°C
Polarity and Voltage Denotation Color Band		Red	Yellow	Silver	Orange	Green	Blue	Violet	

\*Glass passivated forms are available upon request

- Note: 1. Measured with IF = 0.5A, IR = 1.0A, IRR = 0.25A  
 2. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.  
 3. Thermal Resistance: Junction to case, single side cooled.




Fig. 1 Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics




Fig. 3 Max Non-Repetitive Peak Fwd Surge Current




Fig. 4 Typical Junction Capacitance