

NTE1383 Integrated Circuit Dual Audio Power Amp, 5.1W/Ch (10.5W BTL)

Description:

The NTE1383 is an integrated circuit in an 18-Lead DIP designed for use as an audio output with low noise, low distortion, and high output for a wide range of power supply voltages and load resistance. Two built-in amplifiers provide dual or BTL operation. Typical applications include radio cassette recorder, tape recorder, car stereo, and home entertainment.

Features:

- High Output Power, Dual or BTL Circuit Operation
- Wide Output Power Setting Range
- Wide Supply Voltage Range
- Incorporates an Automatic Operating Point Stabilizer Circuit
- Low Distortion, Low 1/f Noise, and Low Shock Noise
- High Audio Channel Separation
- Incorporates a Phase Converter

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Supply Voltage (Note 1), V_{CC} 20V
 Supply Current, I_{CC} 4A
 Power Dissipation ($T_A = +60^\circ\text{C}$), P_D 14W
 Operating Ambient Temperature Range, T_{opr} -30° to $+75^\circ\text{C}$
 Storage Temperature Range, T_{stg} -55° to $+150^\circ\text{C}$

Note 1. V_{CC} at operation mode = 20V (Stabilized power source).

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
Quiescent Circuit Current	I_{CQ}	$V_{CC} = 9V$	$V_i = 0$	20	35	55	mA
		$V_{CC} = 12V$		21	40	65	mA
		$V_{CC} = 13.2V$		22	40	66	mA

Electrical Characteristics (Cont'd): ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
BTL (R _L = 8Ω, f = 1kHz)							
Voltage Gain	G _V	V _{CC} = 9V	V _i = 4mV	40	43	46	dB
		V _{CC} = 12V		40	43	46	dB
		V _{CC} = 13.2V		40	43	46	dB
Total Harmonic Distortion	THD	V _{CC} = 9V	V _i = 4mV	–	0.15	1.0	%
		V _{CC} = 12V		–	0.15	1.0	%
		V _{CC} = 13.2V		–	0.15	1.0	%
Output Power	P _O	V _{CC} = 9V	THD = 10%	4.5	5.0	–	W
		V _{CC} = 12V		8.0	9.0	–	W
		V _{CC} = 13.2V		9.4	10.5	–	W
Output Noise Voltage	V _{no}	V _{CC} = 9V	V _i = 0, R _g = 3.9kΩ	–	0.3	1.0	mV
		V _{CC} = 12V	V _i = 0, R _g = 10kΩ	–	0.5	2.0	mV
		V _{CC} = 13.2V	–	0.7	2.0	mV	
Output Offset Voltage	V _{O(offset)}	V _{CC} = 9V	V _i = 0	–10	–	+10	mV
		V _{CC} = 12V		–12	–	+12	mV
		V _{CC} = 13.2V		–12	–	+12	mV
Dual (R _L = 4Ω, f = 1kHz)							
Voltage Gain	G _V	V _{CC} = 9V	V _i = 4mV	41	44	47	dB
		V _{CC} = 12V		42	45	48	dB
		V _{CC} = 13.2V		42	45	48	dB
Total Harmonic Distortion	THD	V _{CC} = 9V	V _i = 4mV	–	0.3	1.0	%
		V _{CC} = 12V		–	0.3	1.0	%
		V _{CC} = 13.2V		–	0.3	1.0	%
Output Power	P _O	V _{CC} = 9V	THD = 10%	2.0	2.4	–	W
		V _{CC} = 12V		3.6	4.2	–	W
		V _{CC} = 13.2V		4.5	5.1	–	W
Output Noise Voltage	V _{no}	V _{CC} = 9V	V _i = 0, R _g = 3.9kΩ	–	0.2	1.0	mV
		V _{CC} = 12V	V _i = 0, R _g = 10kΩ	–	0.3	1.5	mV
		V _{CC} = 13.2V	–	0.3	1.5	mV	
Channel Balance	CB	V _{CC} = 9V	V _i = 4mV	–	0	1	dB
		V _{CC} = 12V		–	0	1	dB
		V _{CC} = 13.2V		–	0	1	dB

Pin Connection Diagram

