

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

OCT ,2001.



© COPYRIGHT 2001 By --

ALL RIGHTS RESERVED.

LOC
JDIST
/



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	K3	REVISED PER ECO-11-005033	28MAR11	RK	HMR






HOW TO MATE AND UNMATE

MATE: ① → ④
UNMATE: ⑤ → ⑦



(APPLIED TO SHEET 1-2)

- MATERIAL ; HOUSING: HIGH TEMPERATURE THERMO PLASTIC UL94V-0
CONTACT: COPPER ARROY
LOCK LEVER STAINLESS STEEL
SOLDER PEG: COPPER ARROY
- FINISH ; CONTACT AREA: GOLD FLASH ON 0.0013MIN ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLT.
SOLDER PEG: TIN PLATING.
- MECHANICAL KEY POSITION OF CONNECTOR SEE TABLE.
- TOLERANCES NON-CUMULATIVE.
- NOT TO SCALE.
- INSIDE MUST BE RESIST COAT EXCEPT SOLDER PATTERN.
- IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY, OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE INSERTED AND LOCKED IN THE LATCH.



GENERAL TOLERANCE
10 ≥ : ±0.2
30 ≥ > 10 : ±0.25
100 ≥ > 30 : ±0.3
ANGLES : ±3°

TIN PLATING	AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1-1473149-4
	AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1473149-4
	AVAILABLE	2.5V (DDR1)	18.45	1.5	1.8	200	1473149-1
REMARK (PEG)	TOOLING STATUS	POWER SUPPLY	D5	D4	D3	POS	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN T.FUMIKURA	16JAN02	TE Connectivity		
			CHK T.KUSUHARA	17JAN02			
			APVD I.ENOMOTO	17JAN02			
			PRODUCT SPEC 108-5701				
DIMENSIONS: MM			TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	
			0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±			DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS	
MATERIAL			WEIGHT 4.7g			STANDARD PROFILE STANDARD TYPE (NEW LATCH TYPE)	
			CUSTOMER DRAWING			SIZE A3	RESTRICTED TO
			CAGE CODE 00779			DRAWING NO C-1473149	
			SCALE 2:1			SHEET 1 OF 4	REV K3

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

OCT ,2001.

© COPYRIGHT 2001 By -

ALL RIGHTS RESERVED.


LOC
J

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

REFERENCE P.C.BOARD PATTERN LAYOUT (CONNECTOR MOUNTING SIDE)




REAL SIZE (SCALE 1:1)



1.8V	17.55	2.4	2.7
2.5V	18.45	1.5	1.8
POWER SUPPLY	D5	D4	D3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	±

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

DDR1 & DDR2 SODIMM SOCKET
0.6mm PITCH 200POS


STANDARD PROFILE STANDARD TYPE (NEW LATCH TYPE)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1473149	-

SCALE 2:1

SHEET 2 OF 4

REV K3



LOC		DIST		REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD		
	-	SEE SHEET 1			-	-	-		

