

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFAL Mechanicals ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Current refinements (click to remove) Search Tips

 Text Search: 'LAM3B2-14-6Y'

LAM3B214-6Y



For Use with Stranded Aluminum or Copper Code Conductors

- Triple barrel provides termination of three conductors
- Made from high strength, extruded aluminum alloy to provide premium electrical and mechanical performance
- Tin-plated to inhibit corrosion
- Wide wire range -taking capability minimizes inventory requirements
- Inspection window to visually assure full conductor insertion
- Plated steel or aluminum set screw provides high strength, durable electrical contact between conductor and connector
- LAM3LB connector is provided with dual set screws to allow premium clamping of conductor to connector for heavy duty applications
- For use up to 600 V and temperature rated 90°C
- Available with NEMA hole sizes and spacing

Part Number	LAM3B2-14-6Y
RoHS Compliancy Status	Compliant
Note	LAM3B2-14-6Y replaces LAM3B2-14-6
Part Description	Aluminum horizontal configuration, three barrel, two-hole tongue connector, type LAM3B.
Product Type	Mechanical Connectors- Lugs
Height (In.)	0.47
Height (mm)	11.9
Length (In.)	2.49
Length (mm)	63.2
Stud Hole Size (In.)	5/16
Stud Hole Spacing (In.)	0.87
Tongue Width (In.)	1.63
Aluminum or Copper Conductor Size Range	#14 AWG – #2 AWG
CE Compliant	No
Conductor Size Range (mm²)	2.5 – 35
Figure No.	1
Pricing Description	Aluminum Mechanical Lug, 2 Hole, 3 Barrel, #14 #2 AWG, 5/16" (7.9mm) Stud
Tightening Torque (InLbs)	50*
Tongue Length	2.03
Tongue Length (mm)	51.6
Tongue Thickness	0.19
Tongue Width (mm)	41.1
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.