



## Three Phase Rectifier Bridge

$$I_{dAVM} = 140 \text{ A}$$

$$V_{RRM} = 1200-1800 \text{ V}$$

| $V_{RSM}$ | $V_{RRM}$ | Type           |
|-----------|-----------|----------------|
| V         | V         |                |
| 1200      | 1200      | VUO 105-12NO7  |
| 1400      | 1400      | VUO 105-14NO7  |
| 1600      | 1600      | VUO 105-16NO7  |
| 1800      | 1800      | VUO 105-18NO7* |

\* delivery time on request



| Symbol     | Test Conditions                            | Maximum Ratings                                                                                                       |
|------------|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| $I_{dAVM}$ | $T_C = 85^\circ\text{C}$ , module          | 140 A                                                                                                                 |
| $I_{FSM}$  | $T_{VJ} = 45^\circ\text{C}$ ;<br>$V_R = 0$ | $t = 10 \text{ ms}$ (50 Hz), sine 1500 A<br>$t = 8.3 \text{ ms}$ (60 Hz), sine 1650 A                                 |
|            | $T_{VJ} = T_{VJM}$<br>$V_R = 0$            | $t = 10 \text{ ms}$ (50 Hz), sine 1350 A<br>$t = 8.3 \text{ ms}$ (60 Hz), sine 1500 A                                 |
| $I^2t$     | $T_{VJ} = 45^\circ\text{C}$<br>$V_R = 0$   | $t = 10 \text{ ms}$ (50 Hz), sine 11250 A <sup>2</sup> s<br>$t = 8.3 \text{ ms}$ (60 Hz), sine 11300 A <sup>2</sup> s |
|            | $T_{VJ} = T_{VJM}$<br>$V_R = 0$            | $t = 10 \text{ ms}$ (50 Hz), sine 9120 A <sup>2</sup> s<br>$t = 8.3 \text{ ms}$ (60 Hz), sine 9350 A <sup>2</sup> s   |
| $T_{VJ}$   |                                            | -40...+150 °C                                                                                                         |
| $T_{VJM}$  |                                            | 150 °C                                                                                                                |
| $T_{stg}$  |                                            | -40...+150 °C                                                                                                         |
| $V_{ISOL}$ | 50/60 Hz, RMS                              | $t = 1 \text{ min}$ 2500 V~                                                                                           |
|            | $I_{ISOL} \leq 1 \text{ mA}$               | $t = 1 \text{ s}$ 3000 V~                                                                                             |
| $M_d$      | Mounting torque (M5)                       | $5 \pm 15 \%$ Nm                                                                                                      |
|            |                                            | $44 \pm 15 \%$ lb.in.                                                                                                 |
|            | Terminal connection torque (M5)            | $5 \pm 15 \%$ Nm                                                                                                      |
|            |                                            | $44 \pm 15 \%$ lb.in.                                                                                                 |
| Weight     | typ.                                       | 225 g                                                                                                                 |

### Features

- Package with screw terminals
- Isolation voltage 3000 V~
- Planar passivated chips
- Blocking voltage up to 1800 V
- Low forward voltage drop
- UL registered E 72873

### Applications

- Supplies for DC power equipment
- Input rectifiers for PWM inverter
- Battery DC power supplies
- Field supply for DC motors


### Advantages

- Easy to mount with two screws
- Space and weight savings
- Improved temperature and power cycling

| Symbol     | Test Conditions                  | Characteristic Values                             |
|------------|----------------------------------|---------------------------------------------------|
| $I_R$      | $V_R = V_{RRM1}$                 | $T_{VJ} = 25^\circ\text{C}$ $\leq 0.3 \text{ mA}$ |
|            | $V_R = V_{RRM2}$                 | $T_{VJ} = T_{VJM}$ $\leq 8.0 \text{ mA}$          |
| $V_F$      | $I_F = 150 \text{ A}$ ;          | $T_{VJ} = 25^\circ\text{C}$ $\leq 1.6 \text{ V}$  |
| $V_{T0}$   | For power-loss calculations only | 0.8 V                                             |
| $r_T$      |                                  | 5 mΩ                                              |
| $R_{thJC}$ | per diode                        | 0.83 K/W                                          |
|            | per module                       | 0.138 K/W                                         |
| $R_{thJH}$ | per diode                        | 1.13 K/W                                          |
|            | per module                       | 0.188 K/W                                         |

Data according to IEC 60747 and refer to a single diode unless otherwise stated.  
IXYS reserves the right to change limits, test conditions and dimensions.

### Dimensions in mm (1 mm = 0.0394")






Fig. 1 Forward current versus voltage drop per diode




Fig. 2 Surge overload current per diode  
 $I_{FSM}$ : Crest value.  $t$ : duration




Fig. 3  $I^2t$  versus time (1-10 ms) per diode




Fig. 4 Power dissipation versus direct output current and ambient temperature




Fig. 5 Maximum forward current at case temperature




Fig. 6 Transient thermal impedance per diode

Constants for  $Z_{thJC}$  calculation:

| i | $R_{thi}$ (K/W) | $t_i$ (s) |
|---|-----------------|-----------|
| 1 | 0.014           | 0.011     |
| 2 | 0.067           | 0.094     |
| 3 | 0.139           | 0.28      |
| 4 | 0.61            | 0.7       |

Constants for  $Z_{thJK}$  calculation:

| i | $R_{thi}$ (K/W) | $t_i$ (s) |
|---|-----------------|-----------|
| 1 | 0.014           | 0.011     |
| 2 | 0.067           | 0.094     |
| 3 | 0.139           | 0.28      |
| 4 | 0.61            | 0.7       |
| 5 | 0.3             | 4.2       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[VUO105-12NO7](#)