







NOTES:


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FDR REFERENCE ONLY.
4. RATING: 1A @125VAC, 0.5A @250VAC
5. CONTACT RESISTANCE: 20mILLI-OHMS
6. DIELECTRIC STRENGTH: 1500 VAC-1Minute
7. INSULATION RESISTANCE: 200 Mega-OHMS min.
8. MATERIALS:

HOUSING: ZINC ALLOY DIE CAST
CYLINDER: ZINC ALLOY W/CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATED
KEYS (2) KEY CODE 102: TUBULAR

ZINC ALLOY, CHROME PLATING

LEGEND

⊙ = INDICATES KEY PULL POSSIBLE



SWITCH FUNCTION	
POS 1	POS 2
↕	⇒
DNF	1-2

RECOMMENDED PANEL CUTOUT

REVISED SCHEMATIC				TITLE			
B	12174	RELEASED FOR PRODUCTION	5/22/02	CJB	E-SWITCH® K01064-102		
A	11746	DESCRIPTION	10/16/01	CJB			
REV.	ECN No.	DATE	CHKD				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				SCALE	DATE	DR	DWG
				1.5:1	10/16/01	CJB	K100302
							REV
							B