



PAR56

PAR56 300W Multipurpose 12V UW 1CT

Extremely powerful pressed-glass 179 mm diameter reflector lamps

PHILIPS

Product data

• General Characteristics

Cap-Base	Multipurpose [Screw Terminal]
Bulb	PAR56 [PAR 7inch/180mm]
Burning Position	any [Any/Universal]
Main Application	Underwater
Nominal Lifetime	1000 hr
Rated Lifetime (hours)	1000 hr
Rated Lifetime (years)	1 an

• Light Technical Characteristics

Beam Description	-
Beam Angle	40 D
Technical Beam Angle	40 D
Luminous Intensity	16000 (max) cd
Colour Rendering Index	100 Ra8
Colour Temperature	2700 K
Rated Luminous Flux	4378 Lm
Rated Beam Angle	40 D
Luminous flux in 90° cone	4378 Lm

• Electrical Characteristics

Rated Wattage	300.0 W
Lamp Wattage	300 W
Voltage	12 V
Dimmable	yes
Starting Time	0.0 s
Warm-up Time to 60% Light Outp	instant full light

• Environmental Characteristics

Energy Efficiency Label (EEL)	C
Energy consumption kWh/1000h	318 kWh

• Measuring Conditions

Switching cycle	4000X
-----------------	-------


• Product Dimensions

Overall Length C	119.3 (max) mm
Overall Length Rim C1	98 mm
Diameter D	178.5 (max) mm

• Product Data

Order code	159694 42
Full product code	871150015969442
Full product name	PAR56 300W Multipurpose 12V UW 1CT
Order product name	PAR56 300W Multipurpose 12V UW 1CT/8
Pieces per pack	1
Packing configuration	8
Packs per outerbox	8
Bar code on pack - EAN1	8711500159694
Bar code on outerbox - EAN3	8711500159700
Logistic code(s) - 12NC	923804817121
ILCOS code	IPAR-300-12-179/40
Net weight per piece	580.000 gr

Dimensional drawing



PAR56 300W Multipurpose 12V UW 1CT

Product	C (Max)	C1 (Norm)	D (Norm)	D (Max)
PAR56 300W MP 12V UW	119.3	98	-	178.5



© 2013 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2013, August 3
data subject to change